



PHILIPS

CoreLine



Innovative



Easy to install



High quality

- ✓ Industry
- ✓ Office
- ✓ Parking
- ✓ Retail
- ✓ Outdoor

Step aside or stay ahead?

Real professionals choose **Philips CoreLine** for every project
where light really matters



**REAL
PROs**
**REAL
QUALITY**

No choice or no limits?

When lighting really matters, you want to offer your customers the absolute best in quality and choice. The Philips CoreLine gives you all that and more with a full range of easy to install LED luminaires for every application and situation.

Enjoy more performance and variety with Philips CoreLine – the complete range of high quality LED lighting that's **setting the reference in the market.**



www.philips.com/coreline

**REAL
PROs**
**REAL
QUALITY**

CoreLine –
an LED light for
every need



Industry

- Hard-working lighting with costs and safety in mind
- Lighting that works harder while saving more
- Durable, cost-effective for more safety and health



Office

- Productivity-enhancing lighting that people like working in
- Lighting that optimizes space and productivity
- Smart, optimal lighting for more productivity and well-being



Parking

- Robust lighting that heightens safety while lowering costs
- Lighting that puts safety and convenience first
- Tough, safety-first lighting for more visibility and savings



Retail

- Welcoming lighting that keeps customers coming back
- Lighting that enhances the shopping experience
- Warm, inviting lighting for more sales and satisfaction



Outdoor

- Save energy and improve road safety
- Reduce CO₂ emissions for a greener, more sustainable city
- Connect new and existing street lights quickly and easily

Recommended luminaires for Industry

- ✓ Reduce costs
- ✓ Optimize operations
- ✓ Enhance health and safety
- ✓ Improve sustainability



CoreLine **highbay**

For warehouses and general manufacturing areas with medium/high height ceilings

- Highly efficient with up to 140lm/W
- **Long service life of 70,000 hrs at L70**
- Single point mounting system for simple installation
- Low glare rating and color rendering of >80
- Suitable for replacement of 250W/400W conventional highbays




Available in three sizes:

- Ø 385 mm
- Ø 450 mm
- Ø 510 mm



Easy installation

Optional DALI dimming for further energy savings



CoreLine **waterproof**

Waterproof luminaire for applications such as parking garages, warehouses or general lighting

- Energy savings and longer lifetime reduce operating costs
- Refreshed, robust design enabling smarter, simpler and faster installation
- Uniform, wide-beam light distribution, which supports easy and attractive lighting design
- Optional motion detection, emergency lighting, DALI and waterproof external connector (WEC)

New



interact
ready.

Energy-efficient and long lifetime: up to 140lm/W and 50khrs L75 lifetime

Many options available: L600/1200/1500, up to 8000lm, 4000K

Enhanced product architecture with improved electrical and mechanical design (longer sliders, better metal locks, toolless electrical connections)



Recommended luminaires for Industry

- ✓ Reduce costs
- ✓ Optimize operations
- ✓ Enhance health and safety
- ✓ Improve sustainability



CoreLine **trunking**

Designed for supermarkets, warehouses and assembly areas

- Reduced maintenance and best lumens per € solution
- Excellent beam shapes and sparkle for product enhancement
- **Lifetime: 50,000 hours L80**



Highly efficient
and reliable LED
boards



Advanced optics enable
precise and energy-
saving beam shapes

DALI and
emergency
lighting options
available



CoreLine **batten**

LED luminaires especially suitable for assembly
lines and cove lighting

- **Interact Ready version: integrated wireless antenna
for use with Interact Pro app and dashboard**
- General lighting - replacing conventional TL-D
- Installation flexibility and lengths same as TL-D
- Excellent performance and light quality with frosted diffuser
- Direct replacement for conventional battens in terms
of light performance, installation, flexibility and length
- **Lifetime: 50,000 hours L70**



interact
ready.




Installation flexibility
and lengths same as
TL-D

DALI and
emergency
lighting options
available



Through-wiring standard
included



Recommended luminaires for Offices

- ✓ Optimize operations
- ✓ Enhance productivity
- ✓ Support sustainability goals
- ✓ Optimize space



CoreLine **recessed luminaire**

Recessed office LED luminaire for general lighting applications

- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- Easy connection (with looping)
- Flicker-free thanks to high performance driver
- **Lifetime: 50,000 hours L70**



Slim design with a height of less than 35 mm

Office compliant optic available – OC version

Suitable for plaster ceiling installation



CoreLine **surface mounted luminaire**

Surface mounted LED luminaire for general lighting applications

- Easy connection (with looping)
- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- Slim design and <47 mm height
- **Lifetime: 50,000 hours L70**



Suspension set available as an accessory



Recessed version also available for use in grid ceilings (see above)

DALI and emergency lighting options available



Recommended luminaires for Offices

- ✓ Optimize operations
- ✓ Enhance productivity
- ✓ Support sustainability goals
- ✓ Optimize space




CoreLine panel

Recessed office LED luminaire for general lighting applications


- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- **Slim and robust** housing made from aluminum
- **Flicker-free** luminaire with high-performance driver
- Office compliant versions available (UGR<19)
- Recessed, surface mounted and suspended applications
- Optional emergency lighting
- 4300lm light output up to **123lm/W**
- **Lifetime: 50,000 hours L75**



interact
ready.



Mounting accessoires
available



Easy installation

Different sizes
available:

- 600 × 600 mm
- 622 × 622 mm
- 300 × 1200 mm
- 300 × 600 mm



CoreLine downlight

The perfect downlight for use
in general lighting applications

- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- Covers more professional applications due to dimming options and different optics (white and high gloss reflector)
- Reliable DALI and innovative connectivity options (Interact)
- IP54 and emergency lighting versions optionally available
- **Lifetime: 50,000 hours L70**
- Up to 115 lm/W



interact
ready.



White reflector



High gloss reflector

Two sizes and
lumen outputs
available:

- Ø 150 mm – 1100lm
- Ø 200 mm – 2200lm



Recommended luminaires for Parking

- ✓ Optimize operations
- ✓ Enhance safety
- ✓ Decreased operational costs
- ✓ Improve visibility



CoreLine **waterproof**

Waterproof luminaire for applications such as parking garages, warehouses or general lighting

- Energy savings and longer lifetime reduce operating costs
- Refreshed, robust design enabling smarter, simpler and faster installation
- Uniform, wide-beam light distribution, which supports easy and attractive lighting design
- Optional motion detection, emergency lighting, DALI and waterproof external connector (WEC)



Energy-efficient and long lifetime: up to 140lm/W and 50khrs L75 lifetime

Many options available: L600/1200/1500, up to 8000lm, 4000K

Enhanced product architecture with improved electrical and mechanical design (longer sliders, better metal locks, toolless electrical connections)



CoreLine **wall-mounted**

For circulation areas such as hallways and staircases

- Universal solution covering **various application requirements**
- Direct replacement of traditional wall-mounted luminaires
- Delivering the right visual comfort in common areas
- **Water- and vandalproof** as standard (IP65/IK08)
- Optional motion detection with grouping function
- Optional emergency lighting and DALI versions
- **Lifetime: 50,000 hours L70**



Easy installation with looping-wire option



Slim version with diameter of 35 cm (1200 or 2000lm)



Deeper version with diameter 35 or 48 cm (1200, 2000 or 3400lm)



CoreLine **batten**

For production areas with low ceilings

- General lighting – replacing conventional TL-D
- **Lifetime: 50,000 hours L70**
- Installation flexibility and lengths same as TL-D
- **Excellent performance and light quality thanks to frosted diffuser**
- Available wattage: 19W, 38W, 60W



Reliable integrated LED technology, ensuring **maintenance-free installation** and a **long lifetime**

Frosted diffuser ensures visual comfort



Easy installation without removing the cover



Recommended luminaires for

Retail


- ✓ Enhance experience
- ✓ Engage customers
- ✓ Improve sustainability
- ✓ Optimize operations




CoreLine projector

Accent lighting for retail or hospitality areas

- **Modern design** that blends in to most interiors
- Direct replacement of traditional CDM projectors
- Connectable to standard 3C track systems
- **Medium beam** (23D) or **wide beam angle** (36D) available
- Energy efficient: up to 90lm/W
- **Lifetime: 50,000 hours L70**



Recessed lens providing visual comfort



Black version



CoreLine recessed spot

Recessed spot for accent lighting purposes

- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- High-end materials for decorative applications and special **anti-glare optics**
- **Flicker-free** luminaire with high-performance driver
- **Dimmable** on wide range of wall-dimmers
- Multiple rims available in white, aluminium and black
- Slim design fits most ceiling types
- **Lifetime: 50,000 hours L70**



Easy installation



Modular product with many different rim designs

Three lumen outputs available:

- 650lm
- 900lm
- 1200lm



CoreLine slim downlight

The ultra thin downlight for general lighting applications with limited built-in-height

- **Interact Ready version: integrated wireless antenna for use with Interact Pro app and dashboard**
- 'Surface of light' downlight solution
- Product height of less than 50 mm
- Recessed and surface mounted version available
- Slim design fits most ceiling types
- **Lifetime: 50,000 hours L70**



interact
ready.



Easy installation



Surface mounted versions available in 150 and 200 diameter

Three sizes and lumen outputs available:

- Ø 68 mm/650lm
- Ø 150 mm/1100lm
- Ø 200 mm/2100lm



Recommended luminaires for Outdoor

- ✓ Enhance experience
- ✓ Engage customers
- ✓ Improve sustainability
- ✓ Optimize operations



CoreLine bollard

Professional bollard that gives guidance at night time and integrates well in most urban landscapes such as parks, squares and playgrounds, thanks to its discreet design


- **Comfortable light**
- Easy to install
- Saves energy compared to conventional lamps



Available with **symmetric and asymmetric optic**. Ground section **anchor accessory**.

- 1000lm system output
- 1 m height
- IP65 / IK10

Available in **warm white** and **neutral white**



CoreLine malaga

Designed for general road, street and residential application

- **Reliable quality: aluminum die-cast housing and tempered flat glass**
- **Maintainable, driver can be replaced**
- IP65 and IK08 provide durable operation



Available in **two optics** (DM and DW) and **two sizes**

Easy return on investment. The investment in the luminaire, by saving lamp changes required for SON-T lamp luminaires, is already re-paid.

Energy savings of 50 % reduce yearly running costs of the installation. Available in 3700lm, 5500lm, 7500lm and 11000lm.



CoreLine tempo

Professional floodlight for general outdoor lighting, perfect for sports facilities, parking lots and industrial areas

- Replacement of conventional floodlights up to 400W
- High-performance asymmetrical and symmetrical optics
- U-shaped universal mounting bracket and external quick 3-pole IP68 connector
- Reliable quality: Die-casting aluminum housing guarantees robustness, vibration-proof, wind force protection



Product available in **4 types/sizes:**

- CoreLine tempo small BVP110 - Length 285 mm
- CoreLine tempo medium BVP125 - Length 383 mm
- CoreLine tempo large BVP130 - Length 486 mm
- CoreLine tempo X-large BVP140 - Length: 583 mm

Warm white and neutral white available

Seaside resistant treatment and swimming pool protection options available



