

PHILIPS

LED lamps

TrueForce MasterClass High Lumen Corn Cob

For a range of industrial,
commercial and urban applications



The "Perfect Fit" with uncompromising efficacy and color quality

Philips MasterClass High Lumen Corn Cob lamps offer market leading HID replacements in a new, smaller size. Each lamp is specifically designed to meet the **ANSI** profiles of the traditional lamps they are replacing, delivering the ideal LED upgrade solution.

Benefits

- Up to 70% energy savings¹
- Delivers up to 400W replacements
- Long life lowers maintenance costs by reducing re-lamp frequency
- **Fits within industry ANSI outline offering perfect-fit in all HID fixtures**
- UL Type B lamps allow installer to bypass the ballast and reduce maintenance costs

Features

- Includes additional safety cable for secure installation
- Suitable for both enclosed and open fixtures
- Operational temperature range of -20°C to 55°C
- CRI 80 lamps enable both indoor and outdoor applications where color quality matters
- DLC Mogul based lamps
- UL damp rated (UL1993 + UL1598C)
- Active Cooling thermal system
- Built in 8KV surge protection
- Available in both 4000K and 5000K color temperatures (CCT)
- UL Type B system solution
- 5-year limited warranty²

1. LED system watts of 35 compared to 130 of a C100554/ALTO.

2. Depending upon operating hours. For details please visit www.signify.com/warranties.


Philips MasterClass High Lumen Corn Cob lamps

Ordering, electrical and technical data (Subject to change without notice)



Dimensions

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	Lifetime ¹ (hrs)	CCT (K)
MasterClass EX39 lamps									
559849	929002397304	80CC/LED/840/ND EX39 G2 BB 3/1	80	175-250	12000	120-277	80	50,000	4000
559856	929002397404	80CC/LED/850/ND EX39 G2 BB 3/1	80	175-250	12000	120-277	80	50,000	5000
559864	929002397504	115CC/LED/840/ND EX39 G2 BB 3/1	115	250-400	18000	120-277	80	50,000	4000
559872	929002397604	115CC/LED/850/ND EX39 G2 BB 3/1	115	250-400	18000	120-277	80	50,000	5000
559880	929002397704	150CC/LED/840/ND EX39 G2 BB 3/1	150	320-400	24000	120-277	80	50,000	4000
559898	929002397804	150CC/LED/850/ND EX39 G2 BB 3/1	150	320-400	24000	120-277	80	50,000	5000




80W EX39



80W

115W

150W



115W/150W EX39

Energy saving solution

For TrueForce Corn Cob G2 Active cooling 150w

Estimated lighting costs using a 400 MH lamp with ballast

Present Wattage	458 watts
× Annual operating hours	4,000 hours
=	1,832,000 watt-hours
÷ 1,000	= 1,832 kWh per year
× kWh rate of \$0.11	= \$201.52 per year
× 100 lamps	= \$20,152.00 annual energy cost

Estimated lighting costs using a Philips Corn Cob LED lamp

Present Wattage	150 watts
× Annual operating hours	4,000 hours
=	600,000 watt-hours
÷ 1,000	= 600 kWh per year
× kWh rate of \$0.11	= \$66.00 per year
× 100 lamps	= \$6,600.00 annual energy cost

Total estimated savings \$13,552.00 annual savings

Based on 100 lamps per space operating at 4000 hours per year.

1. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 50,000 hours is for bare lamp without fixture.

This example shows an application of 100 lamps accenting a space, operating 4,000 hours. Your actual savings may vary depending on the energy costs in your geographic location.

WARNINGS AND CAUTIONS

Risk of property damage or personal injury – The weight of the lamp is within the UL weight specification of a mogul (E39) base. However, before installing the lamp please ensure that the lamp holder (or socket) is not damaged or loose. The lamp holder (or socket) must be secured firmly to the fixture. If the lamp holder is damaged, corroded, charred or blackened, it must be replaced.

CAUTION: Risk of electric shock – do not use where directly exposed to water.

NOTES: This device complies with Part 15 of the FCC rule. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. This Class B digital apparatus complies with Canadian ICES-005. Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment. This lamp is suitable for dry and/or damp locations (indoor & outdoor applications). Suitable for use in outdoor luminaires as these luminaires provide a damp location for the lamp. This lamp is suitable for use in totally enclosed luminaires.



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.