



Type A



PAR



BR



Candle



G25 / ST19
Miscellaneous

Contents

Type A lamps 1 – 12

PAR lamps 13 – 27

BR lamps 23 – 27

Candles 28 – 33

Misc. (G25, ST19) 34 – 41

Type A lamps

Number of bulbs

							
		14A19/COR/927/FR/P/E26/DIM/T20 14A19/COR/930/FR/P/E26/DIM/T20 14A19/COR/940/FR/P/E26/DIM/T20 14A19/COR/950/FR/P/E26/DIM/T20	14A19/MAS/927-22/FR/P/E26/T20	12.2A19/COR/927/FR/P/E26/DIM/T20 12.2A19/COR/930/FR/P/E26/DIM/T20 12.2A19/COR/940/FR/P/E26/DIM/T20 12.2A19/COR/950/FR/P/E26/DIM/T20	12.2A19/MAS/927-22/FR/P/E26/T20	8.8A19/COR/927/FR/P/E26/DIM/T20 8.8A19/COR/930/FR/P/E26/DIM/T20 8.8A19/COR/940/FR/P/E26/DIM/T20 8.8A19/COR/950/FR/P/E26/DIM/T20	8.8A19/MAS/927-22/FR/P/E26/T20
Dimmer Company	Model No.	9290037846 (588681) 9290037847 (588673) 9290037848 (588665) 9290037849 (588657)	9290037845	9290023852 9290023853 9290023854 9290022852	9290022854	9290020363 (550459) 9290020362 (550442) 9290020361 (550434) 9290020323 (545897)	9290019409 (479444)
Leviton	6602	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	6631	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	6633	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	6672	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	6674	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	6615P	1-5	1-5	NR	NR	2-9	2-9
Leviton	DSE06	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	DSL06	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	DSM10	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	IPI06	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	IPL06	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	VPI06	1-10	1-10	1-13	2-13	1-17	1-17
Lutron	AYCL-153P	1-10	1-10	1-13	1-10	1-17	1-17
Lutron	CTCL-153P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	CTCL-153PDH	1-10	1-10	11-13	1-13	1-17	1-17
Lutron	DV-600P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	DV-600PR	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	DVCL-153P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	DVCL-253P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	DVELV-300P	1-5	1-5	1-6	1-6	1-9	1-9
Lutron	DVRP-253P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	LGCL-153P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	MACL-153M	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	MAELV-600	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	MALV-600	2-10	2-10	NR	NR	NR	NR
Lutron	MRF2-6ND-120	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	NTCL-250	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	PD-5NE	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	PD-6WCL	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	RRD-3LD	1-5	1-5	1-6	1-6	1-9	1-9
Lutron	RRD-6NA	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	S-600P	1-10	2-10	1-13	1-13	1-17	1-17
Lutron	SCL-153P	1-3	1-3	1-3	1-3	1-4	1-4
Lutron	SCL-153PR	1-3	1-3	1-3	1-3	1-4	1-4
Lutron	SELV-300P	1-5	1-5	1-6	1-6	1-9	1-9
Lutron	SLV-600P	1-8	1-8	1-9	1-9	1-13	1-13
Lutron	TGCL-153PH	1-10	1-10	1-13	1-13	1-17	1-17
Cooper	RI061-VW-K2	1-10	1-10	1-13	1-13	1-17	1-17
Eaton	DAL06P	1-10	1-10	1-13	1-13	1-17	1-17
Legrand	HCL453P	1-10	1-10	1-13	1-13	1-17	1-17
Sensors							
Lutron	MSCL-OP153M	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	MSCL-OP153MH	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	MS-OPS2H	1-10	1-10	1-13	1-13	1-17	1-17
Panel Modules							
Lutron	GP (Harrier) Card	NR	1-10	1-13	2-13	NR	NR
Lutron	HW-RPM-4A-120	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	HW-RPM-4U-120	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	LP-RPM-4U-120	1-10	1-10	1-13	1-13	1-17	1-17

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

Type A lamps									
Number of bulbs			5A19/COR/927/FR/P/E26/DIM/T20 5A19/PER/950/P/E26/DIM T20 5A19/PER/940/P/E26/DIM T20 5A19/PER/930/P/E26/DIM T20	5A19/MAS/927-22/FR/P/E26/T20	14A19/PER/8xx/FR/P/E26/D 4/4CT	11A19/CNG/8xx/FR/P/E26/D 4/4CT	8A19/PER/8xx/FR/P/E26/D 4/4CT	5A19/CNG/8xx/FR/P/E26/D 4/4CT	
Dimmer Company	Model No.		9290020357 (550400) 9290020360 (550426) 9290020359 (547042) 9290020358 (550418)	9290019407 (479428)	9290035853 (581868) 9290035852 (581835) 9290035851 (581827) 9290035850 (581801)	9290037520 (587733) 9290037519 (587725) 9290037518 (587717) 9290037517 (587709)	9290035849 (581777) 9290035849 (588079) 9290035848 (581769) 9290035748 (588061)	9290035796 (581785) 9290035796 (588053) 9290035795 (581751) 9290035795 (588046)	9290037512 (587691) 9290037511 (587683) 9290037510 (587675) 9290037509 (587667)
Leviton	6602	Professional Channel	1-20	1-20	1-10	1-13	1-17	1-30	
Leviton	6631		2-20	1-20	1-10	1-13	1-17	1-30	
Leviton	6633		1-20	1-20	1-10	1-13	1-17	1-30	
Leviton	6672		1-20	1-20	1-10	1-13	1-17	1-30	
Leviton	6674		1-20	1-20	1-10	1-13	1-17	1-30	
Leviton	6615P		2-14	2-14	1-5	1-7	1-9	1-15	
Leviton	DSE06		1-20	1-20	1-10	1-13	1-17	1-30	
Leviton	DSL06		1-20	1-20	1-10	1-13	1-17	1-30	
Leviton	DSM10		2-20	2-20	1-10	1-13	1-17	1-30	
Leviton	IPI06		1-20	1-20	1-10	1-13	1-17	1-30	
Leviton	IPL06		1-20	1-20	1-10	1-13	1-17	1-30	
Leviton	VPI06		1-20	2-20	1-10	1-13	1-17	1-30	
Lutron	AYCL-153P		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	CTCL-153P		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	CTCL-153PDH		1-20	1-20	NR	NR	NR	NR	
Lutron	DV-600P		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	DV-600PR		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	DVCL-153P		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	DVCL-253P		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	DVELV-300P		1-20	1-15	1-10	1-7	1-9	1-15	
Lutron	DVRP-253P		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	LGCL-153P		1-20	1-20	NR	NR	NR	NR	
Lutron	MACL-153M		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	MAELV-600		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	MALV-600		NR	NR	NR	NR	NR	NR	
Lutron	MRF2-6ND-120		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	NTCL-250		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	PD-5NE		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	PD-6WCL		1-10	1-5	1-10	1-13	1-17	1-30	
Lutron	RRD-3LD		1-14	1-20	1-5	1-7	1-9	1-15	
Lutron	RRD-6NA		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	S-600P		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	SCL-153P		1-5	1-5	1-3	1-3	1-4	1-8	
Lutron	SCL-153PR		1-5	1-5	1-3	1-3	1-4	1-8	
Lutron	SELV-300P		1-10	1-10	1-5	1-7	1-9	1-15	
Lutron	SLV-600P		1-20	1-20	1-8	1-10	1-13	1-20	
Lutron	TGCL-153PH		1-10	1-20	1-10	1-13	1-17	1-30	
Cooper	RI061-VW-K2		1-20	3-20	1-10	1-13	1-17	1-30	
Eaton	DAL06P		1-20	2-20	1-10	1-13	1-17	1-30	
Legrand	HCL453P		1-20	1-20	1-10	1-13	1-17	1-30	
Sensors									
Lutron	MSCL-OP153M		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	MSCL-OP153MH		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	MS-OPS2H		1-20	1-20	1-10	1-13	1-17	1-30	
Panel Modules									
Lutron	GP (Harrier) Card		NR	NR	1-10	1-13	1-17	1-30	
Lutron	HW-RPM-4A-120		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	HW-RPM-4U-120		1-20	1-20	1-10	1-13	1-17	1-30	
Lutron	LP-RPM-4U-120		1-20	1-20	1-10	1-13	1-17	1-30	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Type A lamps

Number of bulbs

Type A lamps Number of bulbs								
			12A19/LED/9xx/FR/Glass/E26/DIM 1FB T20	9.5A19/LED/9xx/FR/Glass/E26/DIM 1FB T20	8A19/LED/9xx/FR/Glass/E26/DIM 1FB T20	5A19/LED/9xx/FR/Glass/E26/DIM 1FB T20	6.6A15/PER/UD50/CL/G/E26/DIM 2PF T20	8A19/PER/UD/FR/G/E26/WGD 4/ 2PFT20
Dimmer Company	Model No.		9290034984 (578633) 9290034983 (578625) 9290034982 (578617)	9290034981 (578609) 9290034980 (578591) 9290034979 (578583)	9290034978 (578641) 9290034977 (578575) 9290034976 (578567)	9290034975 (578559) 9290034974 (578542) 9290034973 (578534)	9290030845 (573402)	9290030832 (573436)
Leviton	6602	Professional Channel	1-11	1-17	1-10	1-10	1-20	1-10
Leviton	6631		1-11	1-17	1-10	1-10	1-20	1-10
Leviton	6633		1-11	1-17	1-10	1-10	1-20	1-10
Leviton	6672		1-11	1-17	1-10	1-10	1-20	1-10
Leviton	6674		1-11	1-17	1-10	1-10	1-20	1-10
Leviton	6615P		NR	NR	NR	NR	NR	NR
Leviton	DSE06		1-20	1-20	1-10	1-10	1-20	1-10
Leviton	DSL06		NR	NR	1-10	1-10	1-20	1-10
Leviton	DSM10		1-20	1-20	1-10	1-10	1-20	1-10
Leviton	IPI06		1-11	1-17	1-10	1-10	1-20	1-10
Leviton	IPL06		1-11	1-17	1-10	1-10	1-20	1-10
Leviton	VPI06		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	AYCL-153P		1-11	NR	1-11	1-11	1-20	1-11
Lutron	CTCL-153P		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	CTCL-153PDH		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	DV-600P		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	DV-600PR		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	DVCL-153P		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	DVCL-253P		1-19	NR	1-20	1-20	1-20	1-20
Lutron	DVELV-300P		NR	NR	NR	NR	NR	NR
Lutron	DVRP-253P		1-19	1-20	1-20	1-20	1-20	1-20
Lutron	LGCL-153P		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	MACL-153M		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	MAELV-600		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	MALV-600		NR	NR	NR	NR	NR	NR
Lutron	MRF2-6ND-120		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	NTCL-250		1-19	NR	1-20	1-20	1-20	1-20
Lutron	PD-5NE		1-19	1-20	1-10	1-10	1-20	1-10
Lutron	PD-6WCL		NR	NR	1-10	1-10	1-20	1-10
Lutron	RRD-3LD		1-11	1-17	1-10	1-10	1-11	1-10
Lutron	RRD-6NA		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	S-600P		1-11	1-17	1-10	1-10	1-20	1-10
Lutron	SCL-153P		1-3	1-4	1-8	1-8	1-6	1-8
Lutron	SCL-153PR		1-3	1-4	1-8	1-8	1-6	1-8
Lutron	SELV-300P		1-6	1-8	1-10	1-10	1-11	1-10
Lutron	SLV-600P		1-8	1-13	1-10	1-10	1-17	1-10
Lutron	TGCL-153PH		1-11	1-17	1-10	1-10	1-20	1-10
Cooper	RI061-VW-K2		1-11	1-17	1-10	1-10	1-20	1-10
Eaton	DAL06P		1-20	1-20	1-10	1-10	1-20	1-10
Legrand	HCL453P		1-20	1-20	1-10	1-10	1-20	1-10
Sensors								
Lutron	MSCL-OP153M		NR	NR	1-10	1-10	1-20	1-10
Lutron	MSCL-OP153MH		NR	NR	1-10	1-10	1-20	1-10
Lutron	MS-OPS2H		1-5	1-7	1-10	1-10	1-20	1-10
Panel Modules								
Lutron	GP (Harrier) Card		NR	NR	NR	NR	NR	NR
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-20	1-20	1-20
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

Type A lamps								
Number of bulbs			5A15/PER/UD/CL/G/E12-E26/WGD 6/2PF T20	19W(100W Eq) A21	15W(75W Eq) A21	16A19/PER/9xx/P/E26/DIM 6/1FB T20	29A21/PER/8xx/FR/P/E26/WG/HO 4/1PF	16A21/PER/930/P/GU24/DIM 6/1FB T20
Dimmer Company	Model No.		9290029868 (564450) 9290029865 (564385)	9290002596A (451906)	9290002595A (453159) 9290002595A (451898)	9290023857 (561456) 9290023856 (561076) 9290023855 (561068) 9290022853 (561019)	9290023431 (571505) 9290023430 (571497)	9290023276 (558684)
Leviton	6602	Professional Channel	1-10			1-9	1-5	1-9
Leviton	6631		1-10			1-9	1-5	1-9
Leviton	6633		1-10			1-9	1-5	1-9
Leviton	6672		1-10			1-9	1-5	1-9
Leviton	6674		1-10	NR	NR	1-9	1-5	1-9
Leviton	6615P		NR	1-3	1-4		1-3	1-5
Leviton	DSE06		1-10					1-19
Leviton	DSL06		1-10			1-9	1-10	1-19
Leviton	DSM10		1-10					1-20
Leviton	IPI06		1-10	NR	1-8	NR	1-5	1-9
Leviton	IPL06		1-10			1-9	1-5	1-9
Leviton	VPI06		1-10					1-9
Lutron	AYCL-153P		1-11			1-9		1-9
Lutron	CTCL-153P		1-10			1-9		1-9
Lutron	CTCL-153PDH		1-10					1-9
Lutron	DV-600P		1-10	1-6	1-8	1-9	1-5	1-9
Lutron	DV-600PR		1-10					1-9
Lutron	DVCL-153P		1-10			1-9		1-9
Lutron	DVCL-253P		1-20					1-16
Lutron	DVELV-300P		NR	1-3	1-4	1-9	1-3	1-5
Lutron	DVRP-253P		1-20					1-16
Lutron	LGCL-153P		1-10					1-9
Lutron	MACL-153M		1-10	1-6	1-8	1-9	1-5	1-9
Lutron	MAELV-600		1-10					1-20
Lutron	MALV-600		NR					NR
Lutron	MRF2-6ND-120		1-10	1-6	1-8	1-9	1-5	1-9
Lutron	NTCL-250		1-20			1-9		1-16
Lutron	PD-5NE		1-10					1-16
Lutron	PD-6WCL		1-10			1-9	1-5	1-9
Lutron	RRD-3LD		1-10					1-5
Lutron	RRD-6NA		1-10	1-7	1-8	1-9	1-5	1-9
Lutron	S-600P		1-10					1-9
Lutron	SCL-153P		1-8	1-6		1-9		1-2
Lutron	SCL-153PR		1-8					1-2
Lutron	SELV-300P		1-10					1-5
Lutron	SLV-600P		1-10	1-4	1-6*	1-7	1-4	1-7
Lutron	TGCL-153PH		1-10					1-9
Cooper	RI061-VW-K2		1-10					1-9
Eaton	DAL06P		1-10					1-19
Legrand	HCL453P		1-10					1-20
Sensors								
Lutron	MSCL-OP153M		1-10	1-6	1-8	1-9	1-5	1-9
Lutron	MSCL-OP153MH		1-10	1-6		1-9	1-5	1-9
Lutron	MS-OPS2H		1-10					1-9
Panel Modules								
Lutron	GP (Harrier) Card		NR	1-12		1-9		NR
Lutron	HW-RPM-4A-120		1-20	1-17				1-19
Lutron	HW-RPM-4U-120		1-20	1-17				1-20
Lutron	LP-RPM-4U-120		1-20	1-17				1-20

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

Type A lamps

Number of bulbs

Type A lamps									
Number of bulbs			8.8A19/PER/930/P/GU24/DIM 6/1FB T20	16A19/PER/927-22/P/E26/WG 6/1FB T20	5.5A15/PER/927-922/CL/G/E26/WGX1FB	3.8A15/PER/927-922/CL/G/E26/WGX1FB T20	3.8A15/PER/927-922/CL/G/E12/WGX1FB T20	16w (100w Eq) A21 T20, P024994, 2019Q2	
Dimmer Company	Model No.		9290023275 (557686) 9290023275 (557660)	9290022855 (561027)	9290022086 (549402)	9290022083 (549386)	9290022081 (549378)	9290020371 (550525) 9290020370 (547125) 9290020369 (550517) 9290020368 (550509)	
Leviton	6602	Professional Channel	1-17	1-9	1-10	1-10	1-10	1-9	
Leviton	6631		1-17	1-9	1-10	1-10	1-10		
Leviton	6633		1-17	1-9	1-10	2-10	2-10	1-9	
Leviton	6672		1-17	1-9	1-10	1-10	1-10	1-9	
Leviton	6674		1-17	1-9	1-10	1-10	1-10		
Leviton	6615P		NR		NR	NR	NR	1-5	
Leviton	DSE06		1-20		1-10				
Leviton	DSL06		1-20	1-9	1-10	1-10	1-10		
Leviton	DSM10		1-20		1-10				
Leviton	IPI06		1-17	NR	1-10	2-10	2-10	1-9	
Leviton	IPL06		1-17	1-9	1-10	1-10	1-10		
Leviton	VPI06		1-17		1-10				
Lutron	AYCL-153P		1-17	1-9	1-11				
Lutron	CTCL-153P		1-17	1-9	1-10				
Lutron	CTCL-153PDH		NR		1-10				
Lutron	DV-600P		1-17	1-9	1-10	1-10	1-10	1-9	
Lutron	DV-600PR		1-17		1-10				
Lutron	DVCL-153P		1-17	1-9	1-10				
Lutron	DVCL-253P		1-20		1-20				
Lutron	DVELV-300P		1-9	1-9	NR	1-10	1-10	1-5	
Lutron	DVRP-253P		1-20		1-20				
Lutron	LGCL-153P		1-17		1-10				
Lutron	MACL-153M		1-17	1-9	1-10	1-10	1-10	1-9	
Lutron	MAELV-600		1-20		1-10				
Lutron	MALV-600		NR		NR				
Lutron	MRF2-6ND-120		1-17	1-9	1-10	1-10	1-10	1-9	
Lutron	NTCL-250		1-20	1-9	1-20				
Lutron	PD-5NE		1-20		1-10				
Lutron	PD-6WCL		1-17	1-9	1-10	1-10	1-10	1-9	
Lutron	RRD-3LD		1-9		1-10				
Lutron	RRD-6NA		1-17	1-9	1-10			1-9	
Lutron	S-600P		1-17		1-10				
Lutron	SCL-153P		1-4	1-9	1-8				
Lutron	SCL-153PR		1-4		1-8				
Lutron	SELV-300P		1-9		1-10				
Lutron	SLV-600P		1-13	1-7	1-10	1-10	1-10	1-7	
Lutron	TGCL-153PH		1-17		1-10				
Cooper	RI061-VW-K2		1-17		1-10				
Eaton	DAL06P		1-20		1-10				
Legrand	HCL453P		1-20		1-10				
Sensors									
Lutron	MSCL-OP153M		1-17	1-9	1-10	1-10	1-10	1-9	
Lutron	MSCL-OP153MH		1-17	1-9	1-10	1-10	1-10		
Lutron	MS-OPS2H		1-17		1-10				
Panel Modules									
Lutron	GP (Harrier) Card		NR	1-9	NR				
Lutron	HW-RPM-4A-120		1-20		1-20				
Lutron	HW-RPM-4U-120		1-20		1-20				
Lutron	LP-RPM-4U-120		1-20		1-20				

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

Type A lamps Number of bulbs									
			12.2w (75w Eq) A21 T20, P0024994, 2019Q2	16w A21 WG & CG bulb	12w (75w Eq) WG & CG T20, P0022267, 2019Q1 WG, 2019Q2 CG	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	8w WG A19 filament	5.5w(40w Eq)A19	
Dimmer Company	Model No.		9290020367 (550491) 9290020366 (547091) 9290020365 (550483) 9290020364 (550475)	9290020073A 9290020073 9290019413A 9290019413	9290020072 9290019411 (479469)	9290019696 (549493)	9290019334 (536920)	9290018669 (532985) 9290018371 (479428) 9290018362 (479436) 9290018361 (479840)	
Leviton	6602	Professional Channel	1-12	1-9	1-10	1-10	1-10	1-15	
Leviton	6631					1-10			
Leviton	6633		1-12	1-9	1-10	1-10	1-10	1-15	
Leviton	6672		1-12	1-9	1-10	1-10	1-10	1-15	
Leviton	6674					1-10			
Leviton	6615P		1-6	NR	3-6	NR	1-9	1-14	
Leviton	DSE06					1-10			
Leviton	DSL06					1-10			
Leviton	DSM10					1-10			
Leviton	IPI06		1-12	1-9	1-10	1-10	1-10	1-15	
Leviton	IPL06					1-10			
Leviton	VPI06					1-10			
Lutron	AYCL-153P					1-11			
Lutron	CTCL-153P					1-10			
Lutron	CTCL-153PDH					1-10			
Lutron	DV-600P		1-12	1-9	1-10	1-10	1-10	1-15	
Lutron	DV-600PR					1-10			
Lutron	DVCL-153P					1-10			
Lutron	DVCL-253P					1-20			
Lutron	DVELV-300P		1-6	1-5	1-6	NR	1-10	1-15	
Lutron	DVRP-253P					1-20			
Lutron	LGCL-153P					1-10			
Lutron	MACL-153M		1-12	1-9	1-10	1-10	1-10	1-15	
Lutron	MAELV-600					1-10			
Lutron	MALV-600					NR			
Lutron	MRF2-6ND-120		1-12	1-9	1-10	1-10	1-3	1-15	
Lutron	NTCL-250					1-20			
Lutron	PD-5NE					1-10			
Lutron	PD-6WCL		1-12	1-9	1-10	1-10	1-10	1-15	
Lutron	RRD-3LD					1-10			
Lutron	RRD-6NA		1-12	1-9	1-10	1-10	1-10	1-15	
Lutron	S-600P					1-10			
Lutron	SCL-153P					1-8			
Lutron	SCL-153PR					1-8			
Lutron	SELV-300P					1-10			
Lutron	SLV-600P		1-9	1-7	1-9	1-10	1-10	1-5	
Lutron	TGCL-153PH					1-10			
Cooper	RI061-VW-K2					1-10			
Eaton	DAL06P					1-10			
Legrand	HCL453P					1-10			
Sensors									
Lutron	MSCL-OP153M		1-12	1-9	1-10	1-10	1-10	1-15	
Lutron	MSCL-OP153MH					1-10	1-10	1-15	
Lutron	MS-OPS2H					1-10	1-10	1-15	
Panel Modules									
Lutron	GP (Harrier) Card					NR	1-10	1-15	
Lutron	HW-RPM-4A-120					1-20	1-10	1-15	
Lutron	HW-RPM-4U-120					1-20	1-10	1-15	
Lutron	LP-RPM-4U-120					1-20	1-10	1-15	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Type A lamps

Number of bulbs

Type A lamps Number of bulbs								
			12w(75w Eq) A21	16A21/PER/827-22/P/E26/WG	9.5w(60w Eq) A19 WG	16w(100w Eq) A21	9.5w(60w Eq) A19	4.5W(60W Eq) A19
Dimmer Company	Model No.		9290018668 (532993) 9290018367 (479477)	9290018377 9290018377A (479485) 9290018377A (479535) 9290018377A (479402)	9290018373 (479444)	9290018370 (479493) 9290018369 (479899) 9290018368 (479881)	9290018365 (479451) 9290018364 (479865) 9290018363 (479857)	9290012741 (466243) 9290012739 (466227)
Leviton	6602	Professional Channel	1-13	1-3	1-15	1-9	1-15	1-33
Leviton	6631							
Leviton	6633		1-13	1-3	1-15	1-9	1-15	1-33
Leviton	6672		1-13	1-3	1-15	1-9	1-15	1-33
Leviton	6674							1-10
Leviton	6615P		1-6	1-3	1-8	1-5	NR	1-17
Leviton	DSE06							
Leviton	DSL06							
Leviton	DSM10							
Leviton	IPI06		1-13	1-3	1-15	1-9	NR	1-33
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P							
Lutron	CTCL-153P							
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-13	1-3	1-15	1-9	1-15	1-33
Lutron	DV-600PR							
Lutron	DVCL-153P							
Lutron	DVCL-253P							
Lutron	DVELV-300P		1-6	1-3	1-8	1-9	1-15	1-17
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M		1-13	1-3	1-15	1-9	1-15	1-33
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		1-13	1-3	1-15	1-9	1-15	1-33
Lutron	NTCL-250							
Lutron	PD-5NE							
Lutron	PD-6WCL		1-13	1-3	1-15	1-9	1-15	NR
Lutron	RRD-3LD							
Lutron	RRD-6NA		1-13	1-3	1-15	1-9	1-15	1-15
Lutron	S-600P							
Lutron	SCL-153P							
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		1-9	1-3	1-15	1-7	1-8	1-25
Lutron	TGCL-153PH							
Cooper	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M		1-13	1-3	1-15	1-9	1-15	1-33
Lutron	MSCL-OP153MH		1-13		1-15	1-9	1-15	1-33
Lutron	MS-OPS2H		1-13		1-15	1-9	1-15	1-33
Panel Modules								
Lutron	GP (Harrier) Card		1-15		1-15	1-15	1-15	1-33
Lutron	HW-RPM-4A-120		1-15		1-15	1-15	1-15	1-33
Lutron	HW-RPM-4U-120		1-15		1-15	1-15	1-15	1-33
Lutron	LP-RPM-4U-120		1-15		1-15	1-15	1-15	1-33

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

Type A lamps Number of bulbs								
			5.5W(40W Eq)A15 Clear WG	9.5W A19 2700K Core	9W(60W Eq) A19 5000K core	9W(60W Eq) A19 3000K	9.5W A19 2200K-2700K	14W(75W Eq) A21 WG
Dimmer Company	Model No.		9290012150 (462529)	9290012006 (461269) 9290012006 (461194) 9290012006 (461210) 9290012006 (461244)	9290011970 (461327) 9290011970 (455881) 9290011970 (461368)	9290011969 (459057) 9290011969 (462234) 9290011969 (462242)	9290011840	9290011839 (459065) 9290011839 (459073) 9290011839 (459081) 9290011839 (459099)
Leviton	6602	Professional Channel	1-25	1-15	1-17	1-15	1-15	1-11
Leviton	6631							
Leviton	6633		1-25	1-15	1-17	1-15	1-15	1-11
Leviton	6672		1-25	1-15	1-17	1-15	1-15	1-11
Leviton	6674			1-15	1-3	1-15	1-15	1-11
Leviton	6615P		1-13	1-8	1-8	1-8	1-5	1-5
Leviton	DSE06							
Leviton	DSL06							
Leviton	DSM10							
Leviton	IPI06		1-25	1-15	1-17	1-15	1-15	1-11
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P							
Lutron	CTCL-153P							
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-25	1-15	1-17	1-15	1-15	1-11
Lutron	DV-600PR							
Lutron	DVCL-153P							
Lutron	DVCL-253P							
Lutron	DVELV-300P		1-13	1-8	1-8	1-8	1-5	1-5
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M		1-25	1-15	1-3	1-15	NR	1-11
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		1-25	1-15	1-17	1-15	1-15	1-11
Lutron	NTCL-250							
Lutron	PD-5NE							
Lutron	PD-6WCL		NR	1-15	1-17	1-15	1-15	1-11
Lutron	RRD-3LD							
Lutron	RRD-6NA		NR	1-15	1-3	1-15	1-15	1-11
Lutron	S-600P							
Lutron	SCL-153P							
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		1-19	1-15	1-13	1-15	1-11	1-11
Lutron	TGCL-153PH							
Cooper	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M		1-25	1-15	1-3	1-15	NR	1-11
Lutron	MSCL-OP153MH		1-25	1-15	1-17	1-15	1-15	1-11
Lutron	MS-OPS2H		1-25	1-15	1-17	1-15	1-15	1-11
Panel Modules								
Lutron	GP (Harrier) Card		1-25	1-15	1-17	1-15	1-15	1-23
Lutron	HW-RPM-4A-120			1-15	1-17	1-15	1-15	1-23
Lutron	HW-RPM-4U-120			1-15	1-17	1-15	1-15	1-23
Lutron	LP-RPM-4U-120			1-15	1-17	1-15	1-15	1-23

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Type A lamps

Number of bulbs

Type A lamps Number of bulbs								
			7W(40W Eq) A15 CC WG	7W(40W Eq) A19 CC WG	18W(100W Eq) A21 WG	6W(40 Eq) A19	6.5W(40W Eq) A19 WG	9W(60W Eq) A19 5000K
Dimmer Company	Model No.		9290011818 (458760)	9290011815 (458737)	9290011741 (459107) 9290011741 (459115) 9290011741 (459123) 9290011741 (459131)	9290011348 (455808) 9290011178 (453209) 9290011348 (455782) 9290011178 (453274) 9290011348 (455790) 9290011178 (454058)	9290011347 (455774) 9290011176 (453316) 9290011347 (455766) 9290011176 (453183) 9290011347 (455741)	9290011346 (455881) 9290011346 (455873) 9290011346 (455907) 9290011177 (453282) 9290011346 (455899) 9290011177 (453241)
Leviton	6602	Professional Channel	1-21	1-21	1-8	1-12	1-23	1-15
Leviton	6631							
Leviton	6633		1-21	1-21	1-8	1-12	1-23	1-15
Leviton	6672		1-21	1-21	1-8	1-12	1-23	1-15
Leviton	6674		1-21	1-21	1-8	1-12	1-23	1-15
Leviton	6615P		1-11	1-11	1-8	1-12	1-7	1-8
Leviton	DSE06							
Leviton	DSL06							
Leviton	DSM10							
Leviton	IPI06		1-21	1-21	1-8	1-12	1-23	1-15
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P							
Lutron	CTCL-153P							
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-21	1-21	1-8	1-12	1-23	1-15
Lutron	DV-600PR							
Lutron	DVCL-153P							
Lutron	DVCL-253P							
Lutron	DVELV-300P		1-11	1-11	1-8	1-12	1-7	1-8
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M		1-21	1-21	1-8	1-12	1-23	1-15
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		1-15	1-15	1-8	1-12	1-23	1-15
Lutron	NTCL-250							
Lutron	PD-5NE							
Lutron	PD-6WCL		1-21	1-21	1-8	1-12	1-23	1-15
Lutron	RRD-3LD							
Lutron	RRD-6NA		NR	NR	1-8	1-12	1-23	1-15
Lutron	S-600P							
Lutron	SCL-153P							
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		1-16	1-16	1-8	1-12	1-10	1-15
Lutron	TGCL-153PH							
Cooper	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M		1-21	1-21	1-8	1-12	1-23	1-15
Lutron	MSCL-OP153MH				1-8	1-12	1-23	1-15
Lutron	MS-OPS2H		1-21	1-21	1-8	1-12	1-23	1-15
Panel Modules								
Lutron	GP (Harrier) Card		1-21	1-21	1-22			
Lutron	HW-RPM-4A-120		1-21	1-21	1-22			
Lutron	HW-RPM-4U-120		1-21	1-21	1-22			
Lutron	LP-RPM-4U-120		1-21	1-21	1-22			

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

							
		9.5W A19 WG	10.5W(60W Eq) A19 Slim style	8W A19 Slim Style	11W(60W Eq) A19 Sultan	22W(100W Eq) A21	11W(60W Eq) A19 Sultan
Dimmer Company	Model No.	9290011345 (455824) 9290011345 (455831) 9290011345 (455865) 9290011345 (455832) 9290011345 (455857) 9290011345 (455816) 9290011345 (455840)					
		9290002709 (433235) 9290002709 (433151) 9290002707 (433227) 9290002707 (433144)	9290002706 (433219) 9290002706 (433136) 9290002704 (433201) 9290002704 (433128)	9290002296 (425264)	9290002290 (423525) 9290002290 (424432)	9290002268 (429258)	
Leviton	6602	1-15					
Leviton	6631						
Leviton	6633	1-15					
Leviton	6672	1-15					
Leviton	6674	1-15	1-14	1-18	1-4	NR	1-4
Leviton	6615P	1-8	1-5	1-8	1-4	NR	1-4
Leviton	DSE06						
Leviton	DSL06						
Leviton	DSM10						
Leviton	IPI06	1-15	1-14	1-18	NR	1-6	NR
Leviton	IPL06						
Leviton	VPI06						
Lutron	AYCL-153P				1-5		1-5
Lutron	CTCL-153P				1-5		1-5
Lutron	CTCL-153PDH						
Lutron	DV-600P	1-15	1-14	1-18	1-4	NR	1-4
Lutron	DV-600PR						
Lutron	DVCL-153P						
Lutron	DVCL-253P				1-5		1-5
Lutron	DVELV-300P	1-8	1-5	1-8	1-6	NR	1-6
Lutron	DVRP-253P						
Lutron	LGCL-153P						
Lutron	MACL-153M	1-15	1-14	1-18	1-13	1-6	1-13
Lutron	MAELV-600					1-6	
Lutron	MALV-600						
Lutron	MRF2-6ND-120	1-15	1-14	1-18	1-13	1-6	1-13
Lutron	NTCL-250				1-5		1-5
Lutron	PD-5NE						
Lutron	PD-6WCL	1-15					
Lutron	RRD-3LD						
Lutron	RRD-6NA	1-15	1-14	1-18	1-13	1-6	1-13
Lutron	S-600P						
Lutron	SCL-153P		1-14	1-18	1-13		1-13
Lutron	SCL-153PR						
Lutron	SELV-300P					1-6	
Lutron	SLV-600P	1-15	1-8	1-11	1-13	1-6	1-13
Lutron	TGCL-153PH						
Cooper	RI061-VW-K2				1-2	NR	1-2
Eaton	DAL06P						
Legrand	HCL453P						
Sensors							
Lutron	MSCL-OP153M	1-15	1-14	1-18	1-13	1-6	1-13
Lutron	MSCL-OP153MH	1-15					
Lutron	MS-OPS2H	1-15					
Panel Modules							
Lutron	GP (Harrier) Card	1-19					
Lutron	HW-RPM-4A-120						
Lutron	HW-RPM-4U-120						
Lutron	LP-RPM-4U-120						

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Type A lamps

Number of bulbs

Type A lamps Number of bulbs								
			8W(40W Eq) A19 Sultan	17W(75W Eq) A21 Prince	7W(40W Eq) A15 CC WG	7W(40W Eq) A19 CC WG	10W A19 L Prize	8W(40W Eq)A19Remote Phospor
Dimmer Company	Model No.		9290002267 (423483) 9290002267 (424374) 9290002267 (429266)	9290002018 (422220) 17E26A21D (418590)	9290011818 (458778)	9290011815 (458745)	420075	414839
Leviton	6602	Professional Channel			1-21	1-21		
Leviton	6631							
Leviton	6633				1-21	1-21		
Leviton	6672				1-21	1-21		
Leviton	6674		NR	1-8	1-21	1-21	1	1-4
Leviton	6615P		1-9	1-4	1-11	1-11	1-4	NR
Leviton	DSE06							
Leviton	DSL06							
Leviton	DSM10							
Leviton	IPI06		1-9	1-8	1-21	1-21	1-2	NR
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P			1-8				
Lutron	CTCL-153P			1-8				
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-6	1-8	1-21	1-21	1-4	NR
Lutron	DV-600PR							
Lutron	DVCL-153P							
Lutron	DVCL-253P			1-8				
Lutron	DVELV-300P		1-9	1-4	1-11	1-11	1-5	1-18
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M		1-12	1-8	1-21	1-21	1-9	NR
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		1-12	1-8	1-15	1-15	1-11	NR
Lutron	NTCL-250			1-8				
Lutron	PD-5NE							
Lutron	PD-6WCL				1-21	1-21		
Lutron	RRD-3LD							
Lutron	RRD-6NA		1-13	1-8	NR	NR	1-9	1-16
Lutron	S-600P			1-8			NR	NR
Lutron	SCL-153P		1-18					1-8
Lutron	SCL-153PR							
Lutron	SELV-300P			1-8				
Lutron	SLV-600P		1-12	1-4	1-16	1-16	1-4	NR
Lutron	TGCL-153PH							
Cooper	RI061-VW-K2						NR	1-4
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M		1-12	1-8	1-21	1-21	1-9	NR
Lutron	MSCL-OP153MH		1-18					
Lutron	MS-OPS2H		1-18		1-21	1-21		
Panel Modules								
Lutron	GP (Harrier) Card				1-21	1-21		
Lutron	HW-RPM-4A-120				1-21	1-21		
Lutron	HW-RPM-4U-120				1-21	1-21		
Lutron	LP-RPM-4U-120				1-21	1-21		

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

			
		12.5W(60W Eq)A19 Remote Phosphor	8W A19
Dimmer Company	Model No.	409946	409938
Leviton	6602		
Leviton	6631		NR
Leviton	6633		
Leviton	6672		
Leviton	6674	1-12	1-14
Leviton	6615P	1-12	NR
Leviton	DSE06		
Leviton	DSL06		
Leviton	DSM10		
Leviton	IPI06	1-12	1-16
Leviton	IPL06		
Leviton	VPI06		
Lutron	AYCL-153P		1-4
Lutron	CTCL-153P		1-4
Lutron	CTCL-153PDH		
Lutron	DV-600P	1-8	1-16
Lutron	DV-600PR		
Lutron	DVCL-153P		
Lutron	DVCL-253P		1-4
Lutron	DVELV-300P	1-12	1-9
Lutron	DVRP-253P		
Lutron	LGCL-153P		
Lutron	MACL-153M	1-12	NR
Lutron	MAELV-600		1-16
Lutron	MALV-600		NR
Lutron	MRF2-6ND-120	1-12	NR
Lutron	NTCL-250		1-4
Lutron	PD-5NE		
Lutron	PD-6WCL		
Lutron	RRD-3LD		
Lutron	RRD-6NA	1-12	1-16
Lutron	S-600P		
Lutron	SCL-153P		
Lutron	SCL-153PR		
Lutron	SELV-300P		
Lutron	SLV-600P	NR	1-16
Lutron	TGCL-153PH		
Cooper	RI061-VW-K2		1-16
Eaton	DAL06P		
Legrand	HCL453P		
Sensors			
Lutron	MSCL-OP153M	1-12	NR
Lutron	MSCL-OP153MH		
Lutron	MS-OPS2H		
Panel Modules			
Lutron	GP (Harrier) Card		
Lutron	HW-RPM-4A-120		
Lutron	HW-RPM-4U-120		
Lutron	LP-RPM-4U-120		

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

PAR lamps Number of bulbs					 	 		 			
			4GU10/LED/930/F35/DIM/G/120V T20 10/1	4GU10/LED/927-22/F35/G/WG/T20 10/1	10PAR30S-L/EXPERTCOLOR/Fxx/ 9xx/P/D/T/JA8	10PAR30S-L/EXPERTCOLOR RETAIL/ Fxx-Sxx/9xx/D	14PAR38/EXPERTCOLOR/Fxx-Sxx/ 9xx/P/D/T20/JA8	14PAR38/EXPERTCOLOR RETAIL/ Fxx-Sxx/9xx/P/D			
Dimmer Company	Model No.		9290020555 (468140)	9290020553 (471565)	9290045790 (590216) 9290037558 (587642) 9290037557 (587634)	9290037556 (587626) 9290037555 (587618) 9290037554 (587600)	9290037553 (587592) 9290037552 (587584) 9290037551 (587576)	9290037550 (587568) 9290037549 (587550) 9290037548 (587543)	9290037547 (587535) 9290037546 (587527) 9290037545 (587519)	9290037544 (587501) 9290037543 (587493) 9290037542 (587485)	9290037541 (587477) 9290037540 (587469) 9290037539 (587451) 9290037538 (587444)
Leviton	6602	Professional Channel	1-20	1-20	1-15	1-15	1-10	1-10			
Leviton	6631		1-20	1-20	1-15	1-15	1-10	1-10			
Leviton	6633		1-20	1-20	1-15	1-15	1-10	1-10			
Leviton	6672		1-20	1-20	1-15	1-15	1-10	1-10			
Leviton	6674		1-20	1-20	1-15	1-15	1-10	1-10			
Leviton	6615P		NR	NR	1-8	1-8	1-5	1-5			
Leviton	DSE06		1-20	1-20	1-20	1-20	1-20	1-20			
Leviton	DSL06		1-20	1-20	1-20	1-20	1-20	1-20			
Leviton	DSM10		1-20	1-20	1-20	1-20	1-20	1-20			
Leviton	IPI06		1-20	1-20	1-15	1-15	1-10	1-10			
Leviton	IPL06		1-20	1-20	1-15	1-15	1-10	1-10			
Leviton	VPI06		1-20	NR	1-15	1-15	1-10	1-10			
Lutron	AYCL-153P		1-20	1-20	1-15	1-15	1-10	1-10			
Lutron	CTCL-153P		1-20	1-20	1-15	1-15	1-10	1-10			
Lutron	CTCL-153PDH		NR	1-20	1-15	1-15	1-10	1-10			
Lutron	DV-600P		1-20	1-20	1-15	1-15	1-20	1-20			
Lutron	DV-600PR		1-20	1-20	1-15	1-15	1-10	1-10			
Lutron	DVCL-153P		1-20	1-20	1-15	1-15	1-10	1-10			
Lutron	DVCL-253P		1-20	1-20	1-15	1-15	1-10	1-10			
Lutron	DVELV-300P		1-20	1-20	1-8	1-8	1-5	1-5			
Lutron	DVRP-253P		NR	NR	1-20	1-20	1-15	1-15			
Lutron	LGCL-153P		1-20	1-20	1-15	1-15	1-10	1-10			
Lutron	MACL-153M		1-20	1-20	1-15	1-15	1-10	1-10			
Lutron	MAELV-600		1-20	1-20	1-20	1-20	1-20	1-20			
Lutron	MALV-600		NR	NR	NR	NR	1-15	1-15			
Lutron	MRF2-6ND-120		1-20	1-20	1-15	1-15	1-10	1-10			
Lutron	NTCL-250		1-20	1-20	1-15	1-15	1-15	1-15			
Lutron	PD-5NE		1-20	NR	1-20	1-20	1-20	1-20			
Lutron	PD-6WCL		1-20	1-20	1-15	1-15	1-10	1-10			
Lutron	RRD-3LD		1-20	1-19	1-8	1-8	1-5	1-5			
Lutron	RRD-6NA		1-20	1-20	1-15	1-15	1-15	1-15			
Lutron	S-600P		1-20	1-20	1-15	1-15	1-15	1-15			
Lutron	SCL-153P		1-20	1-20	1-15	1-15	1-15	1-15			
Lutron	SCL-153PR		1-9	1-9	1-3	1-3	1-3	1-3			
Lutron	SELV-300P		1-19	1-20	1-8	1-8	1-8	1-8			
Lutron	SLV-600P		1-20	1-20	1-10	1-10	1-11	1-11			
Lutron	TGCL-153PH		1-20	1-20	1-15	1-15	1-15	1-15			
Eaton	RI061-VW-K2		1-20	1-20	1-15	1-15	1-10	1-10			
Eaton	DAL06P		1-20	1-20	1-20	1-20	1-20	1-20			
Legrand	HCL453P		1-20	NR	1-20	1-20	1-20	1-20			
Sensors											
Lutron	MSCL-OP153M		1-20	NR	1-15	1-15	1-15	1-15			
Lutron	MSCL-OP153MH		1-20	1-20	1-10	1-10	1-10	1-10			
Lutron	MS-OPS2H		1-20	1-20	1-15	1-15	1-15	1-15			
Panel Modules											
Lutron	GP (Harrier) Card		NR	NR	1-20	1-20	NR	NR			
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-20	1-20	1-20			
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20			
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20			

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

							
		8.5PAR30S/COR/9xx/Fxx/D/P/ULW/ T20 6/1FB	8.5PAR30L/COR/9xx/Fxx/D/P/ULW/ T20 6/1FB	5.5PAR20/COR/Fxx/9xx/DIM/P/T20 6/1FB	5.5PAR20/COR/Fxx/927-922/DIM/P/ T20 6/1FB	10PAR38/COR/9xx/Fxx/DIM/P/ULW/ T20 6/1FB	13PAR38/COR/9xx/Fxx/DIM/P/ULW/ T20 6/1FB
Dimmer Company	Model No.	9290037537 (587436) 9290037390 (586321) 9290037536 (587428) 9290037389 (586313) 9290037392 (586347) 9290037388 (586305) 9290037391 (586339)	9290037535 (587410) 9290037386 (586289) 9290037534 (587402) 9290037385 (586271) 9290037387 (586297) 9290037384 (586263)	9290037398 (586404) 9290037397 (586396) 9290037396 (586388) 9290037395 (586370)	9290037394 (586362) 9290037393 (586354)	9290037383 (586255) 9290037380 (586222) 9290037382 (586248) 9290037379 (586214) 9290037381 (586230)	9290037378 (586206) 9290037373 (586156) 9290037377 (586198) 9290037372 (586149) 9290037376 (586180) 9290037371 (586131) 9290037375 (586172) 9290037370 (586123) 9290037374 (586164) 9290037369 (586115)
Leviton	6602	1-20	1-20	1-20	1-20	1-15	1-20
Leviton	6631	1-20	1-20	1-20	1-20	1-15	1-20
Leviton	6633	1-20	1-20	1-20	1-20	1-15	1-20
Leviton	6672	1-20	1-20	1-20	1-20	1-15	1-20
Leviton	6674	1-20	1-20	1-20	1-20	1-15	1-20
Leviton	6615P	NR	NR	1-14	NR	1-8	1-14
Leviton	DSE06	1-20	1-20	1-20	1-20	1-20	1-20
Leviton	DSL06	1-20	1-20	1-20	1-20	1-20	1-20
Leviton	DSM10	1-20	1-20	1-20	1-20	1-20	1-20
Leviton	IPI06	1-20	1-20	1-20	1-20	1-15	1-20
Leviton	IPL06	1-20	1-20	1-20	1-20	1-15	1-20
Leviton	VPI06	1-20	1-20	1-20	1-20	1-15	1-20
Lutron	AYCL-153P	1-20	1-20	1-20	1-20	1-15	1-10
Lutron	CTCL-153P	1-20	1-20	1-20	1-20	1-15	1-10
Lutron	CTCL-153PDH	1-20	1-20	1-20	1-20	1-15	1-20
Lutron	DV-600P	1-20	1-20	1-20	1-20	1-15	1-20
Lutron	DV-600PR	1-20	1-20	1-20	1-20	1-15	1-20
Lutron	DVCL-153P	1-20	1-20	1-20	1-20	1-15	1-20
Lutron	DVCL-253P	1-20	1-20	1-20	1-20	1-15	1-10
Lutron	DVELV-300P	1-20	1-20	1-20	1-20	1-8	1-20
Lutron	DVRP-253P	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	LGCL-153P	1-20	1-20	1-20	1-20	1-15	1-20
Lutron	MACL-153M	1-20	1-20	1-20	1-20	1-15	1-20
Lutron	MAELV-600	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	MALV-600	NR	NR	NR	NR	NR	NR
Lutron	MRF2-6ND-120	NR	NR	NR	NR	NR	NR
Lutron	NTCL-250	1-20	1-20	1-20	1-20	1-15	1-10
Lutron	PD-5NE	1-20	1-20	1-20	1-20	1-20	1-19
Lutron	PD-6WCL	1-20	1-20	1-20	1-20	1-15	1-20
Lutron	RRD-3LD	1-9	1-9	1-14	1-20	1-8	1-6
Lutron	RRD-6NA	1-20	1-20	1-20	1-20	1-15	1-20
Lutron	S-600P	1-20	1-20	1-20	1-20	1-15	1-20
Lutron	SCL-153P	1-20	1-20	1-20	1-20	1-15	1-10
Lutron	SCL-153PR	1-20	1-20	1-7	1-7	1-4	1-20
Lutron	SELV-300P	1-14	1-14	1-14	1-14	1-8	1-20
Lutron	SLV-600P	1-20	1-20	1-20	1-20	1-11	1-8
Lutron	TGCL-153PH	1-20	1-20	1-20	1-20	1-15	1-20
Eaton	RI061-VW-K2	1-20	1-20	1-20	1-20	1-15	1-20
Eaton	DAL06P	1-20	1-20	1-20	1-20	1-20	1-20
Legrand	HCL453P	1-20	1-20	2-20	1-20	1-20	1-20
Sensors							
Lutron	MSCL-OP153M	1-20	1-20	1-20	1-20	1-15	1-20
Lutron	MSCL-OP153MH	NR	NR	NR	NR	NR	NR
Lutron	MS-OPS2H	1-18	1-18	1-20	1-20	1-15	1-12
Panel Modules							
Lutron	GP (Harrier) Card	NR	NR	NR	NR	NR	NR
Lutron	HW-RPM-4A-120	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	HW-RPM-4U-120	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	LP-RPM-4U-120	1-20	1-20	1-20	1-20	1-20	1-20

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs

PAR lamps									
Number of bulbs			27PAR38TrueF 8xx Fxx DIM 120V-277V 6/1FB	33PAR38/PER/8xx/Sxx-Fxx/DIM/120V 6/1FB	9.4PAR30S/COR/935/F25/DIM/120V/T20 6/1FB	14PAR38/COR/9xx/F25/DIM/120V/T20 6/1FB	14PAR38/COR/930/F25/D/P/B/ULW/T20 6/1FB	13PAR38/LED/950/F25/DIM/GULW/T20 6/1FB	
Dimmer Company	Model No.		9290030636 (569731) 9290030635 (569723)	9290019208-Phase out 9290019197 (534636) 9290019168 (534602) 9290019196 (534628)	9290034669 (577759)	9290034668 (577742) 9290034667 (577734)	9290031338 (576470)	9290030303 (567818) 9290030300 (567792) 9290030299 (567784) 9290030298 (567776) 9290030296 (567768) 9290030295 (567750)	
Leviton	6602	Professional Channel	NR	1-5	1-10	1-10	1-5		
Leviton	6631		NR	1-5	1-10	1-10			
Leviton	6633		NR	1-5	1-10	1-10	1-5	1-10	
Leviton	6672		NR	1-5	1-10	1-10	1-5		
Leviton	6674		NR	1-5	1-10	1-10		1-10	
Leviton	6615P		1-3	1-2	NR	NR	1-5		
Leviton	DSE06		1-5	1-5					
Leviton	DSL06		NR	1-5	1-10	1-10		1-10	
Leviton	DSM10		NR	1-5					
Leviton	IPI06		NR	1-5	NR	NR	1-5	1-10	
Leviton	IPL06		NR	1-5	1-10	1-10			
Leviton	VPI06		NR	1-5					
Lutron	AYCL-153P		NR	1-5	1-10	1-10		1-10	
Lutron	CTCL-153P		NR	1-5	1-10	1-10		1-10	
Lutron	CTCL-153PDH		NR	NR					
Lutron	DV-600P		NR	1-5	1-10	1-10	1-5	1-10	
Lutron	DV-600PR		NR	1-5					
Lutron	DVCL-153P		NR	1-5	1-10	1-10		1-10	
Lutron	DVCL-253P		NR	1-5	1-10	1-10		1-10	
Lutron	DVELV-300P		1-3	1-2			1-5	1-5	
Lutron	DVRP-253P		1-5	1-5					
Lutron	LGCL-153P		NR	NR					
Lutron	MACL-153M		NR	1-5	1-10	1-10	1-5		
Lutron	MAELV-600		NR	1-5					
Lutron	MALV-600		NR	1-5					
Lutron	MRF2-6ND-120		NR	1-5	1-10	1-10	1-5	1-10	
Lutron	NTCL-250		NR	1-5	1-10	1-10		1-10	
Lutron	PD-5NE		NR	1-5					
Lutron	PD-6WCL		NR	1-5	1-10	1-10	1-5		
Lutron	RRD-3LD		NR	1-2					
Lutron	RRD-6NA		NR	1-5					
Lutron	S-600P		NR	1-5					
Lutron	SCL-153P		NR	1	1-10	1-10		1-10	
Lutron	SCL-153PR		NR	1					
Lutron	SELV-300P		1-3	1-2					
Lutron	SLV-600P		NR	1-3	1-10	1-8	1-5	1-8	
Lutron	TGCL-153PH		NR	1-5					
Eaton	RI061-VW-K2		NR	1-5					
Eaton	DAL06P		NR	1-5					
Legrand	HCL453P		NR	1-5					
Sensors									
Lutron	MSCL-OP153M		NR	1-5	1-10	1-10	1-5		
Lutron	MSCL-OP153MH		NR	1-5	1-10	1-10		1-10	
Lutron	MS-OPS2H		1-5	1-5					
Panel Modules									
Lutron	GP (Harrier) Card		NR	NR					
Lutron	HW-RPM-4A-120		NR	1-5					
Lutron	HW-RPM-4U-120		NR	1-5					#VALUE!
Lutron	LP-RPM-4U-120		NR	1-5					

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

PAR lamps Number of bulbs								
			PAR38 13W JA8	10PAR38/LED/9xx/Fxx/DIM/GULW/T20 6/1FB	8.5PAR30S/LED/9xx/F25/DIM/GULW/T20 6/1FB	8.5PAR30L/LED/9xx/Fxx/DIM/GULW/T20 6/1FB	5.5PAR20/LED/F40/9xx/DIM/G/T20 6/1FB	13PAR38/COR/9xx/Fxx/DIM/P/ULW/T20 6/1FB
Dimmer Company	Model No.		9290030297 (567834) 9290030302 (567842)	9290030293 (567917) 9290030288 (567875) 9290030292 (567933) 9290030287 (567925) 9290030290 (567891) 9290030286 (567867) 9290030289 (567883) 9290030285 (567859)	9290030282 (568055) 9290030278 (568014) 9290030277 (568006)	9290030280 (568030) 9290030271 (567965) 9290030279 (568022) 9290030270 (567957) 9290030274 (567999) 9290030269 (567941) 9290030272 (567973)	9290030265 (568097) 9290030261 (568063)	9290030263 (568105)
Leviton	6602	Professional Channel						
Leviton	6631							
Leviton	6633		1-10	1-15	1-15	1-15	1-20	1-20
Leviton	6672							
Leviton	6674		1-10	1-15	1-15	1-15	1-20	1-20
Leviton	6615P							
Leviton	DSE06							
Leviton	DSL06		1-10	1-15	1-15	1-15	1-20	1-20
Leviton	DSM10							
Leviton	IPI06		1-10	1-15	1-15	1-15	1-20	1-20
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P		1-10	1-15	1-15	1-15	1-20	1-20
Lutron	CTCL-153P		1-10	1-15	1-15	1-15	1-20	1-20
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-10	1-15	1-15	1-15	1-20	1-20
Lutron	DV-600PR							
Lutron	DVCL-153P		1-10	1-15	1-15	1-15	1-20	1-20
Lutron	DVCL-253P		1-10	1-15	1-15	1-15	1-20	1-20
Lutron	DVELV-300P		1-5	1-8	1-8	1-8	1-10	1-10
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M							
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		1-10	1-15	1-15	1-15	1-20	1-20
Lutron	NTCL-250		1-10	1-15	1-15	1-15	1-20	1-20
Lutron	PD-5NE							
Lutron	PD-6WCL							
Lutron	RRD-3LD							
Lutron	RRD-6NA							
Lutron	S-600P							
Lutron	SCL-153P		1-10	1-15	1-15	1-15	1-20	1-20
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		1-8	1-10	1-10	1-10	1-15	1-15
Lutron	TGCL-153PH							
Eaton	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M							
Lutron	MSCL-OP153MH		1-10	1-15	1-15	1-15	1-20	1-20
Lutron	MS-OPS2H							
Panel Modules								
Lutron	GP (Harrier) Card							
Lutron	HW-RPM-4A-120							
Lutron	HW-RPM-4U-120							
Lutron	LP-RPM-4U-120							

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs

															
			PAR20 5.5W JA8	17W PAR38 SO/Expert color, 14w PAR38 T20, 10w PAR38 T20					12W PAR30L Expert color, 9.4w PAR30L & PAR30S T20			12W PAR30S AF SO/ Expert color			
Dimmer Company	Model No.		9290030262 (568071)	9290022383 (551895) 9290022382 (551887) 9290020451 (546937) 9290020450 (546929)	9290019092 (546937) 9290019091 (546929) 9290018538 (546950) 9290018537 (546945)	9290013698 (471797) 9290013398 (470864) 9290013394 (470823) 9290011138 (435420)	9290011137 (435412) 9290011135 (435396) 9290011131 (435354)	9290020457 (546993) 9290020456 (546985) 9290020455 (546977) 9290020454 (546969)	9290013412 (470988) 9290013411 (470970) 9290013410 (470962) 9290013409 (470954)	9290012858 (471052) 9290012857 (471045) 9290012856 (471037)	9290013697 (471789) 9290013407 (470930) 9290013406 (470922) 9290013402 (478989)	9290012862 (471094) 9290011129 (435339) 9290011126 (435305) 9290011125 (435297)	9290011123 (435271) 9290011122 (435263)		
Leviton	6602	Professional Channel		1-8				1-8			1-12				
Leviton	6631														
Leviton	6633		1-20	1-8				1-8			1-8				
Leviton	6672			1-8				1-8			1-8				
Leviton	6674		1-20					1-8			1-8				
Leviton	6615P			1-4				1-5			1-4				
Leviton	DSE06														
Leviton	DSL06		1-20					1-8			1-8				
Leviton	DSM10														
Leviton	IPI06		1-20	1-8				1-8			1-8				
Leviton	IPL06														
Leviton	VPI06														
Lutron	AYCL-153P		1-20												
Lutron	CTCL-153P		1-20												
Lutron	CTCL-153PDH														
Lutron	DV-600P		1-20	1-8				1-8			1-12				
Lutron	DV-600PR														
Lutron	DVCL-153P		1-20												
Lutron	DVCL-253P		1-20												
Lutron	DVELV-300P		1-10	1-4				1-5			1-4				
Lutron	DVRP-253P														
Lutron	LGCL-153P														
Lutron	MACL-153M			1-8				1-8			1-12				
Lutron	MAELV-600														
Lutron	MALV-600														
Lutron	MRF2-6ND-120		1-20	1-8				1-8			1-8				
Lutron	NTCL-250		1-20												
Lutron	PD-5NE														
Lutron	PD-6WCL			1-8				1-8			1-12				
Lutron	RRD-3LD														
Lutron	RRD-6NA							1-8			1-8				
Lutron	S-600P														
Lutron	SCL-153P		1-20												
Lutron	SCL-153PR														
Lutron	SELV-300P														
Lutron	SLV-600P		1-15	1-5				1-8			1-8				
Lutron	TGCL-153PH														
Eaton	RI061-VW-K2														
Eaton	DAL06P														
Legrand	HCL453P														
Sensors															
Lutron	MSCL-OP153M			1-8				1-8			1-12				
Lutron	MSCL-OP153MH		1-20	1-8				1-8			1-8				
Lutron	MS-OPS2H			1-8				1-8			1-8				
Panel Modules															
Lutron	GP (Harrier) Card			1-8											
Lutron	HW-RPM-4A-120														
Lutron	HW-RPM-4U-120														
Lutron	LP-RPM-4U-120														

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

							
		14PAR38/COR/930/F25-F40/DIM/120V T20 6/1FB	8.5PAR20/PER/9xx/Fxx/DIM/EC/120V 6/1FB	12PAR30S/EXPERTCOLOR/F25/9xx/DIM	17PAR38/EXPERTCOLOR/F40/9xx/DIM	17PAR38/EXPERTCOLOR RETAIL/S8/9xx/DIM	120V Gen2 Glass PAR30L 10-75W
Dimmer Company	Model No.	9290020453 (546950) 9290020452 (546945)	9290019225 (535336) 9290019221 (535294) 9290019224 (535328) 9290019220 (535286) 9290019223 (535310) 9290019219 (535278) 9290019222 (535300) 9290019218 (535260)	9290013408 (470948) 9290013404 (470914) 9290013403 (470906)	9290013401 (470880) 9290013400 (470872) 9290013396 (470849)	9290013395 (470831) 9290012853 (471003) 9290012855 (471029) 9290012852 (470996) 9290012854 (471011)	9290013224 (471359) 9290013220 (529735) 9290013224 (471318) 9290013218 (529727) 9290013223 (529750) 9290013216 (529719) 9290013221 (529743) 9290013215 (529701)
Leviton	6602	1-8	5-15	1-12	1-8	1-8	1-15
Leviton	6631						
Leviton	6633	1-8	1-15	1-8	1-8	1-8	1-15
Leviton	6672	1-8	1-15	1-8	1-8	1-8	1-15
Leviton	6674		1-15	1-8			
Leviton	6615P	1-4	1-8	1-4	1-4	1-4	1-8
Leviton	DSE06						
Leviton	DSL06		1-15	1-8			
Leviton	DSM10						
Leviton	IPI06	1-8	1-15	1-8	1-8	1-8	1-15
Leviton	IPL06						
Leviton	VPI06						
Lutron	AYCL-153P		1-3				NR
Lutron	CTCL-153P		1-3				NR
Lutron	CTCL-153PDH						
Lutron	DV-600P	1-8	1-15	1-12	1-8	1-8	1-15
Lutron	DV-600PR						
Lutron	DVCL-153P		1-3				NR
Lutron	DVCL-253P		1-3				NR
Lutron	DVELV-300P	1-4	1-8	1-4	1-4	1-4	1-8
Lutron	DVRP-253P						
Lutron	LGCL-153P						
Lutron	MACL-153M	1-8	1-15	1-12	1-8	1-8	1-15
Lutron	MAELV-600						
Lutron	MALV-600						
Lutron	MRF2-6ND-120	1-8	1-15	1-8	1-8	1-8	1-15
Lutron	NTCL-250		1-3				NR
Lutron	PD-5NE						
Lutron	PD-6WCL	1-8	1-15	1-12	1-8	1-8	1-15
Lutron	RRD-3LD						
Lutron	RRD-6NA		1-15	1-8			1-2
Lutron	S-600P						
Lutron	SCL-153P		1-3				NR
Lutron	SCL-153PR						
Lutron	SELV-300P						
Lutron	SLV-600P	1-5	1-13	1-8	1-5	1-5	1-11
Lutron	TGCL-153PH						
Eaton	RI061-VW-K2						
Eaton	DAL06P						
Legrand	HCL453P						
Sensors							
Lutron	MSCL-OP153M	1-8	1-15	1-12	1-8	1-8	1-15
Lutron	MSCL-OP153MH	1-8	1-15	1-8	1-8	1-8	1-15
Lutron	MS-OPS2H	1-8	1-15	1-8	1-8	1-8	1-15
Panel Modules							
Lutron	GP (Harrier) Card	1-8	1-15		1-8	1-8	1-15
Lutron	HW-RPM-4A-120		1-15				1-15
Lutron	HW-RPM-4U-120		1-15				1-15
Lutron	LP-RPM-4U-120		1-15				1-15

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps
Number of bulbs

							
		120V Gen2 Glass PAR30S 10-75W	120V Gen2 Glass PAR38 12-90W	120V Gen2 Glass PAR38 14-120W	7W PAR16L ES	7W PAR20 WG Glass	7W PAR20 Glass
Dimmer Company	Model No.	9290013213 (471334) 9290013207 (529784) 9290013212 (529818) 9290013205 (529776) 9290013210 (529800) 9290013204 (529768) 9290013209 (529792)	9290013203 (529693) 9290013198 (529651) 9290013202 (529685) 9290013197 (529644) 9290013201 (474700) 9290013196 (474692) 9290013200 (529677) 9290013195 (529636) 9290013199 (529669) 9290013194 (529628)	9290013192 (529610) 9290013191 (529602) 9290013186 (529537) 9290013190 (474684) 9290013185 (474676) 9290013189 (529594) 9290013184 (529529) 9290013188 (529552) 9290013183 (529503)	9290013181 (475434)	9290013173 (471136) 9290013172 (471102)	9290013170 (471151) 9290013169 (471144) 9290013167 (471128) 9290013165 (471110)
Leviton	6602	1-15	1-11	1-10	1-15	1-15	1-16
Leviton	6631						
Leviton	6633	1-15	1-11	1-10	1-15	1-15	1-16
Leviton	6672	1-15	1-11	1-10	1-15	1-15	1-16
Leviton	6674						
Leviton	6615P	1-8	1-5	1-5	1-10	1-10	1-10
Leviton	DSE06						
Leviton	DSL06						
Leviton	DSM10						
Leviton	IPI06	1-15	1-11	1-10	1-15	1-15	1-16
Leviton	IPL06						
Leviton	VPI06						
Lutron	AYCL-153P	NR	1-5	NR	8G	1-15	3
Lutron	CTCL-153P	NR	1-5	NR	8G	1-15	3
Lutron	CTCL-153PDH						
Lutron	DV-600P	1-15	1-11	1-10	1-15	1-15	1-16
Lutron	DV-600PR						
Lutron	DVCL-153P	NR	1-5	NR	8G	1-15	3
Lutron	DVCL-253P	NR	1-5	NR	8G	1-15	3
Lutron	DVELV-300P	1-8	1-5	1-5	1-10	1-15	1-10
Lutron	DVRP-253P						
Lutron	LGCL-153P						
Lutron	MACL-153M	1-15	1-11	1-10	1-15	1-15	1-16
Lutron	MAELV-600						
Lutron	MALV-600						
Lutron	MRF2-6ND-120	1-15	1-11	1-5	1-15	1-15	1-16
Lutron	NTCL-250	NR	1-5	NR	8G	1-15	3
Lutron	PD-5NE						
Lutron	PD-6WCL	1-15	1-11	1-10	1-15	1-15	1-16
Lutron	RRD-3LD						
Lutron	RRD-6NA	1-2	1-3	1-10		1-15	1-16
Lutron	S-600P			1-8	1-15		
Lutron	SCL-153P	NR	1-5	NR	8G	1-15	3
Lutron	SCL-153PR						
Lutron	SELV-300P						
Lutron	SLV-600P	1-11	1-8		1-15	1-15	1-16
Lutron	TGCL-153PH						
Eaton	RI061-VW-K2						
Eaton	DAL06P						
Legrand	HCL453P						
Sensors							
Lutron	MSCL-OP153M	1-15	1-11	1-10	1-15	1-15	1-16
Lutron	MSCL-OP153MH	1-15	1-11	1-5	1-15	1-15	1-16
Lutron	MS-OPS2H	1-15	1-11	1-10	1-15	1-15	1-16
Panel Modules							
Lutron	GP (Harrier) Card	1-15	1-14	1-10	1-15	1-15	1-16
Lutron	HW-RPM-4A-120	1-15	1-2	1-10	1-15	1-15	1-16
Lutron	HW-RPM-4U-120	1-15	1-2	1-10	1-15	1-15	1-16
Lutron	LP-RPM-4U-120	1-15	1-2	1-10	1-15	1-15	1-16

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

PAR lamps									
Number of bulbs			12W Glass PAR30	13.5W PAR38 GLASS	16W PAR38 Glass	12PAR30S/EXPERTCOLOR RETAIL /F40/930/DIM	7W PAR16S/PAR16L 500lm	8W PAR30L	
			9290012954 (467928) 9290012946 (467860) 9290012952 (467902) 9290012944 (467845) 9290012950 (467894) 9290012942 (467837) 9290012949 (467886) 9290012940 (467811) 9290012948 (467878)	9290012927 (468025) 9290012922 (467779) 9290012927 (468009) 9290012921 (467761) 9290012926 (467803) 9290012920 (467753) 9290012923 (468199)	9290012919 (467984) 9290012915 (468181) 9290012919 (467944) 9290012914 (467712) 9290012918 (467746) 9290012913 (467704)	9290012861 (471086) 9290012860 (471078) 9290012859 (471060)	9290012457 (465005) 9290012456 (464999) 9290012457 (465039) 9290012454 (464981) 9290012456 (465021)	9290012391 (463737) 9290012391 (463752)	
Dimmer Company	Model No.		NR	NR	1-9	1-12	1-20	1-15	
Leviton	6602	Professional Channel							
Leviton	6631								
Leviton	6633		1-13	NR	1-9	1-8	1-20	1-15	
Leviton	6672		NR	1-11	1-9	1-8	1-20	1-15	
Leviton	6674		NR	NR	1-9	1-8	NR	1-15	
Leviton	6615P		2-5	1-5	2-5	1-4	1-10	1-8	
Leviton	DSE06								
Leviton	DSL06		NR	NR	1-9	1-8	NR	1-15	
Leviton	DSM10								
Leviton	IPI06		1-13	1-11	1-9	1-8	1-20	1-15	
Leviton	IPL06								
Leviton	VPI06								
Lutron	AYCL-153P								
Lutron	CTCL-153P								
Lutron	CTCL-153PDH								
Lutron	DV-600P		1-13	1-11	1-9	1-12	1-20	1-15	
Lutron	DV-600PR								
Lutron	DVCL-153P								
Lutron	DVCL-253P								
Lutron	DVELV-300P		1-5	1-5	1-5	1-4	1-10	1-8	
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M		NR	NR	NR	1-12	NR	1-15	
Lutron	MAELV-600								
Lutron	MALV-600								
Lutron	MRF2-6ND-120		NR	NR	NR	1-8	NR	1-15	
Lutron	NTCL-250								
Lutron	PD-5NE								
Lutron	PD-6WCL		NR	NR	NR	1-12		1-15	
Lutron	RRD-3LD								
Lutron	RRD-6NA		NR	NR	1-9	1-8	NR	1-15	
Lutron	S-600P								
Lutron	SCL-153P								
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P		1-9	1-8	1-7	1-8	1-16	1-10	
Lutron	TGCL-153PH								
Eaton	RI061-VW-K2								
Eaton	DAL06P								
Legrand	HCL453P								
Sensors									
Lutron	MSCL-OP153M		NR	NR	NR	1-12	NR	1-15	
Lutron	MSCL-OP153MH		NR	NR	NR	1-8	NR	1-15	
Lutron	MS-OPS2H		1-13	1-11	1-9	1-8	1-20	1-15	
Panel Modules									
Lutron	GP (Harrier) Card		NR	NR	1-10		NR	1-15	
Lutron	HW-RPM-4A-120		NR	NR	1-10		NR	1-15	
Lutron	HW-RPM-4U-120		NR	NR	1-10		NR	1-15	
Lutron	LP-RPM-4U-120		NR	NR	1-10		NR	1-15	

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs

						
		6W PAR20	6W(50W Eq) PAR20 SO	12W PAR38 SO	7W PAR16-GU10	12.5W PAR30L SO AF
Dimmer Company	Model No.	9290012260 (463711) 9290012254 (463687) 9290012253 (463679) 9290012251 (463653) 9290012259 (463703) 9290012254 (463612) 9290012253 (463604) 9290012250 (463646) 9290012255 (463695) 9290012254 (463851) 9290012253 (463844) 9290012247 (463729) 9290012254 (463620) 9290012254 (463794) 9290012252 (463661)				
Leviton	6602	1-15	1-15	1-14	NR	1-8
Leviton	6631					
Leviton	6633	1-15	1-15	NR	2-16	1-8
Leviton	6672	1-15	1-15	1-14	2-16	1-8
Leviton	6674	1-15	1-15		2-13	1-8
Leviton	6615P	1-15	1-15	1-7	NR	1-5
Leviton	DSE06					
Leviton	DSL06	1-15	1-15		2-13	1-8
Leviton	DSM10					
Leviton	IPI06	1-15	1-15	1-14	NR	1-8
Leviton	IPL06					
Leviton	VPI06					
Lutron	AYCL-153P					
Lutron	CTCL-153P					
Lutron	CTCL-153PDH					
Lutron	DV-600P	1-15	1-15	1-14	2-16	1-8
Lutron	DV-600PR					
Lutron	DVCL-153P					
Lutron	DVCL-253P					
Lutron	DVELV-300P	NR	NR	1-7	1-8	1-5
Lutron	DVRP-253P					
Lutron	LGCL-153P					
Lutron	MACL-153M	1-15	1-15	NR	2-20	1-8
Lutron	MAELV-600					
Lutron	MALV-600					
Lutron	MRF2-6ND-120	1-15	1-15	NR	2-16	1-8
Lutron	NTCL-250					
Lutron	PD-5NE					
Lutron	PD-6WCL	1-15	1-15	NR	2-16	1-8
Lutron	RRD-3LD					
Lutron	RRD-6NA	1-15	1-15	NR	2-16	1-8
Lutron	S-600P					
Lutron	SCL-153P					
Lutron	SCL-153PR					
Lutron	SELV-300P					
Lutron	SLV-600P	NR	NR	1-10	2-12	1-8
Lutron	TGCL-153PH					
Eaton	RI061-VW-K2					
Eaton	DAL06P					
Legrand	HCL453P					
Sensors						
Lutron	MSCL-OPI53M	1-15	1-15	NR	2-20	1-8
Lutron	MSCL-OPI53MH	1-15	1-15	NR	2-20	1-8
Lutron	MS-OPS2H	1-15	1-15	1-15	2-20	1-8
Panel Modules						
Lutron	GP (Harrier) Card			1-15	2-20	
Lutron	HW-RPM-4A-120			1-15	2-20	
Lutron	HW-RPM-4U-120			1-15	2-20	
Lutron	LP-RPM-4U-120			1-15	2-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

PAR lamps Number of bulbs												
			6W PAR20 AF			13W PAR38 SO	4.5W PAR16-GU10		10.5W PAR30L AF		15W PAR38	
Dimmer Company	Model No.		9290011487 (456269) 9290011452 (456111) 9290011451 (456103) 9290011450 (456095)	9290011449 (456087) 9290011449 (458893) 9290011448 (456079) 9290011448 (458927)	9290011448 (458919) 9290011447 (456061) 9290011446 (456053) 9290011445 (456046)	9290011322 (454751) 9290011321 (454744) 9290011320 (454736) 9290011319 (454728)	9290011288 (454363) 9290011288 (454405) 9290011288 (458034) 9290011288 (454389)	9290011288 (455378) 9290011288 (458034)	9290011114 (452656) 9290011114 (452623) 9290011114 (434984) 9290011114 (434992)	9290011113 (452615) 9290011113 (434984)	9290011111 (453431)	
Leviton	6602	Professional Channel	1-20			1-8			1-15			1-8
Leviton	6631											
Leviton	6633		1-20			1-8			1-8			1-8
Leviton	6672		1-20			1-8			1-15			1-8
Leviton	6674		1-20			1-8			1-15	1-7		1-8
Leviton	6615P		1-10			1-5			1-12	1-6		1-4
Leviton	DSE06											
Leviton	DSL06		1-20			1-8			1-15	1-7		1-8
Leviton	DSM10											
Leviton	IPI06		1-20			1-8			1-15	1-7		1-8
Leviton	IPL06											
Leviton	VPI06											
Lutron	AYCL-153P											
Lutron	CTCL-153P											
Lutron	CTCL-153PDH											
Lutron	DV-600P		1-20			1-8			1-15	1-7		1-8
Lutron	DV-600PR											
Lutron	DVCL-153P											
Lutron	DVCL-253P											
Lutron	DVELV-300P		1-10			1-5			1-12	1-6		1-4
Lutron	DVRP-253P											
Lutron	LGCL-153P											
Lutron	MACL-153M		1-20			1-8			NR	1-7		1-8
Lutron	MAELV-600											
Lutron	MALV-600											
Lutron	MRF2-6ND-120		NR			1-8			1-15	1-7		1-8
Lutron	NTCL-250											
Lutron	PD-5NE											
Lutron	PD-6WCL		NR			1-8			1-11			
Lutron	RRD-3LD											
Lutron	RRD-6NA		1-20			1-8			1-15	1-7		1-8
Lutron	S-600P											
Lutron	SCL-153P											
Lutron	SCL-153PR											
Lutron	SELV-300P											
Lutron	SLV-600P		1-20			NR			1-15	1-7		1-8
Lutron	TGCL-153PH											
Eaton	RI061-VW-K2											
Eaton	DAL06P											
Legrand	HCL453P											
Sensors												
Lutron	MSCL-OP153M		1-20			1-8			NR	1-7		1-8
Lutron	MSCL-OP153MH		1-20			1-8			1-15			
Lutron	MS-OPS2H		1-20			1-4			1-15			
Panel Modules												
Lutron	GP (Harrier) Card		1-20									
Lutron	HW-RPM-4A-120		1-20									
Lutron	HW-RPM-4U-120		1-20									
Lutron	LP-RPM-4U-120		1-20									

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

BR lamps

Number of bulbs

									
			7.2BR30/MAS/922-27/P/E26/WG 6/1FB	8.8BR30/CNG/8xx/FR/P/E26/ DIM/120V 6/1CT	13.3BR40/PER/9xx/P/E26/DIM 6/1CT T20	13.3BR40/PER/927-22/P/E26/WG 6/1CT T20	P0027894 BR40 T20	15BR30/PER/927/P/E26/WG/HO/T20 4/1PF	
Dimmer Company	Model No.		9790020069 9290018703 (457044)	9290036201 (583617) 9290036200 (583609) 9290036199 (583591) 9290036198 (583583)	9290034775 (577882) 9290034774 (577874) 9290034773 (577866) 9290034772 (577858)	9290034771 (577841)	9290023515 (558056) 9290023512 (558049)	9290023514 (571471)	
Leviton	6602	Professional Channel	1-20	1-17	2-11	1-11	1-8	1-10	
Leviton	6631		1-20	1-17	1-11	1-11	1-8	1-10	
Leviton	6633		1-20	1-17	1-11	1-11	1-8	1-10	
Leviton	6672		1-20	1-17	1-11	1-11	1-8	1-10	
Leviton	6674		2-20	2-17	1-11	1-11	1-8	1-10	
Leviton	6615P		1-10	NR	2-6	2-6	1-4	1-5	
Leviton	DSE06		1-20	1-17	1-20	1-20		1-20	
Leviton	DSL06		2-20	2-17	1-20	1-20	1-16	1-20	
Leviton	DSM10		1-20	1-17	1-20	1-20		1-20	
Leviton	IPI06		1-20	1-17	1-11	1-11	1-8	1-10	
Leviton	IPL06		2-20	2-17	1-11	1-11	1-8	1-10	
Leviton	VPI06		1-20	1-17	1-11	1-11		1-10	
Lutron	AYCL-153P		1-20	1-17	1-11	1-11		1-10	
Lutron	CTCL-153P		1-20	1-17	1-11	1-11		1-10	
Lutron	CTCL-153PDH		NR	NR	NR	NR		NR	
Lutron	DV-600P		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	DV-600PR		1-20	1-17	1-11	1-11		1-10	
Lutron	DVCL-153P		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	DVCL-253P		1-20	1-17	1-19	1-19		1-17	
Lutron	DVELV-300P		1-10	1-9	1-6	1-6	1-4	1-5	
Lutron	DVRP-253P		1-20	1-17	1-19	1-19		1-17	
Lutron	LGCL-153P		1-20	1-17	1-11	1-11		1-10	
Lutron	MACL-153M		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	MAELV-600		1-20	1-17	1-20	1-20		1-20	
Lutron	MALV-600		NR	NR	1	1		1-10	
Lutron	MRF2-6ND-120		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	NTCL-250		1-20	1-17	1-19	1-19		1-17	
Lutron	PD-5NE		1-20	1-17	1-19	1-19		1-17	
Lutron	PD-6WCL		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	RRD-3LD		1-10	1-9	1-6	1-6		1-5	
Lutron	RRD-6NA		1-20	1-17	1-11	1-11		1-10	
Lutron	S-600P		1-20	1-17	1-11	1-11		1-10	
Lutron	SCL-153P		1-5	1-4	1-3	1-3		1-3	
Lutron	SCL-153PR		1-5	1-4	1-3	1-3		1-3	
Lutron	SELV-300P		1-10	1-9	1-6	1-6		1-5	
Lutron	SLV-600P		1-16	1-13	1-8	1-8	1-6	1-8	
Lutron	TGCL-153PH		1-20	1-17	1-11	1-11		1-10	
Cooper	RI061-VW-K2		1-20	1-17	1-11	1-11		1-10	
Eaton	DAL06P		1-20	1-17	1-20	1-20		1-20	
Legrand	HCL453P		1-20	1-17	1-20	1-20		1-20	
Sensors									
Lutron	MSCL-OP153M		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	MSCL-OP153MH		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	MS-OPS2H		1-20	1-17	1-11	1-11		1-10	
Panel Modules									
Lutron	GP (Harrier) Card		NR	NR	NR	NR		1-20	
Lutron	HW-RPM-4A-120		1-20	1-17	1-20	1-20		1-20	
Lutron	HW-RPM-4U-120		1-20	1-17	1-20	1-20		1-20	
Lutron	LP-RPM-4U-120		1-20	1-17	1-20	1-20		1-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

BR lamps

Number of bulbs

BR lamps Number of bulbs								
			15BR30/PER/950/P/E26/D/HO/T20 4/IPF	BR40, P0025038, 2019Q2	7.2BR30/COR/9xx/P/E26/DIM 6/1FB T20	5R20/PER/950/P/E26/DIM 6/1FB T20	P0025038 BR40	5R20/PER/927/P/E26/DIM 6/1FB T20
Dimmer Company	Model No.		9290023513 (571463)	9290022042 (548115) 9290020356 (547430) 9290020355 (547422)	9290022041 (548107) 9290020923 (553891) 9290020322 (545913) 9290020321 (545905)	9290022040 (548123)	9290020924 (553909)	9290020922 (553883)
Leviton	6602	Professional Channel	1-10	1-18	1-20	1-20	1-18	1-20
Leviton	6631		1-10		1-20	1-20		1-20
Leviton	6633		1-10	1-18	1-20	1-20	1-18	1-20
Leviton	6672		1-10	1-18	1-20	1-20	1-18	1-20
Leviton	6674		1-10		2-20	2-20		2-20
Leviton	6615P		1-5	1-9	1-10	1-15	1-9	1-15
Leviton	DSE06		1-20		1-20	1-20		1-20
Leviton	DSL06		1-20		2-20	2-20		2-20
Leviton	DSM10		1-20		1-20	1-20		1-20
Leviton	IPI06		1-10	1-18	1-20	1-20	1-18	1-20
Leviton	IPL06		1-10		2-20	2-20		2-20
Leviton	VPI06		1-10		1-20	1-20		1-20
Lutron	AYCL-153P		1-10		1-20	1-20		1-20
Lutron	CTCL-153P		1-10		1-20	1-20		1-20
Lutron	CTCL-153PDH		NR		NR	NR		NR
Lutron	DV-600P		1-10	1-18	1-20	1-20	1-18	1-20
Lutron	DV-600PR		1-10		1-20	1-20		1-20
Lutron	DVCL-153P		1-10		1-20	1-20		1-20
Lutron	DVCL-253P		1-17		1-20	1-20		1-20
Lutron	DVELV-300P		1-5	1-9	1-10	1-15	1-9	1-15
Lutron	DVRP-253P		1-17		1-20	1-20		1-20
Lutron	LGCL-153P		1-10		1-20	1-20		1-20
Lutron	MACL-153M		1-10	1-18	1-20	1-20	1-18	1-20
Lutron	MAELV-600		1-20		1-20	1-20		1-20
Lutron	MALV-600		1-10		NR	NR		NR
Lutron	MRF2-6ND-120		1-10	1-18	1-20	1-20	1-18	1-20
Lutron	NTCL-250		1-17		1-20	1-20		1-20
Lutron	PD-5NE		1-17		1-20	1-20		1-20
Lutron	PD-6WCL		1-10	1-18	1-20	1-20	1-18	1-20
Lutron	RRD-3LD		1-5		1-10	1-15		1-15
Lutron	RRD-6NA		1-10		1-20	1-20		1-20
Lutron	S-600P		1-10		1-20	1-20		1-20
Lutron	SCL-153P		1-3		1-5	1-8		1-8
Lutron	SCL-153PR		1-3		1-5	1-8		1-8
Lutron	SELV-300P		1-5		1-10	1-15		1-15
Lutron	SLV-600P		1-8	1-13	1-16	1-20	1-13	1-20
Lutron	TGCL-153PH		1-10		1-20	1-20		1-20
Cooper	RI061-VW-K2		1-10		1-20	1-20		1-20
Eaton	DAL06P		1-20		1-20	1-20		1-20
Legrand	HCL453P		1-20		1-20	1-20		1-20
Sensors								
Lutron	MSCL-OP153M		1-10	1-18	1-20	1-20	1-18	1-20
Lutron	MSCL-OP153MH		1-10		1-20	1-20		1-20
Lutron	MS-OPS2H		1-10		1-20	1-20		1-20
Panel Modules								
Lutron	GP (Harrier) Card		1-20		NR	NR		NR
Lutron	HW-RPM-4A-120		1-20		1-20	1-20		1-20
Lutron	HW-RPM-4U-120		1-20		1-20	1-20		1-20
Lutron	LP-RPM-4U-120		1-20		1-20	1-20		1-20

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

BR lamps

Number of bulbs

BR lamps									
Number of bulbs			BR20, P0025038, 2019Q2	8.8w BR40 WG & CG, P0020365, 2018Q4	5R20/MAS/927-22/P/E26/WG 6/1FB T20	9W BR30	9W BR30	9W(65Weq) BR40 WG	
Dimmer Company	Model No.		9290020354 (547414) 9290020353 (547406)	9290020092 9290020091 (457010)	9290020090 9290020089 (456979)	9290012137 (461855) 9290011944 (464180)	9290011749 (458109) 9290011749 (460345) 9290011749 (465286) 9290011749 (464198) 9290011749 (462143) 9290011749 (465229)	9290011558 (457010) 9290011558 (457002) 9290011558 (457028)	
Leviton	6602	Professional Channel	1-20	1-18	1-20	NR	1-5	1-16	
Leviton	6631				1-20				
Leviton	6633		1-20	1-18	1-20	NR	1-4	1-16	
Leviton	6672		1-20	1-18	1-20	1-8	1-8	1-16	
Leviton	6674				2-20	1-8	1-8	1-16	
Leviton	6615P		1-16	1-9	1-15	1-8	1-8	1-8	
Leviton	DSE06				1-20				
Leviton	DSL06				2-20				
Leviton	DSM10				1-20				
Leviton	IPI06		1-20	1-18	1-20	1-5	1-5	1-16	
Leviton	IPL06				2-20				
Leviton	VPI06				1-20				
Lutron	AYCL-153P				1-20				
Lutron	CTCL-153P				1-20				
Lutron	CTCL-153PDH				NR				
Lutron	DV-600P		1-20	1-18	1-20	1-8	1-8	1-16	
Lutron	DV-600PR				1-20				
Lutron	DVCL-153P				1-20				
Lutron	DVCL-253P				1-20				
Lutron	DVELV-300P		1-16	1-9	1-15	1-8	1-8	1-8	
Lutron	DVRP-253P				1-20				
Lutron	LGCL-153P				1-20				
Lutron	MACL-153M		1-20	1-18	1-20	1-8	1-8	1-16	
Lutron	MAELV-600				1-20				
Lutron	MALV-600				NR				
Lutron	MRF2-6ND-120		1-20	1-18	1-20	1-8	1-8	1-16	
Lutron	NTCL-250				1-20				
Lutron	PD-5NE				1-20				
Lutron	PD-6WCL		1-20	1-18	1-20	1-8	1-8	1-16	
Lutron	RRD-3LD				1-15				
Lutron	RRD-6NA				1-20	1-8	1-8	1-16	
Lutron	S-600P				1-20				
Lutron	SCL-153P				1-8				
Lutron	SCL-153PR				1-8				
Lutron	SELV-300P				1-15				
Lutron	SLV-600P		1-20	1-13	1-20	1-8	1-8	1-12	
Lutron	TGCL-153PH				1-20				
Cooper	RI061-VW-K2				1-20				
Eaton	DAL06P				1-20				
Legrand	HCL453P				1-20				
Sensors									
Lutron	MSCL-OP153M		1-20	1-18	1-20	1-8	1-8	1-16	
Lutron	MSCL-OP153MH				1-20	1-8	1-8	1-16	
Lutron	MS-OPS2H				1-20	1-8	1-6	1-16	
Panel Modules									
Lutron	GP (Harrier) Card				NR				1-16
Lutron	HW-RPM-4A-120				1-20				1-16
Lutron	HW-RPM-4U-120				1-20				1-16
Lutron	LP-RPM-4U-120				1-20				1-16

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

BR lamps

Number of bulbs

									
			6W(50W Eq) BR20 WG	9W(65W Eq) BR30 WG	9.5W(65W Eq) Slim style BR30	9.5W(65W Eq) BR30 WG	12W BR40 AF	13W BR30 AF Dim Tone	
Dimmer Company	Model No.		9290011557 (456979) 9290011557 (456995) 9290011557 (456987)	9290011555 (457044)	9290011119 (452441) 9290011119 (452466) 9290011119 (452482) 9290011118 (452359)	9290011118 (452383) 9290011118 (452391) 9290011118 (452417)	9290011117 (452243) 9290011117 (452235) 9290011117 (452268) 9290011117 (452284)	9290002580 (451914)	9290002344 (426445)
Leviton	6602	Professional Channel	1-25	1-16					
Leviton	6631								
Leviton	6633		1-25	1-16					
Leviton	6672		1-25	1-16	1-8				
Leviton	6674		1-25	1-16	1-8	1-12	1-10	1-4	
Leviton	6615P		1-12	1-8	1-5	1-7	1-5	1-5	
Leviton	DSE06								
Leviton	DSL06								
Leviton	DSM10								
Leviton	IPI06		1-25	1-16	1-8	1-6	1-10	1--7	
Leviton	IPL06								
Leviton	VPI06								
Lutron	AYCL-153P								
Lutron	CTCL-153P								
Lutron	CTCL-153PDH								
Lutron	DV-600P		1-25	1-16	1-8	1-12	1-10	1-5	
Lutron	DV-600PR								
Lutron	DVCL-153P								
Lutron	DVCL-253P								
Lutron	DVELV-300P		1-12	1-8	1-5	1-7	1-5	1-5	
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M		1-25	1-16	1-8	1-12	1-12	1-11	
Lutron	MAELV-600							1-11	
Lutron	MALV-600								
Lutron	MRF2-6ND-120		1-25	1-16	1-8	1-12	1-10	1-11	
Lutron	NTCL-250								
Lutron	PD-5NE								
Lutron	PD-6WCL		1-15	1-16	1-15	1-15	1-12		
Lutron	RRD-3LD								
Lutron	RRD-6NA		1-25	1-16	1-15	1-12	1-10	1-11	
Lutron	S-600P								
Lutron	SCL-153P						1-12	1-11	
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P		1-15	1-12	1-7	1-7	1-8	1-11	
Lutron	TGCL-153PH								
Cooper	RI061-VW-K2							1-11	
Eaton	DAL06P								
Legrand	HCL453P								
Sensors									
Lutron	MSCL-OP153M		1-25	1-16	1-8	1-12	1-12	1-11	
Lutron	MSCL-OP153MH		1-15	1-16	1-8	1-12	1-12		
Lutron	MS-OPS2H		1-25	1-16	1-8	1-12	1-12		
Panel Modules									
Lutron	GP (Harrier) Card		1-25	1-16	1-26	1-27	1-18		
Lutron	HW-RPM-4A-120		1-25	1-16	1-38	1-38	1-25		
Lutron	HW-RPM-4U-120		1-25	1-16	1-38	1-38	1-25		
Lutron	LP-RPM-4U-120		1-25	1-16	1-38	1-38	1-25		

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

BR lamps

Number of bulbs

BR lamps Number of bulbs				
			13W BR30 AF	8W BR20 AF
Dimmer Company	Model No.		9290002198 (420281)	9290002192 (420331) 9290002192 (423400) 9290002192 (428813)
Leviton	6602	Professional Channel		
Leviton	6631			
Leviton	6633			
Leviton	6672			
Leviton	6674		1-11	1-14
Leviton	6615P		1-5	1-9
Leviton	DSE06			
Leviton	DSL06			
Leviton	DSM10			
Leviton	IPI06		1-11	1-18
Leviton	IPL06			
Leviton	VPI06			
Lutron	AYCL-153P		1-11	
Lutron	CTCL-153P		1-11	
Lutron	CTCL-153PDH			
Lutron	DV-600P		1-11	1-8
Lutron	DV-600PR			
Lutron	DVCL-153P			
Lutron	DVCL-253P		1-11	
Lutron	DVELV-300P		1-5	NR
Lutron	DVRP-253P			
Lutron	LGCL-153P			
Lutron	MACL-153M		1-11	1-18
Lutron	MAELV-600			
Lutron	MALV-600		1-11	
Lutron	MRF2-6ND-120		1-11	1-18
Lutron	NTCL-250		1-11	
Lutron	PD-5NE			
Lutron	PD-6WCL			
Lutron	RRD-3LD			
Lutron	RRD-6NA		1-11	1-18
Lutron	S-600P			
Lutron	SCL-153P		1-11	1-18
Lutron	SCL-153PR			
Lutron	SELV-300P			
Lutron	SLV-600P		1-11	1-8
Lutron	TGCL-153PH			
Cooper	RI061-VW-K2			
Eaton	DAL06P			
Legrand	HCL453P			
Sensors				
Lutron	MSCL-OP153M	1-11	1-18	
Lutron	MSCL-OP153MH		1-18	
Lutron	MS-OPS2H		1-18	
Panel Modules				
Lutron	GP (Harrier) Card			
Lutron	HW-RPM-4A-120			
Lutron	HW-RPM-4U-120			
Lutron	LP-RPM-4U-120			

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles

Number of bulbs

							
		5B11/PER/CR195WG/FR/G/E26/WGD T20	3.5B11/PER/UD/CL/G/E26/WGD 6/3PF T20	5B11/PER/UD/CL/G/E12/WGD 4/3CT T20	5BA11/PER/CR195WG/FR/G/E26-E12/WGD 1CT T20	3.5BA11/PER/UD50/CL/G/E26-E12/D 6/3PF T20	2.3BA11/PER/UD/CL/G/E12/WGD 6/3PFT20
Dimmer Company	Model No.	9290030949 (575175)	9290030899 (574392)	9290030855 (573378)	9290030825 (575191) 9290030824 (575183) 9290029908 (575167)	9290029919 (564948) 9290029916 (564930)	9290029918 (566653)
Leviton	6602		1-10	1-10	1-10	1-10	1-10
Leviton	6631	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	6633	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	6672	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	6674	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	6615P	NR	NR	NR	NR	NR	NR
Leviton	DSE06		1-10	1-10	1-10	1-10	1-10
Leviton	DSL06	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	DSM10		1-10	1-10	1-10	1-10	1-10
Leviton	IPI06	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	IPL06	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	VPI06		1-10	1-10	1-10	1-10	1-10
Lutron	AYCL-153P		1-11	1-11	1-11	1-11	1-11
Lutron	CTCL-153P		1-10	1-10	1-10	1-10	1-10
Lutron	CTCL-153PDH		1-10	1-10	1-10	1-10	1-10
Lutron	DV-600P		1-10	1-10	1-10	1-10	1-10
Lutron	DV-600PR		1-10	1-10	1-10	1-10	1-10
Lutron	DVCL-153P	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	DVCL-253P		1-20	1-20	1-20	1-20	1-20
Lutron	DVELV-300P		NR	NR	NR	NR	NR
Lutron	DVRP-253P		1-20	1-20	1-20	1-20	1-20
Lutron	LGCL-153P		1-10	1-10	1-10	1-10	1-10
Lutron	MACL-153M	1-9	1-10	1-10	1-10	1-10	1-10
Lutron	MAELV-600		1-10	1-10	1-10	1-10	1-10
Lutron	MALV-600		NR	NR	NR	NR	NR
Lutron	MRF2-6ND-120		1-10	1-10	1-10	1-10	1-10
Lutron	NTCL-250		1-20	1-20	1-20	1-20	1-20
Lutron	PD-5NE		1-10	1-10	1-10	1-10	1-10
Lutron	PD-6WCL	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	RRD-3LD		1-10	1-10	1-10	1-10	1-10
Lutron	RRD-6NA	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	S-600P		1-10	1-10	1-10	1-10	1-10
Lutron	SCL-153P		1-11	1-8	1-8	1-11	1-11
Lutron	SCL-153PR		1-11	1-8	1-8	1-11	1-11
Lutron	SELV-300P		1-10	1-10	1-10	1-10	1-10
Lutron	SLV-600P	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	TGCL-153PH		1-10	1-10	1-10	1-10	1-10
Cooper	RI061-VW-K2		1-10	1-10	1-10	1-10	1-10
Eaton	DAL06P		1-10	1-10	1-10	1-10	1-10
Legrand	HCL453P		1-10	1-10	1-10	1-10	1-10
Sensors							
Lutron	MSCL-OP153M	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	MSCL-OP153MH	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	MS-OPS2H		1-10	1-10	1-10	1-10	1-10
Panel Modules							
Lutron	GP (Harrier) Card		NR	NR	NR	NR	NR
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-20	1-20
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-20	1-20
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-20	1-20

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Candles

Number of bulbs

									
			3.5BA11/PER/UD/CL/G/E26/WGD T20	5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	5BA11/PER/UD/CL/G/E26-E12/WGD 6/3PF T20	3.5B11/VIN/820/E12/Amber/G/SP D 4/2PF T20	6.6BA11/PER/UD/CL/G/E12+E26/WGD 2PF T20	6.6BA11 WG E12/E26 T20	
Dimmer Company	Model No.		9290029917 (566679)	9290029915 (564922)	9290029911 (566695) 9290029910 (566687)	9290029887 (565804)	9290029866 (564492)	9290022957 (557470) 9290022956 (557462)	
Leviton	6602	Professional Channel	1-10	1-10	1-10	1-10	1-10		
Leviton	6631		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	6633		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	6672		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	6674		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	6615P		NR	NR	NR	NR	NR		
Leviton	DSE06		1-10	1-10	1-10	1-10	1-10		
Leviton	DSL06		1-10	1-10	1-10	1-10	1-10	1-30	
Leviton	DSM10		1-10	1-10	1-10	1-10	1-10		
Leviton	IPI06		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	IPL06		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	VPI06		1-10	1-10	1-10	1-10	1-10		
Lutron	AYCL-153P		1-11	1-11	1-11	1-11	1-11		
Lutron	CTCL-153P		1-10	1-10	1-10	1-10	1-10		
Lutron	CTCL-153PDH		1-10	1-10	1-10	1-10	1-10		
Lutron	DV-600P		1-10	1-10	1-10	1-10	1-10		
Lutron	DV-600PR		1-10	1-10	1-10	1-10	1-10		
Lutron	DVCL-153P		1-10	1-10	1-10	1-10	1-10	1-23	
Lutron	DVCL-253P		1-20	1-20	1-20	1-20	1-20		
Lutron	DVELV-300P		NR	NR	NR	NR	NR	1-11	
Lutron	DVRP-253P		1-20	1-20	1-20	1-20	1-20		
Lutron	LGCL-153P		1-10	1-10	1-10	1-10	1-10		
Lutron	MACL-153M		1-10	1-10	1-10	1-10	1-10	1-23	
Lutron	MAELV-600		1-10	1-10	1-10	1-10	1-10		
Lutron	MALV-600		NR	NR	NR	NR	NR		
Lutron	MRF2-6ND-120		1-10	1-10	1-10	1-10	1-10		
Lutron	NTCL-250		1-20	1-20	1-20	1-20	1-20		
Lutron	PD-5NE		1-10	1-10	1-10	1-10	1-10		
Lutron	PD-6WCL		1-10	1-10	1-10	1-10	1-10	1-23	
Lutron	RRD-3LD		1-10	1-10	1-10	1-10	1-10		
Lutron	RRD-6NA		1-10	1-10	1-10	1-10	1-10		
Lutron	S-600P		1-10	1-10	1-10	1-10	1-10		
Lutron	SCL-153P		1-11	1-8	1-8	1-11	1-8		
Lutron	SCL-153PR		1-11	1-8	1-8	1-11	1-8		
Lutron	SELV-300P		1-10	1-10	1-10	1-10	1-10		
Lutron	SLV-600P		1-10	1-10	1-10	1-10	1-10	1-17	
Lutron	TGCL-153PH		1-10	1-10	1-10	1-10	1-10		
Cooper	RI061-VW-K2		1-10	1-10	1-10	1-10	1-10		
Eaton	DAL06P		1-10	1-10	1-10	1-10	1-10		
Legrand	HCL453P		1-10	1-10	1-10	1-10	1-10		
Sensors									
Lutron	MSCL-OP153M		1-10	1-10	1-10	1-10	1-10	1-23	
Lutron	MSCL-OP153MH		1-10	1-10	1-10	1-10	1-10	1-23	
Lutron	MS-OPS2H		1-10	1-10	1-10	1-10	1-10		
Panel Modules									
Lutron	GP (Harrier) Card		NR	NR	NR	NR	NR		
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-20	1-20		
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-20	1-20		
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-20	1-20		

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles

Number of bulbs

							
		3.3w Dimmable B11 Filament T20, P0025721	4.5w (40w Eq) WG BA11 Filament T20, P0023793	2w (25 Eq) WG BA11 Filament T20, P0023793	5.5B11/PER/927-922/CL/G/E12/WGX T20	3.3B11/PER/927-922/CL/G/E26/WGX T20	3BA11/MOD/840/E12/CL/GL/DIM 8/1BC
Dimmer Company	Model No.	9290022602 (556555) 9290022073 (549436) 9290022077 (549477) 9290022062 (549170) 9290022076 (549469) 9290022058 (549139) 9290022075 (549451) 9290022057 (549121) 9290022074 (549444) 9290022083 (549386) 9290022050 (549279) 9290022081 (549378) 9290020513 (550250) 9290022054 (549311) 9290019701 (549576) 9290022051 (549287) 9290019693 (549550) 9290022049 (549261) 9290022048 (549253) 9290022045 (549337) 9290022046 (549345) 9290020472 (549584) 9290019694 (549568) 9290020012 (543173)					
Leviton	6602	1-3	2	2-20	1-10	1-10	3-15
Leviton	6631				1-10	1-10	
Leviton	6633	1-5	1-10	2-15	1-10	1-10	2-15
Leviton	6672	1-5	1-5	8-20	1-10	1-10	1-15
Leviton	6674				1-10	1-10	1-15
Leviton	6615P	1-2	1-10	1-10	NR	NR	1-15
Leviton	DSE06				1-10	1-10	
Leviton	DSL06				1-10	1-10	
Leviton	DSM10				1-10	1-10	
Leviton	IPI06	1-5	2-3	1-20	1-10	1-10	1-15
Leviton	IPL06	1-20			1-10	1-10	
Leviton	VPI06				1-10	1-10	
Lutron	AYCL-153P				1-11	1-11	
Lutron	CTCL-153P				1-10	1-10	
Lutron	CTCL-153PDH				1-10	1-10	
Lutron	DV-600P	1-5	1-5	1-20	1-10	1-10	1-15
Lutron	DV-600PR				1-10	1-10	
Lutron	DVCL-153P				1-10	1-10	
Lutron	DVCL-253P				1-20	1-20	
Lutron	DVELV-300P	1-20	1-10	1-20	NR	NR	1-15
Lutron	DVRP-253P				1-20	1-20	
Lutron	LGCL-153P				1-10	1-10	
Lutron	MACL-153M	1-5	1-10	1-20	1-10	1-10	
Lutron	MAELV-600				1-10	1-10	
Lutron	MALV-600				NR	NR	
Lutron	MRF2-6ND-120	3-5	2-10	2-20	1-10	1-10	1-15
Lutron	NTCL-250				1-20	1-20	
Lutron	PD-5NE				1-10	1-10	
Lutron	PD-6WCL	1-5	1-10	2-20	1-10	1-10	2-15
Lutron	RRD-3LD				1-10	1-10	
Lutron	RRD-6NA	1-3	1-10	1-20	1-10	1-10	
Lutron	S-600P				1-10	1-10	
Lutron	SCL-153P				1-8	1-11	
Lutron	SCL-153PR				1-8	1-11	
Lutron	SELV-300P				1-10	1-10	
Lutron	SLV-600P	1-10	1-10	1-20	1-10	1-10	1-15
Lutron	TGCL-153PH				1-10	1-10	
Cooper	RI061-VW-K2				1-10	1-10	
Eaton	DAL06P				1-10	1-10	
Legrand	HCL453P				1-10	1-10	
Sensors							
Lutron	MSCL-OP153M	1-5	1-10	1-20	1-10	1-10	
Lutron	MSCL-OP153MH	1-8	1-10	1-20	1-10	1-10	1-15
Lutron	MS-OPS2H	1-20	1-10	1-20	1-10	1-10	1-15
Panel Modules							
Lutron	GP (Harrier) Card	1-20	1-10	1-20	NR	NR	1-15
Lutron	HW-RPM-4A-120	1-5	1-10	1	1-20	1-20	1-15
Lutron	HW-RPM-4U-120	1-5	1-10	1	1-20	1-20	1-15
Lutron	LP-RPM-4U-120	1-5	1-10	1	1-20	1-20	1-15

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles

Number of bulbs

Candles									
Number of bulbs			3.3BA11/PER/927-922/CL/G/E12/WGX T20	3.8w(40w Eq) WG Candle, P0020414, P0023247	2.5-8w Dimmable Candle and Vintage	5.5w BA11/G16.5 Candle	4.5W (40W Eq) 2700K	4.5W(40W Eq) 5000K	
Dimmer Company	Model No.		9290019692 (549543)	9290019514 (537621) 9290019514 (556852)	9290018427 (478719) 9290013151 (470781) 9290018426 (478701) 9290013149 (470765) 9290018425 (478693) 9290013148 (470757) 9290018424 (478685) 9290012687 (465567) 9290018423 (478677) 9290012687 (465583)	9290018418 (478842) 9290018415 (478818) 9290018417 (478834) 9290018414 (478800) 9290018416 (478826) 9290018413 (478792)	9290012138 (461921) 9290012137 (461871) 9290012138 (461939) 9290012137 (461889) 9290012138 (462358) 9290012137 (461897) 9290012137 (461855) 9290012137 (461905) 9290012137 (461863)	9290012130 (463901) 9290012130 (463919) 9290012130 (463943)	
Leviton	6602	Professional Channel	1-10	3-20	3-20	1-5	2-30	2-30	
Leviton	6631		1-10						
Leviton	6633		1-10	2-20	2-20	1-10	2-30	2-30	
Leviton	6672		1-10	1-20	1-20	1-10	2-30	2-30	
Leviton	6674		1-10				2-30	2-30	
Leviton	6615P		NR	1-20	1-20	1-5	2-16	2-16	
Leviton	DSE06		1-10						
Leviton	DSL06		1-10						
Leviton	DSM10		1-10						
Leviton	IPI06		1-10	4-20	4-20	1-10	2-30	2-30	
Leviton	IPL06		1-10						
Leviton	VPI06		1-10						
Lutron	AYCL-153P		1-11						
Lutron	CTCL-153P		1-10						
Lutron	CTCL-153PDH		1-10						
Lutron	DV-600P		1-10	1-20	1-20	1-10	2-30	2-30	
Lutron	DV-600PR		1-10						
Lutron	DVCL-153P		1-10						
Lutron	DVCL-253P		1-20						
Lutron	DVELV-300P		NR	1-20	1-20	1-3	2-16	2-16	
Lutron	DVRP-253P		1-20						
Lutron	LGCL-153P		1-10						
Lutron	MACL-153M		1-10	1-20	1-20	1-10	2-30	2-30	
Lutron	MAELV-600		1-10						
Lutron	MALV-600		NR						
Lutron	MRF2-6ND-120		1-10	1-10	1-10	1-10	2-30	2-30	
Lutron	NTCL-250		1-20						
Lutron	PD-5NE		1-10						
Lutron	PD-6WCL		1-10	3-20	3-20	1-10	2-30	NR	
Lutron	RRD-3LD		1-10						
Lutron	RRD-6NA		1-10	1-20	1-20	1-10	2-30	2-30	
Lutron	S-600P		1-10						
Lutron	SCL-153P		1-11						
Lutron	SCL-153PR		1-11						
Lutron	SELV-300P		1-10						
Lutron	SLV-600P		1-10	1-20	1-20	1-10	2-30	2-30	
Lutron	TGCL-153PH		1-10						
Cooper	RI061-VW-K2		1-10						
Eaton	DAL06P		1-10						
Legrand	HCL453P		1-10						
Sensors									
Lutron	MSCL-OP153M		1-10	1-20	1-20	1-10	2-30	2-30	
Lutron	MSCL-OP153MH		1-10	1-20	1-20	1-10	2-30	NR	
Lutron	MS-OPS2H		1-10	1-20	1-20	1-10	2-30	2-30	
Panel Modules									
Lutron	GP (Harrier) Card		NR	1-20	1-20	1-8	2-30	2-30	
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-10	2-30	2-30	
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-10	2-30	2-30	
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-10	2-30	2-30	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles

Number of bulbs

									
			3.5W Filament	7W(60W Eq) DS WG	4.5W(40Eq) DS WG	3.5W (25W Eq) WG DS	2.5W(25W Eq) DS	6.5W(60W Eq) DS	
Dimmer Company	Model No.		9290012103 (461681)	9290011821 (458679) 9290011820 (458687) 9290011821 (458661) 9290011820 (459321) 9290011821 (458653) 9290011820 (458703) 9290011820 (458695)	9290011673 (457200) 9290011671 (457218) 9290011673 (457192) 9290011670 (457119) 9290011673 (457184)	9290011668 (457242) 9290011668 (457234) 9290011668 (457226)	9290011151 (451831) 9290002799 (435149)	9290011121 (452813)	
Leviton	6602	Professional Channel	1-33	1-21	1-26	1-15	NR	NR	
Leviton	6631								
Leviton	6633		1-33	1-21	1-26	1-25	1-7	1-10	
Leviton	6672		1-33	1-21	1-26	1-35	1-7	1-10	
Leviton	6674		1-10	1-21	1-10	1-20	1-7	1-10	
Leviton	6615P		1-17	1-11	1-13	1-17	NR	NR	
Leviton	DSE06								
Leviton	DSL06								
Leviton	DSM10								
Leviton	IPI06		1-33	1-21	1-26	1-35	NR	NR	
Leviton	IPL06								
Leviton	VPI06								
Lutron	AYCL-153P								
Lutron	CTCL-153P								
Lutron	CTCL-153PDH								
Lutron	DV-600P		1-33	1-21	1-26	1-15	1-7	1-10	
Lutron	DV-600PR								
Lutron	DVCL-153P								
Lutron	DVCL-253P								
Lutron	DVELV-300P		1-17	1-11	1-13	1-17	1-7	NR	
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M		1-33	1-21	1-26	1-35	1-7	1-10	
Lutron	MAELV-600								
Lutron	MALV-600								
Lutron	MRF2-6ND-120		1-33	1-21	1-26	1-35	1-7	1-10	
Lutron	NTCL-250								
Lutron	PD-5NE								
Lutron	PD-6WCL		NR	NR	NR	1-35	1-7	1-10	
Lutron	RRD-3LD								
Lutron	RRD-6NA		1-15	1-25	NR	1-35	1-7	1-10	
Lutron	S-600P								
Lutron	SCL-153P								
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P		1-25	1-16	1-19	1-15	1-7	1-10	
Lutron	TGCL-153PH								
Cooper	RI061-VW-K2								
Eaton	DAL06P								
Legrand	HCL453P								
Sensors									
Lutron	MSCL-OP153M		1-33	1-21	1-26	1-35	1-7	1-10	
Lutron	MSCL-OP153MH		1-33	NR	1-33	2-45			
Lutron	MS-OPS2H		1-33	1-21	1-33	1-45			
Panel Modules									
Lutron	GP (Harrier) Card		1-33	1-25	1-40	1-50		1-10	
Lutron	HW-RPM-4A-120		1-33	1-25	1-45	1-50		1-10	
Lutron	HW-RPM-4U-120		1-33	1-25	1-45	1-50		1-10	
Lutron	LP-RPM-4U-120		1-33	1-25	1-45	1-50		1-10	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Candles

Number of bulbs

			
		4.5W(40W Eq) DS	3.5W DW
Dimmer Company	Model No.	9290002889 (435156) 9290002798 (435164) 9290002797 (435172)	9290002419 (427773) 9290002417 (427765) 9290002419 (427815) 9290002417 (427799) 9290002418 (427781)
Leviton	6602	NR	
Leviton	6631		
Leviton	6633	1-10	
Leviton	6672	1-10	
Leviton	6674	1-10	1-10
Leviton	6615P	NR	1-17
Leviton	DSE06		
Leviton	DSL06		
Leviton	DSM10		
Leviton	IPI06	NR	NR
Leviton	IPL06		
Leviton	VPI06		
Lutron	AYCL-153P		
Lutron	CTCL-153P		
Lutron	CTCL-153PDH		
Lutron	DV-600P	NR	NR
Lutron	DV-600PR		
Lutron	DVCL-153P		
Lutron	DVCL-253P		
Lutron	DVELV-300P	NR	10--21
Lutron	DVRP-253P		
Lutron	LGCL-153P		
Lutron	MACL-153M	1-10	1-42
Lutron	MAELV-600		
Lutron	MALV-600		
Lutron	MRF2-6ND-120	1-10	1-42
Lutron	NTCL-250		
Lutron	PD-5NE		
Lutron	PD-6WCL	1-10	
Lutron	RRD-3LD		
Lutron	RRD-6NA	1-10	1-42
Lutron	S-600P		
Lutron	SCL-153P		4-42
Lutron	SCL-153PR		
Lutron	SELV-300P		
Lutron	SLV-600P	1-10	NR
Lutron	TGCL-153PH		
Cooper	RI061-VW-K2		
Eaton	DAL06P		
Legrand	HCL453P		
Sensors			
Lutron	MSCL-OP153M	1-10	1-42
Lutron	MSCL-OP153MH		
Lutron	MS-OPS2H		
Panel Modules			
Lutron	GP (Harrier) Card		
Lutron	HW-RPM-4A-120		
Lutron	HW-RPM-4U-120		
Lutron	LP-RPM-4U-120		

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow **AF** = Air Flux **DS** = Diamond Spark **CC** = Clear Classic **DC** = Die Cast **DW** = Direct White **SO** = Single Optic

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs									
			5G25/PER/UD50/E26/FR/G/D 4/ 2PFT20	3.5G16.5/PER/UD/CL/G/E26/ WGD T20	3.5G25/PER/UD/FR-CL/G/E26/ WGD T20	3.5G25/PER/UD50/CL/G/E26/ D 4/2PFT20	5G25/PER/UD50/CL/G/E26 D 4/ 3PFT20	6.5G25/VIN/820/E26/Amber/G/ SP D 4/1PFT20	
Dimmer Company	Model No.		9290030998 (575217)	9290030852 (573303) 9290030851 (573295)	9290030850 (573352) 9290030848 (573345)	9290030849 (573337)	9290029914 (564914)	9290029895 (565887)	
Leviton	6602	Professional Channel	1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	6631		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	6633		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	6672		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	6674		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	6615P		NR	NR	NR	NR	NR	NR	
Leviton	DSE06		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	DSL06		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	DSM10		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	IPI06		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	IPL06		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	VPI06		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	AYCL-153P		1-11	1-11	1-11	1-11	1-11	1-11	
Lutron	CTCL-153P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	CTCL-153PDH		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	DV-600P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	DV-600PR		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	DVCL-153P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	DVCL-253P		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	DVELV-300P		NR	NR	NR	NR	NR	NR	
Lutron	DVRP-253P		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	LGCL-153P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	MACL-153M		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	MAELV-600		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	MALV-600		NR	NR	NR	NR	NR	NR	
Lutron	MRF2-6ND-120		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	NTCL-250		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	PD-5NE		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	PD-6WCL		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	RRD-3LD		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	RRD-6NA		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	S-600P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	SCL-153P		1-8	1-11	1-11	1-11	1-8	1-8	
Lutron	SCL-153PR		1-8	1-11	1-11	1-11	1-8	1-8	
Lutron	SELV-300P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	SLV-600P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	TGCL-153PH		1-10	1-10	1-10	1-10	1-10	1-10	
Cooper	RI061-VW-K2		1-10	1-10	1-10	1-10	1-10	1-10	
Eaton	DAL06P		1-10	1-10	1-10	1-10	1-10	1-10	
Legrand	HCL453P		1-10	1-10	1-10	1-10	1-10	1-10	
Sensors									
Lutron	MSCL-OP153M		1-10	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	MSCL-OP153MH		1-10	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	MS-OPS2H		1-10	1-10	1-10	1-10	1-10	1-10	1-10
Panel Modules									
Lutron	GP (Harrier) Card		NR	NR	NR	NR	NR	NR	NR
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs									
			5.5ST19/VIN/9xx/E26/CL/G/SP D 4/ 1PF T20	5.5A19/VIN/9xx/E26/CL/G/ SP DIM 1PF T20	3.5T10/VIN/820/E26/Amber/G/ SP D 4/1PFT20	3.5A15/VIN/820/E26/Amber/G/ SP D 4/1PFT20	6.5ST19/VIN/820/E26/Amber/G/ SP/D 1PFT20	8.8ST19/PER/950/CL/G/E26/ DIM 1PF T20	
Dimmer Company	Model No.		9290029890 (565838) 9290029888 (565812)	9290029885 (565788)	9290029874 (565671)	9290029872 (565655)	9290029869 (565622)	9290022961 (556548)	
Leviton	6602	Professional Channel	1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	6631		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	6633		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	6672		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	6674		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	6615P		NR	NR	NR	NR	NR	NR	
Leviton	DSE06		1-10	1-10	1-10	1-10	1-10	1-20	
Leviton	DSL06		1-10	1-10	1-10	1-10	1-10	1-20	
Leviton	DSM10		1-10	1-10	1-10	1-10	1-10	1-20	
Leviton	IPI06		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	IPL06		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	VPI06		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	AYCL-153P		1-11	1-11	1-11	1-11	1-11	1-19	
Lutron	CTCL-153P		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	CTCL-153PDH		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	DV-600P		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	DV-600PR		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	DVCL-153P		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	DVCL-253P		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	DVELV-300P		NR	NR	NR	NR	NR	NR	
Lutron	DVRP-253P		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	LGCL-153P		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	MACL-153M		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	MAELV-600		1-10	1-10	1-10	1-10	1-10	1-20	
Lutron	MALV-600		NR	NR	NR	NR	NR	NR	
Lutron	MRF2-6ND-120		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	NTCL-250		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	PD-5NE		1-10	1-10	1-10	1-10	1-10	1-20	
Lutron	PD-6WCL		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	RRD-3LD		1-10	1-10	1-10	1-10	1-10	1-9	
Lutron	RRD-6NA		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	S-600P		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	SCL-153P		1-11	1-11	1-11	1-11	1-8	1-5	
Lutron	SCL-153PR		1-11	1-11	1-11	1-11	1-8	1-5	
Lutron	SELV-300P		1-10	1-10	1-10	1-10	1-10	1-9	
Lutron	SLV-600P		1-10	1-10	1-10	1-10	1-10	1-14	
Lutron	TGCL-153PH		1-10	1-10	1-10	1-10	1-10	1-19	
Cooper	RI061-VW-K2		1-10	1-10	1-10	1-10	1-10	1-19	
Eaton	DAL06P		1-10	1-10	1-10	1-10	1-10	1-20	
Legrand	HCL453P		1-10	1-10	1-10	1-10	1-10	1-20	
Sensors									
Lutron	MSCL-OP153M		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	MSCL-OP153MH		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	MS-OPS2H		1-10	1-10	1-10	1-10	1-10	1-19	
Panel Modules									
Lutron	GP (Harrier) Card		NR	NR	NR	NR	NR	NR	NR
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs									
			8ST19/PER/927-922/CL/G/E26/ WGX T20	8w A15 Filament T20	2.7w WG G25 Filament T20	3.8w Dimmable G25 Filament T20, P0025721	5.5A15/PER/927-922/CL/G/E26/ WGX1FB	4GU10/LED/930/F35/DIM/G/ 120V T20 10/1	
Dimmer Company	Model No.		9290022960 (556530)	9290022093 (548313)	9290022080 (549360) 9290022047 (549352)	9290022070 (549212) 9290022069 (549204) 9290022068 (549196) 9290022067 (549188)	9290020915 (547959) 9290020915 (572669)	9290020555 (468140)	
Leviton	6602	Professional Channel	1-10	1-15	2-20	1-3	1-10	1-20	
Leviton	6631		1-10				1-10	1-20	
Leviton	6633		1-10	1-15	2-15	1-5	1-10	1-20	
Leviton	6672		1-10	1-15	8-20	1-5	1-10	1-20	
Leviton	6674		1-10				1-10	1-20	
Leviton	6615P		NR	1-9	1-10	1-2	NR	1-20	
Leviton	DSE06		1-10				1-10	1-20	
Leviton	DSL06		1-10				1-10	1-20	
Leviton	DSM10		1-10				1-10	1-20	
Leviton	IPI06		1-10	1-15	1-20	1-5	1-10	1-20	
Leviton	IPL06		1-10	1-8			1-10	1-20	
Leviton	VPI06		1-10				1-10	1-20	
Lutron	AYCL-153P		1-11				1-11	1-20	
Lutron	CTCL-153P		1-10				1-10	1-20	
Lutron	CTCL-153PDH		1-10				1-10	NR	
Lutron	DV-600P		1-10	1-15	1-20	1-5	1-10	1-20	
Lutron	DV-600PR		1-10				1-10	1-20	
Lutron	DVCL-153P		1-10				1-10	1-20	
Lutron	DVCL-253P		1-20				1-20	1-20	
Lutron	DVELV-300P		NR	1-9	1-20	1-20	NR	1-20	
Lutron	DVRP-253P		1-20				1-20	1-20	
Lutron	LGCL-153P		1-10				1-10	1-20	
Lutron	MACL-153M		1-10	1-15	1-20	1-5	1-10	1-20	
Lutron	MAELV-600		1-10				1-10	1-20	
Lutron	MALV-600		NR				NR	NR	
Lutron	MRF2-6ND-120		1-10	1-15	2-20	3-5	1-10	1-20	
Lutron	NTCL-250		1-20				1-20	1-20	
Lutron	PD-5NE		1-10				1-10	1-20	
Lutron	PD-6WCL		1-10	1-15	2-20	1-5	1-10	1-20	
Lutron	RRD-3LD		1-10				1-10	1-20	
Lutron	RRD-6NA		1-10	1-15	1-20	1-3	1-10	1-20	
Lutron	S-600P		1-10				1-10	1-20	
Lutron	SCL-153P		1-8				1-8	1-20	
Lutron	SCL-153PR		1-8				1-8	1-9	
Lutron	SELV-300P		1-10				1-10	1-19	
Lutron	SLV-600P		1-10	1-15	1-20	1-10	1-10	1-20	
Lutron	TGCL-153PH		1-10				1-10	1-20	
Cooper	RI061-VW-K2		1-10				1-10	1-20	
Eaton	DAL06P		1-10				1-10	1-20	
Legrand	HCL453P		1-10				1-10	1-20	
Sensors									
Lutron	MSCL-OP153M		1-10	1-15	1-20	1-5	1-10	1-20	
Lutron	MSCL-OP153MH		1-10	2-15	1-20	1-8	1-10	1-20	
Lutron	MS-OPS2H		1-10	1-15	1-20	1-20	1-10	1-20	
Panel Modules									
Lutron	GP (Harrier) Card		NR	1-10	1-20	1-20	NR	1-20	
Lutron	HW-RPM-4A-120		1-20	1-5	1	1-5	1-20	1-20	
Lutron	HW-RPM-4U-120		1-20	1-5	1	1-5	1-20	1-20	
Lutron	LP-RPM-4U-120		1-20	1-5	1	1-5	1-20	1-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X). Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs									
			4GU10/LED/927-22/F35/G/WG/T20 10/1	3G16.5/MOD/840/E12/CL/GL/DIM 4/BC	4T10/MOD/840/E26/CL/GL/DIM 4/1BC	4G25/MOD/840/E26/CL/GL/DIM 4/1BC	3.8w WG G25 Filament T20, P0023793	3.8w(40w Eq) WG Candle, P0020414, P0023247	
Dimmer Company	Model No.		9290020553 (471565)	9290020014 (543157)	9290020009 (543132)	9290020008 (543124)	9290019699 (549527)	9290019515 (537605) 9290019515 (556837) 9290019513 (537597) 9290019513 (556829)	
Leviton	6602	Professional Channel	1-20	3-15	3-15	3-15	2	3-20	
Leviton	6631		1-20						
Leviton	6633		1-20	2-15	2-15	2-15	1-10	2-20	
Leviton	6672		1-20	1-15	1-15	1-15	1-5	1-20	
Leviton	6674		1-20	1-15	1-15	1-15			
Leviton	6615P		1-19	1-15	1-15	1-15	1-10	1-20	
Leviton	DSE06		1-20						
Leviton	DSL06		1-20						
Leviton	DSM10		1-20						
Leviton	IPI06		1-20	1-15	1-15	1-15	2-3	4-20	
Leviton	IPL06		1-20						
Leviton	VPI06		1-20						
Lutron	AYCL-153P		1-20						
Lutron	CTCL-153P		1-20						
Lutron	CTCL-153PDH		1-20						
Lutron	DV-600P		1-20	1-15	1-15	1-15	1-5	1-20	
Lutron	DV-600PR		1-20						
Lutron	DVCL-153P		1-20		1-15	1-15			
Lutron	DVCL-253P		1-20						
Lutron	DVELV-300P		1-20	1-15	1-15	1-15	1-10	1-20	
Lutron	DVRP-253P		1-20						
Lutron	LGCL-153P		1-20						
Lutron	MACL-153M		1-20				1-10	1-20	
Lutron	MAELV-600		1-20						
Lutron	MALV-600		NR						
Lutron	MRF2-6ND-120		1-20	1-15	1-15	1-15	2-10	1-10	
Lutron	NTCL-250		1-20						
Lutron	PD-5NE		NR						
Lutron	PD-6WCL		1-20	2-15	2-15	2-15	1-10	3-20	
Lutron	RRD-3LD		1-19						
Lutron	RRD-6NA		NR				1-10	1-20	
Lutron	S-600P		1-20						
Lutron	SCL-153P		1-20						
Lutron	SCL-153PR		1-9						
Lutron	SELV-300P		1-20						
Lutron	SLV-600P		1-20	1-15	1-15	1-15	1-10	1-20	
Lutron	TGCL-153PH		1-20						
Cooper	RI061-VW-K2		1-20						
Eaton	DAL06P		1-20						
Legrand	HCL453P		1-20						
Sensors									
Lutron	MSCL-OP153M		1-20				1-10	1-20	
Lutron	MSCL-OP153MH		1-20	1-15	1-15	1-15	1-10	1-20	
Lutron	MS-OPS2H		1-20	1-15	1-15	1-15	1-10	1-20	
Panel Modules									
Lutron	GP (Harrier) Card		1-15	1-15	1-15	1-15	1-10	1-20	
Lutron	HW-RPM-4A-120		NR	1-15	1-15	1-15	1-10	1-20	
Lutron	HW-RPM-4U-120		NR	1-15	1-15	1-15	1-10	1-20	
Lutron	LP-RPM-4U-120		NR	1-15	1-15	1-15	1-10	1-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs								
			4.5A19/VIN/820/E26/CL/GL/DIM 4/ FBH T20	7.5T20/modern/840/CL/G/DIM 2/1CT	7.5A50/modern/840/CL/G/DIM 2/1CT	7.5G63/modern/840/CL/G/DIM 2/1CT	7.5T20/VIN/820/CL/G/E26/amber/ SP/DIM 1CT	7.5A50/VIN/820/CL/G/E26/amber/ SP/DIM 1CT
Dimmer Company	Model No.		9290019509 (556795)	9290019368 (536318)	9290019367 (536300)	9290019366 (536292)	9290019365 (575241)	9290019364 (575233)
Leviton	6602	Professional Channel	3-20	1-3	1-3	1-3	1-3	1--3
Leviton	6631							
Leviton	6633		2-20	NR	NR	NR	NR	NR
Leviton	6672		1-20	1-3	1-3	1-3	1-3	1-3
Leviton	6674			1-3	1-3	1-3	1-3	1-3
Leviton	6615P		1-20	1-3	1-3	1-3	1-3	1-3
Leviton	DSE06							
Leviton	DSL06							
Leviton	DSM10							
Leviton	IPI06		4-20	1-3	1-3	1-3	1-3	1-3
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P							
Lutron	CTCL-153P							
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	DV-600PR							
Lutron	DVCL-153P			1-3	1-3	1-3	1-3	1-3
Lutron	DVCL-253P							
Lutron	DVELV-300P		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M		1-20				1-3	1-3
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		1-10	1-3	1-3	1-3	1-3	1-3
Lutron	NTCL-250							
Lutron	PD-5NE							
Lutron	PD-6WCL		3-20	1-3	1-3	1-3	1-3	1-3
Lutron	RRD-3LD							
Lutron	RRD-6NA		1-20				1-3	1-3
Lutron	S-600P							
Lutron	SCL-153P							
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	TGCL-153PH							
Cooper	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M		1-20				1-3	1-3
Lutron	MSCL-OP153MH		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	MS-OPS2H		1-20	1-3	1-3	1-3	1-3	1-3
Panel Modules								
Lutron	GP (Harrier) Card		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	HW-RPM-4A-120		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	HW-RPM-4U-120		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	LP-RPM-4U-120		1-20	1-3	1-3	1-3	1-3	1-3

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs								
			7.5G63/VIN/820/CL/G/E26/amber/SP/DIM 1CT	3-5.5w WG filament	2.5-8w Dimmable Candle and Vintage	4.5w (40w) G16.5 filament dimmable	4.5W(60W Eq) Filament	
Dimmer Company	Model No.		9290019363 (575225)	9290019337 (536950) 9290019326 (536888) 9290019322 (536847) 9290019336 (536746) 9290019325 (536870) 9290019321 (536839) 9290019335 (536938) 9290019324 (536862) 9290019333 (536524) 9290019323 (536854)	9290018438 (478925) 9290018428 (478727) 9290012096 (461111) 9290018433 (478776) 9290013357 (475848) 9290018430 (478743) 9290013356 (475830) 9290018429 (478735) 9290012687 (466524)	9290018434 (478784) 9290013354 (475814) 9290012102 (461673)	9290012740 (466235)	
Leviton	6602	Professional Channel	1-3	2-10	3-20	3-20	1-33	
Leviton	6631							
Leviton	6633		NR	1-10	2-20	2-20	1-33	
Leviton	6672		1-3	1-10	1-20	1-20	1-33	
Leviton	6674		1-3				1-10	
Leviton	6615P		1-3	1-10	1-20	1-20	1-17	
Leviton	DSE06							
Leviton	DSL06							
Leviton	DSM10							
Leviton	IPI06		1-3	1-10	4-20	4-20	1-33	
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P							
Lutron	CTCL-153P							
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-3	2-10	1-20	1-20	1-33	
Lutron	DV-600PR							
Lutron	DVCL-153P		1-3					
Lutron	DVCL-253P							
Lutron	DVELV-300P		1-3	1-10	1-20	1-20	1-17	
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M		1-3	1-10	1-20	1-20	1-33	
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		1-3	2-10	1-10	1-10	1-33	
Lutron	NTCL-250							
Lutron	PD-5NE							
Lutron	PD-6WCL		1-3	NR	3-20	3-20	NR	
Lutron	RRD-3LD							
Lutron	RRD-6NA		1-3	1-3	1-20	1-20	1-17	
Lutron	S-600P							
Lutron	SCL-153P							
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		1-3	2-10	1-20	1-20	1-25	
Lutron	TGCL-153PH							
Cooper	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M		1-3	1-10	1-20	1-20	1-33	
Lutron	MSCL-OP153MH		1-3	1-10	1-20	1-20	1-33	
Lutron	MS-OPS2H		1-3	1-10	1-20	1-20	1-33	
Panel Modules								
Lutron	GP (Harrier) Card		1-3	1-10	1-20	1-20	1-33	
Lutron	HW-RPM-4A-120		1-3	1-10	1-20	1-20	1-33	
Lutron	HW-RPM-4U-120		1-3	1-10	1-20	1-20	1-33	
Lutron	LP-RPM-4U-120		1-3	1-10	1-20	1-20	1-33	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs								
			4.5W (40W Eq) 2700K	10W (60W Eq) G25 WG CC Bulb	7W (60W Eq) DS WG	7W (40W Eq) G25 WG CC Bulb	4.5W(40Eq) DS WG	6.5W (60W Eq) DS
Dimmer Company	Model No.		9290012138 (461913) 9290012138 (461947) 9290012138 (461953)	9290011898 (459347) 9290011816 (458828) 9290011898 (459354) 9290011816 (458844) 9290011898 (459339) 9290011816 (458836)	9290011822 (458620) 9290011822 (458638)	9290011817 (458802) 9290011817 (458794) 9290011817 (458810)	9290011674 (457150) 9290011674 (457143) 9290011672 (457168) 9290011672 (457176)	9290002886 (435180)
Leviton	6602	Professional Channel	2-30	9-15	1-21	1-21	1-26	NR
Leviton	6631							
Leviton	6633		2-30	1-15	1-21	1-21	1-26	1-10
Leviton	6672		2-30	1-15	1-21	1-21	1-26	1-10
Leviton	6674		2-30	1-15	1-21	1-21	1-10	1-10
Leviton	6615P		2-16	1-8	1-11	1-11	1-13	NR
Leviton	DSE06							
Leviton	DSL06							
Leviton	DSM10							
Leviton	IPI06		2-30	1-15	1-21	1-21	1-26	NR
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P							
Lutron	CTCL-153P							
Lutron	CTCL-153PDH							
Lutron	DV-600P		2-30	1-15	1-21	1-21	1-26	1-10
Lutron	DV-600PR							
Lutron	DVCL-153P							
Lutron	DVCL-253P							
Lutron	DVELV-300P		1-16	1-8	1-11	1-11	1-13	NR
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M		2-30	1-15	1-21	1-21	1-26	1-10
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		2-30	1-15	1-21	1-15	1-26	1-10
Lutron	NTCL-250							
Lutron	PD-5NE							
Lutron	PD-6WCL		2-30	1-15	NR	1-21	NR	1-10
Lutron	RRD-3LD							
Lutron	RRD-6NA		2-30	1-15	1-25	NR	NR	1-10
Lutron	S-600P							
Lutron	SCL-153P							
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		2-30	1-11	1-16	1-16	1-19	1-10
Lutron	TGCL-153PH							
Cooper	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M		2-30	1-15	1-21	1-21	1-26	1-10
Lutron	MSCL-OP153MH		2-30	11-15	NR	1-21	1-33	
Lutron	MS-OPS2H		2-30	1-15	1-21	1-21	1-33	
Panel Modules								
Lutron	GP (Harrier) Card		2-30	1-15	1-25	1-21	1-40	1-10
Lutron	HW-RPM-4A-120		2-30	1-15	1-25	1-21	1-45	1-10
Lutron	HW-RPM-4U-120		2-30	1-15	1-25	1-21	1-45	1-10
Lutron	LP-RPM-4U-120		2-30	1-15	1-25	1-21	1-45	1-10

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Misc. (G25,ST19)

Number of bulbs

					
			3.5W DW	4W (40W Eq) WG	3W
Dimmer Company	Model No.		9290002420 (427807)	469676	427237 420414 426916 410217 420430 410209 420422
Leviton	6602	Professional Channel		3-20	
Leviton	6631				NR
Leviton	6633			2-20	
Leviton	6672		1-10	1-20	
Leviton	6674		1-17		1-6
Leviton	6615P		NR	1-20	NR
Leviton	DSE06				
Leviton	DSL06				
Leviton	DSM10				
Leviton	IPI06		NR	4-20	NR
Leviton	IPL06				
Leviton	VPI06				
Lutron	AYCL-153P				NR
Lutron	CTCL-153P				NR
Lutron	CTCL-153PDH				
Lutron	DV-600P		1-21	1-20	1-8
Lutron	DV-600PR				
Lutron	DVCL-153P				
Lutron	DVCL-253P				NR
Lutron	DVELV-300P		1-42	1-20	1-2
Lutron	DVRP-253P				
Lutron	LGCL-153P				
Lutron	MACL-153M		1-42	1-20	1-12
Lutron	MAELV-600				1-12
Lutron	MALV-600				NR
Lutron	MRF2-6ND-120		1-10	1-10	NR
Lutron	NTCL-250				NR
Lutron	PD-5NE				
Lutron	PD-6WCL			3-20	
Lutron	RRD-3LD				
Lutron	RRD-6NA		1-42	1-20	1-12
Lutron	S-600P				NR
Lutron	SCL-153P		4-42		
Lutron	SCL-153PR				
Lutron	SELV-300P				1-12
Lutron	SLV-600P		NR	1-20	1-12
Lutron	TGCL-153PH				
Cooper	RI061-VW-K2				NR
Eaton	DAL06P				
Legrand	HCL453P				
Sensors					
Lutron	MSCL-OP153M		1-42	1-20	1-7
Lutron	MSCL-OP153MH			1-20	
Lutron	MS-OPS2H			1-20	
Panel Modules					
Lutron	GP (Harrier) Card			1-20	
Lutron	HW-RPM-4A-120			1-20	
Lutron	HW-RPM-4U-120			1-20	
Lutron	LP-RPM-4U-120			1-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Notes



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

10/2024 philips.com/lighting

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.
All other trademarks are owned by Signify Holding or their respective owners.