



## EU Declaration of Conformity

Document No.: Philips Hue ambiance A60 Bulb SLR  
Year in which CE Mark was first affixed: 2021

### 1. Product Range / Model:

|                        |  |
|------------------------|--|
| Product Range / Model: | <b>NAME:</b> LED LAMP<br><b>DESCRIPTION:</b> E27, B22<br><b>Model:</b> 9290024896,9290024897,9290024898,9290024899 |
|------------------------|--|

### 2. Manufacturer Name & Address:

**Signify**  
 I.B.R.S./C.C.R.I. /Numéro 10461  
 5600 VB Eindhoven, The Netherlands

### 3. This declaration of conformity is issued under the sole responsibility of the manufacturer.

### 4. Object of the declaration:

|               |     |
|---------------|-----|
| Product Code: | N/A |
|---------------|-----|

**5&6. The object of the declaration described above is in conformity with the following relevant Union harmonization legislation and with the applicable requirements of the following harmonized standards and technical specifications:**

| Radio Equipment Directive(RED), 2014/53/EU            |   |
|---|---|
| EN 62471: 2008<br>EN 62560: 2012 + A1: 2015 +A11:2019 | Photobiological safety of lamps and lamp systems  |
| EN 62493: 2015<br>EN IEC 55015:2019+A11:2020          | Self-ballasted LED-lamps for general lighting services by voltage > 50V-safety specifications<br>Assessment of lighting equipment related to human exposure to electromagnetic fields<br>Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment  |
| EN 61000-3-2: 2014<br>EN 61000-3-3: 2013              | Electromagnetic compatibility (EMC) - Part 3-2: - Limits for harmonic current emissions<br>Electromagnetic compatibility (EMC) - Part 3-3: - Limits - Limitation of voltage changes, voltage fluctuations and flicker in public low-voltage supply systems, for equipment with rated current ≤ 16 A per phase and not subject to conditional connection |
| EN 61547: 2009<br>EN 62479: 2010                      | Equipment for general lighting purposes - EMC immunity requirements.<br>Assessment of the compliance of low power electronic and electrical equipment with the basic restrictions related to human exposure to electromagnetic fields (10 MHz to 300 GHz)   |
| ETSI EN 300328 V.2.2.2                                | Electromagnetic compatibility and Radio spectrum Matters (ERM);Wideband transmission systems; Data transmission equipment operating in the 2.4GHz ISM band and using wide band modulation techniques; Harmonized EN covering essential requirements under article 3.2 of the R&TTE Directive  |
| ETSI EN 301489-1 V2.2.3                               | Electromagnetic compatibility and Radio spectrum Matters(ERM); ElectroMagnetic Compatibility (EMC) standard for radio equipment and services; Part 1: Common technical requirements   |
| ETSI EN 301489-17 V3.2.4                              | Electromagnetic compatibility and Radio spectrum Matters(ERM); ElectroMagnetic Compatibility (EMC) standard for radio equipment; Part 17: Specific conditions for Broadband Data Transmission Systems   |


### EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures

Commission Regulation (EU) 2019/2020 and amendment Commission Regulation (EU) 2021/341

### Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU

EN IEC 63000:2018

**7. Additional information: The products in this declaration are produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.**

|  |   |
|--|---|
| <b>Signed for and on behalf of:</b><br>Sept, 01, 2021<br>SIGNIFY<br>I.B.R.S./C.C.R.I./Numéro 10461<br>5600 VB Eindhoven<br>The Netherlands | Eindhoven, the Netherlands<br>Signed for and on behalf of Signify<br>Head of Quality and Continuous Improvement<br><br>Jost Van Jaarsveld |
|--|---|