

Day-Brite

CFI

by Signify

Industrial

VTC Sealed strip

4ft, 3600 lumens



Day-Brite/CFI VTC Sealed strip is a durable wet location rated product designed for use in both indoor and outdoor environments. This luminaire offers rugged reliability and the efficiency your successful business requires.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lumens: _____ Qty: _____

Notes: _____

Ordering guide

Example: VTC436L840-UNV

Series	Length (nominal)	Lumens ¹ (nominal)	Color temp. (K)	Voltage
VTC	4	36L	840 –	UNV
VTC Sealed strip LED	4 4' length	36L 3600 lumens	840 80 CRI, 4000K	UNV Universal voltage 120-277V (non-dimmable)

1. Nominal delivered lumens at 25°C ambient.

All options are factory installed.

Many luminaire components, such as reflectors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.

Features

- Grey one piece, molded polycarbonate body. No rusting, no oxidation, and no corrosion.
- Standard lens is frosted.
- Gasket provides tight seal between plastic lens and housing.
- Stainless steel latches are standard.
- Hanging V hooks included (set of 2).
- Wrap around mounting brackets included (set of 2).
- cULus listed to meet UL 1598 standards for -10C to 40C ambient. Suitable for wet locations. IP65 rated
- 5 Year Limited Warranty

Light to go

Compatible configurations

Luminaire


VTC436L840UNV



VTC Sealed strip LED

4ft, 3600 lumens

Dimensions



Photometry

4' VTC Sealed strip LED, 3600 nominal delivered lumens

Catalog No.	VTC436L840-UNV	Candlepower				Light Distribution			Average Luminance							
Test No.	6046530.50P	Angle	End	45	Cross	Back-45	Degrees	Lumens	% Luminaire	Angle	End	45°	Cross			
S/MH	1.3	0	1054	1054	1054	1054	0-30	821	22.5	45	1008	822	811			
Lamp Type	LED	5	1053	1047	1046	1048	0-40	1351	37.1	55	961	757	759			
Lumens	3644	15	1014	999	1000	1001	0-60	2449	67.2	65	889	684	702			
Input Watts	35	25	938	918	924	926	0-90	3416	93.7	75	756	605	642			
LPW	104	35	830	813	830	820	0-180	3644	100.0	85	483	510	581			
		45	697	691	725	699	90-180	228	6.3							
		55	544	559	608	567	Coefficients of Utilization									
		65	376	420	479	428	EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)									
		75	202	285	349	290	pcc	80			70			50		
		85	50	160	226	163	pw	70	50	30	70	50	30	50	30	
		95	13	98	154	98	RCR									
		105	8	59	110	59	0	118	118	118	114	114	114	108	108	
		115	2	21	65	21	1	105	100	95	102	97	92	91	88	
		125	2	3	22	3	2	95	86	79	92	84	77	79	73	
		135	2	2	3	2	3	86	75	66	83	73	65	69	62	
		145	2	2	2	2	4	79	66	57	76	64	56	61	54	
		155	3	3	3	3	5	72	59	49	70	57	49	54	47	
		165	3	3	3	3	6	67	53	44	64	52	43	49	41	
		175	4	4	3	3	7	62	48	39	60	47	38	45	37	
							8	57	44	35	55	43	34	41	33	
							9	54	40	31	52	39	31	37	30	
							10	50	37	29	49	36	28	35	28	

Comparative yearly lighting energy cost per 1000 lumens – \$2.31 based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Photometric values based on test performed in compliance with LM-79.



© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

www.day-brite.com