



# **Environmental Product Declaration**

of the DigiStreet LED based luminaire

(ISO 14021, based on ISO 14040/14044, EN 15804)

## **Product**

DigiStreet is a family of road and street luminaires designed for the digital age. They feature universal sockets on the top and/or bottom of each luminaire that are ready to carry future sensors and lighting management systems. DigiStreet luminaires are available in a range of forms and optics, making them ideal for public lighting in many different applications. DigiStreet uses the high-performance Ledgine optimized engine with the latest LED performance and a wide range of optics to the latest standards. The DigiStreet family also includes catenary and suspended versions. With a focus on saving energy and resources and optimizing maintenance efficiency, DigiStreet is the ideal choice for cities looking to switch to future-proof, efficient LED lighting.



City center, traffic routes, parking areas, airports and harbors, residential areas.



## **Environmental Assessment - results**

## Material content

Table 1: base/ancillary materials

Aluminum	58.5%
Packaging (cardboard, paper, labels)	13.8%
Glass optical cover	11.1%
Elements of potting	4.1%
Electronics (driver, LED board)	3.5%
Steel	2.7%
Plastics (PA, PMMA, PC)	3.2%
Other (silicon, cables, connectors)	3.0%

Product weight (including packaging): 9.1 kg

Tab	le 2	$\cdot$ I CA	, boi	ınd	laries

Product stage	Raw material supply	A1
	Transport	A2
	Manufacturing	АЗ
Construction process stage	Transport from the gate to the site	A4
	Assembly	A5
Use stage	Operational energy use	В6
End of life stage	Transport	C2
	Waste processing	С3
	Disposal	C4
Benefits and loads beyond	Reuse - Recovery-	D
the system boundaries	Recycling - potential	

#### LCA results

To measure the environmental footprint of the luminaire, a life cycle assessment was carried out according to ISO 14040/14044. The CEN Norm EN 15804 serves as the core PCR. Environmental impacts of reference product are representative of product family.

## Table 3: Environmental impacts

The tables underneath display the results of the life cycle assessment. For module B6, the RSL is defined as 100,000 hours, the equivalence of 25 years in operation in a roadway luminaire application.

Indicator (cf. glossary)	Total value	Unit	A1-A3	A4	A5	B6	C2	C3	C4	D
GWP	1,95E+03	[kg CO2-Eq.]	4%	0%	0%	96%	0%	0%	0%	-1%
ODP	2,16E-04	[kg CFC11-Eq.]	7%	0%	0%	93%	0%	0%	0%	0%
AP	8,95E+00	[kg SO2-Eq.]	7%	0%	0%	93%	0%	0%	0%	-1%
EP	1,19E+00	[kg (PO4)3 Eq.]	10%	0%	0%	90%	0%	0%	0%	-1%
POCP	4,13E-01	[kg Ethen Eq.]	12%	0%	0%	90%	0%	0%	0%	-1%
ADPE	1,03E-02	[kg Sb Eq.]	79%	0%	0%	21%	0%	0%	0%	0%
ADPF	2,35E+04	[MJ]	5%	0%	0%	95%	0%	0%	0%	-1%

Table 4: Resource use

Indicator (cf. glossary)	Total value	Unit	A1-A3	A4	A5	B6	C2	C3	C4	D
PERE	5,64E+03	[MJ]	2%	0%	0%	99%	0%	0%	0%	-1%
PERM	0,00E+00	[MJ]	0%	0%	0%	0%	0%	0%	0%	0%
PERT	5,64E+03	[MJ]	2%	0%	0%	99%	0%	0%	0%	-1%
PENRE	3,98E+04	[MJ]	4%	0%	0%	97%	0%	0%	0%	0%
PENRM	3,35E+01	[MJ]	100%	0%	0%	0%	0%	0%	0%	0%
PENRT	3,98E+04	[MJ]	4%	0%	0%	97%	0%	0%	0%	0%

## Interpretation of the LCA results

For all impact categories except the Abiotic Depletion Potential (ADPE, non-fossil), the dominant phase is the use phase, associated with electricity consumption and its related generation. In particular, the contribution to global warming potential (GWP) is for 95% associated with the use phase and 5% with the production phase. The production phase has a minor contribution to the overall environmental impact, but is nevertheless the main contributor to the ADPE. This arises from the extraction of virgin material, mainly gold, silver and copper used to make electronic components. Recycling the system provides a significant reduction in ADPE through the recovery of precious metals.

# **Environmental Assessment - input data**

## **Product**

# Declared product 1x DigiStreet Mini

## Technical data

The system comprises a set of modules that are the key building blocks for a luminaire. A typical application has the following technical features:

- 1x built-in Xitanium driver
- 1x LED board, containing 40 LEDs
- 1x glass optical cover
- · Die cast aluminum housing
- Mechanical parts made of metal or plastic (driver box, mounting elements...)
- Connectors
- · Cables

## **Construction data**

Name	Value	Unit
Dimension luminaire	860 x 236 x 107	mm
Dimension driver	241 x 59 x 38	mm
Dimension LED board	200 x 175	mm
Luminous flux	5,000	lm
Luminous efficacy	113	lm/W
Color temperature	3,000	K
Power	40	W
Lifetime L80B10 Ta=25°C	100	khr

## Delivery status

Product weight: 9.1 kg (incl. 1.1 kg packaging).

## Manufacture

Manufacture of the product is divided between Philips Lighting Poland in Pila (for the drivers), Philips Lighting Poland in Kętrzyn (for the LED boards and the final assembly of the product), and suppliers located in other European countries.

## Environment and health during manufacturing

The manufacturing plants of Pila and Ketrzyn are certified according to ISO 14001 (Environment). In addition, Pila and Ketrzyn are certified according to OHSAS 18001 (Health and Safety).

## **Packaging**

Packaging materials are cardboard and polyethylene (PE). Packaging weight is 1.1 kg.

## Environment and health during use

The product is compliant with the European RoHS Directive 2011/65/EU of 8 June 2011 on Restriction of the use of certain Hazardous Substances in Electrical and Electronic equipment and with the European REACH regulation (EC) No 1907/2006 of 18 December 2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals.

## Reference Service Life

The RSL is established as 100,000 hours operation, the equivalent of 25 years in operation in case of a roadway luminaire application.

During the lifetime, no component is replaced.

#### End of Life

In the European Union, luminaires fall under the scope of the WEEE directive. Efforts are made to improve collection, reuse and recycling of the products mainly via collective Collection & Recycling Service Organizations (CRSOs). According to Eurostat and other official collection systems, the collection rate of WEEEs via CRSOs is 85% at maximum. End of life scenario is further based on a material split and respective recycling rates. Recovery potential for steel and precious metals is evaluated. The energy required for treatment of materials (shredding) is included.

## Further information

For the full and detailed list of specifications, please refer to the global e-catalogue.

# Calculation rules

## Declared unit

The declared unit is a luminaire system, with a total weight of 9.1 kilograms including packaging, and providing a luminous flux of 5,000 lumens. This luminaire provides sufficient light for various outdoor applications operated in Europe for 100,000 hours (electricity consumption of 3,980 kWh).

## System boundaries

Type of environmental declaration: cradle-to-grave, including recycling benefits (avoided burden). The following life stages are included:

- Production: raw material extraction, processing, energy and materials; manufacture of modules; assembly and packaging
- Operational energy use (average European energy mix)
- · Transport to the area of the user
- Waste processing
- · Final disposal for WEEE fraction not recycled
- · Recycling of metals from PCBs.

#### Estimates and assumptions

- Background data are used for suppliers' specific processes
- Foreground data are used for the assembly of the luminaire and drivers
- Data on collection and recycling are based on readily available data taken from generic national statistics

#### Cut-off criteria

Where no data was available, items that represented less than 1% of the total product weight were neglected. No excluded flows were

of any known particular environmental concern.

#### Background data

Necessary background data are sourced from the Ecoinvent database v3.3.

#### Data quality

Specific data used is less than 5 years old. Background data is geographically representative of the production location, and is less than 10 years old.

#### Allocation

In the aggregated module A1-A3, allocation of energy and auxiliaries was used for assembly of the driver and the luminaire in the Ketrzyn factory.

#### Methods

- CML IA baseline V3.04/EU25/Characterization/ Excluding long-term emissions.
- · Cumulative energy demand V1.1.

#### Requisite evidence

Data is based on documentation and bill of materials of the product.

### References

- · Ecoinvent www.ecoinvent.org
- ·Life Cycle Assessment Principles and framework (ISO 14040:2006)
- Life Cycle Assessment Requirements and guidelines (ISO 14044:2006)

Disclaimer

## LCA scenarios

Name	Value	Unit
Transport to the building site (A4)		
Road transport from manufacturing plant to the customer		
Transport distance	2200	km
Capacity utilization (including empty runs)	90	%
Installation into the building (A5)		
Packaging	1.1	kg
Operational energy use (B6)		
Electricity consumption	3980	kWh
Equipment output	0.040	kW
End of life (C1-C4)		
Collected separately	6.8	kg
Recycling	5.2	kg
Incineration	2.8	kg
Reference service life		
For the example of a roadway luminaire application		
Reference service life	25	a

#### Disclaimer

All environmental calculations are made in a European context. The calculations are performed on the most commonly used luminaire in the range. The LCA has been performed in accordance with the processes as used by Philips Lighting. Note that the information provided herein is subject to change. Philips Lighting does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Philips Lighting assumes no legal liability or responsibility for any loss or damage resulting from the use of the information thereto given here. For purposes hereof "Philips Lighting" means Philips Lighting N.V. and its subsidiaries and associated companies (directly or indirectly).

## Further information

Please contact:

sustainability.lighting@philips.com Collection and Recycling (brochure) Ecoinvent (website)

#### Glossary

ADP (Abiotic Depletion Potential): Impact related to the depletion of non-renewable resources, i.e. fossil fuels (ADPF), metals and minerals (ADPE).

AP (Acidification Potential): Contributions of SO2, NOx, HCl, NH3 and HF to the potential acid deposition, causing a wide range of impacts on soil, groundwater, surface water, organisms, ecosystems and buildings.

EP (Eutrophication Potential): Potential to cause overfertilization of water and soil, which can result in increased growth of biomass.

GWP (Global Warming Potential): Relative measure of how much heat a greenhouse gas (CO2, N2O, CH4...) traps in the atmosphere. It is calculated over a specific time interval, commonly 20, 100 or 500 years.

LCA: Life cycle assessment.

PCR: Product Category Rules.

PERE: Use of renewable primary energy excluding renewable primary energy resources used as raw materials.

PERM: Use of renewable primary energy resources used as raw materials.

PERT: Total use of renewable primary energy resources.

PENRE: Use of non-renewable primary energy excluding non-renewable primary energy resources used as raw materials.

PENRM: Use of non-renewable primary energy resources used as raw materials.

PENRT: Total use of non-renewable primary energy resources.

POCP (Photo-chemical Oxidation Potential or photochemical smog): Formation of reactive substances (mainly ozone) which are injurious to human health and ecosystems and which also may damage crops.

RSL: Reference service life.

