

# Day-Brite

## CFI

by ignify

Linear

SCD Wide strip



## Convenient lighting solution, excellent value

Choose the Day-Brite/CFI LED Wide strip to make your project run smoothly and keep your budget on track.

We know you are always looking for easy installation and quality lighting for a great price. The Wide strip will quickly become your go-to fixture for a variety of applications.

- More than 25% energy savings compared to 2 x 32T8
- Reliable LED technology, ensuring maintenance free long life
- Direct replacement for conventional strip luminaire

**Excellent value and convenience make this luminaire a top choice.**



# SCD Wide strip

## Linear LED



### Great lighting at a great value

- White painted metal housing for durability.
- Frosted acrylic lens for even, low glare lighting.
- Hardware for surface mounting included.
- Easy hanging installation with holes provided in housing.
- cULus listed to meet UL 1598 standards for -10C to 35C ambient.
- Suitable for damp locations.
- 5 Year Limited Warranty.

### Ordering guide


Example: SCD450L840-UNV

Series	Length (nominal)	Lumens <sup>1</sup> (nominal)	Color temp. (K)	Voltage
<input type="text" value="SCD"/>	<input type="text"/>	<input type="text"/>	<input type="text" value="840"/> –	<input type="text" value="UNV"/>
SCD Wide strip LED	2 2' length	20L 2000 lumens	840 80 CRI, 4000K	UNV Universal voltage 120-277V (non-dimmable)
	4 4' length	28L 2800 lumens 50L 5000 lumens		

<sup>1</sup> Nominal delivered lumens at 25°C ambient.

Many luminaire components, such as reflectors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.

### Dimensions



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

