



DDRC1220FR-GL

Relay Controller

Robust control of switched loads

The Philips Dynalite DDRC1220FR-GL provides control of multiple types of switched loads. This general-purpose 12 channel controller supports switched loads of up to 20 A per channel, up to a maximum device load of 180 A.

DDRC1220FR-GL

Robust control of switched loads

- Feed-through power circuit design Electrically equivalent to a 12 pole contactor, with the added advantage of each pole being separately controllable via the DyNet network.
- Flexible mounting solution A DIN-rail mountable device, designed to be installed into the distribution board supplying power to the controlled circuit.
- Inbuilt diagnostic functionality Features circuit run time tracking on each channel and Device Online/Offline status indication.
- Multiple wiring schemes supported Controls single phase and neutral or three phase and neutral (star) wiring configurations.
- **Hardware override** Service override switch accessible from front panel.

Dimensions (i. 99): (ii. 99): (ii. 99): (ii. 99): (ii. 90): (ii. 90):

 $\begin{tabular}{ll} Specifications \\ Due to continuous improvements and innovations, specifications may change without notice. \\ \end{tabular}$



Electrical

| Supply Type | Single phase | |
|---|--|--|
| upply Voltage 100-240 VAC | | |
| Supply Current | 0.25 A | |
| Outputs 12 x SPST feed-th | 12 x SPST feed-through relay with manual override | |
| Output Channel Current | 20 A (max) | |
| Maximum Device Load | 180 A | |
| Output Channel Ratings | (See Load Table on Pg 4) | |
| Maximum CH-CH Voltage | 300 VAC (UL) 400 VAC (CE) | |
| Maximum CH-XX-CH Voltage (CH2-12 only XX = unpopulated channel (2x terminals) f | • | |
| Supported Wiring Schemes | Single Phase and Neutral Three Phase and Neutral (Star) | |
| DyNet DC Output Voltage | 12 VDC | |
| DyNet DC Output Current | 200 mA | |
| Overvoltage Category | III | |
| Control | | |
| Serial Ports | 1 x RS-485 | |
| Supported Protocols | DyNet DMX Rx | |
| DMX Rx Channels | 12 | |
| Dry Contact Inputs | 1 (AUX) | |
| Diagnostic Functions | Device online/offline status | |
| User Controls Manua | 1 x service switch Il override switch for each channel | |
| Indicators | 1 x diagnostic LED | |

Refer to Installation Instructions for correct terminations for phase separation.

Physical

| Dimensions (H x W x D) | 93 x 215 x 64 mm (3.66 x 8.46 x 2.52 in) |
|--------------------------------|--|
| Packed Weight | 1.1 kg (2.43 lb) |
| Construction | Polycarbonate DIN rail enclosure (12 unit) |
| Serial Ports | 2 x RJ12 1 x 6-way pluggable screw terminal SHLD, GND, D+, D-, +12V, AUX |
| Serial Port Conductor Size | 2.5 mm² (#12 AWG) (max) |
| Supply Terminals | 3 x screw terminal Line, Neutral, Earth |
| Supply Terminal Conductor Size | 5 mm² (#10 AWG) (max) |
| Load Terminals | 12 x 2-way screw terminal Line IN, Line OUT |
| Load Terminal Conductor Size | 5 mm² (#10 AWG) (max) |

Environment**

| Operating Temperature | 0° to 50°C ambient (32° to 122°F) |
|-------------------------------|--------------------------------------|
| Storage/Transport Temperature | -25° to 70°C ambient (-13° to 158°F) |
| Humidity | 0 to 90% non-condensing |
| IEC Pollution Degree | II |

Compliance

| Certification | CE RCM III /cIII | , FCC, ICES-003, UKCA, RoHS |
|---------------|-------------------|-------------------------------|
| Certification | CL, NCIVI, UL/CUL | ., FCC, ICL3-003, UKCA, KUII3 |

^{**} For indoor installation only










Electrical



Output Channel Ratings

| Load Type | Maximum Ra | Maximum Rating per Output* | |
|-------------------|-------------------|--|--|
| | UL/cUL | CE | |
| General Use | | | |
| Incandescent | 16 A, 277 VAC | 20 A, 240 VAC | |
| Standard Driver | | | |
| Electronic Driver | 16 A | 16 A, 277 VAC | |
| Motor | 14.5 FLA** (2 ½ H | 16 FLA** (1 HP), 120 VAC 14.5 FLA** (2 ½ HP), 240 VAC 14.1 FLA** (3 HP), 277 VAC | |
| Inrush Current | | 500 A | |

^{*} Note Maximum Device Load and Maximum CH-CH Voltage on Pg 3

Ordering Code

| Product | Philips 12NC |
|---------------|--------------|
| DDRC1220FR-GL | 913703243009 |



© 2023 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Revision 11 2023-02-02 www.dynalite.com

^{**} FLA: Full Load Amps