
## **Installation Instruction**


## **Dimensions**





ta  $35^{\circ}$ 





: LED(4500 lumen) Lamp


Voltage : 12.8 V DC


IP Classification : IP 65


Net Weight : 19 Kg


Max. Projected Area : 0.411 m<sup>2</sup>


Application : Solar Street Light














\* Note - Representation product images and actual product may vary based on versions

## Precaution:

- 1. This luminaire will not operate below 0 degree ambient.
- 2. Maximum installation height is 5m.
- 3. Before installation check the luminaire by pressing the switch and make sure that it is glowing.
- 4. After three months of manufacturing it is necessary to check the glowing of the luminaire, if it is not working then contact to customer care.
- 5. The Light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced.