



The SCD Wide strip LED from Day-Brite/CFI, is an economical luminaire delivering the right light required for commercial or residential applications.

Project: _____
Location: _____
Cat.No: _____
Type: _____
Notes: _____

Ordering guide

Example: SCD450L840-UNV

Series	Length (nominal)	Lumens ¹ (nominal)	Color temp. (K)	Voltage
<input type="text" value="SCD"/>			<input type="text" value="840"/> –	<input type="text" value="UNV"/>
SCD Wide strip LED	2 2' length	20L 2000 lumens	840 80 CRI, 4000K	UNV Universal voltage 120-277V(non-dimmable)
	3 3' length	30L 3000 lumens		
	4 4' length	28L 2800 lumens 50L 5000 lumens		

1. Nominal delivered lumens at 25°C ambient.

All options are factory installed.

Many luminaire components, such as reflectors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.

Features


- White painted metal housing for durability.
- Easy hanging installation with holes provided in housing.
- 5 Year Limited Warranty.
- Frosted acrylic lens for even, low glare lighting.
- cULus listed to meet UL 1598 standards for -10C to 35C ambient.
- DLC Listing for most variations. Please check the DLC Qualified Products List to confirm.
- Hardware for surface mounting included.
- Suitable for damp locations.



SCD Wide strip LED

2ft, 3ft & 4ft

Dimensions



SCD Wide strip LED

2ft, 3ft & 4ft

Photometry

2' Wide strip LED, 2,000 nominal delivered lumens

Catalog No. SCD220L840-UNV Test No. 4788764693_1 S/MH 1.2 Lamp Type LED Lumens 2116 LPW 105 Input Watts 20 Comparative yearly lighting energy cost per 1000 lumens – \$2.29 based on 3000 hrs. and \$.08 pwr KWH. The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology. Photometric values based on test performed in compliance with LM-79.	Candlepower					Light Distribution			Average Luminance																																																																																																																																										
	Angle End 45 Cross Back-45 0 596 596 596 596 5 596 595 590 594 15 569 572 572 571 25 517 531 542 529 35 448 477 503 475 45 366 417 457 412 55 273 348 395 342 65 178 273 307 268 75 84 178 204 174 85 8 88 118 83 95 0 57 91 53 105 0 34 64 29 115 2 16 25 16 125 0 2 28 1 135 0 0 2 0 145 0 0 0 0 155 0 0 0 0 165 0 0 0 0 175 0 0 0 0	Degrees Lumens % Luminaire 0-30 467 22.1 0-40 771 36.5 0-60 1418 67.0 0-90 2004 94.7 90-180 112 5.3 0-180 2116 100.0	Angle End 45° Cross 45 10693 10110 10519 55 9687 9562 10163 65 8320 8991 9253 75 6103 7568 7711 85 1304 5529 6273																																																																																																																																																
Coefficients of Utilization EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)										<table border="1"> <thead> <tr> <th rowspan="2">pcc</th> <th colspan="3">80</th> <th colspan="3">70</th> <th colspan="2">50</th> </tr> <tr> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>pw</td> <td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>RCR</td> <td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>0</td> <td>118</td><td>118</td><td>118</td> <td>114</td><td>114</td><td>114</td> <td>108</td><td>108</td> </tr> <tr> <td>1</td> <td>105</td><td>100</td><td>95</td> <td>102</td><td>97</td><td>92</td> <td>92</td><td>88</td> </tr> <tr> <td>2</td> <td>95</td><td>86</td><td>78</td> <td>92</td><td>83</td><td>76</td> <td>79</td><td>73</td> </tr> <tr> <td>3</td> <td>86</td><td>75</td><td>66</td> <td>83</td><td>73</td><td>64</td> <td>69</td><td>62</td> </tr> <tr> <td>4</td> <td>79</td><td>66</td><td>56</td> <td>76</td><td>64</td><td>55</td> <td>61</td><td>53</td> </tr> <tr> <td>5</td> <td>72</td><td>58</td><td>49</td> <td>69</td><td>57</td><td>48</td> <td>54</td><td>46</td> </tr> <tr> <td>6</td> <td>66</td><td>52</td><td>43</td> <td>64</td><td>51</td><td>42</td> <td>49</td><td>41</td> </tr> <tr> <td>7</td> <td>61</td><td>47</td><td>38</td> <td>59</td><td>46</td><td>38</td> <td>44</td><td>37</td> </tr> <tr> <td>8</td> <td>57</td><td>43</td><td>34</td> <td>55</td><td>42</td><td>34</td> <td>40</td><td>33</td> </tr> <tr> <td>9</td> <td>53</td><td>39</td><td>31</td> <td>52</td><td>39</td><td>31</td> <td>37</td><td>30</td> </tr> <tr> <td>10</td> <td>50</td><td>36</td><td>28</td> <td>48</td><td>36</td><td>28</td> <td>34</td><td>27</td> </tr> </tbody> </table>				pcc	80			70			50		70	50	30	70	50	30	50	30	pw									RCR									0	118	118	118	114	114	114	108	108	1	105	100	95	102	97	92	92	88	2	95	86	78	92	83	76	79	73	3	86	75	66	83	73	64	69	62	4	79	66	56	76	64	55	61	53	5	72	58	49	69	57	48	54	46	6	66	52	43	64	51	42	49	41	7	61	47	38	59	46	38	44	37	8	57	43	34	55	42	34	40	33	9	53	39	31	52	39	31	37	30	10	50	36	28	48	36	28	34	27
pcc	80			70			50																																																																																																																																												
	70	50	30	70	50	30	50	30																																																																																																																																											
pw																																																																																																																																																			
RCR																																																																																																																																																			
0	118	118	118	114	114	114	108	108																																																																																																																																											
1	105	100	95	102	97	92	92	88																																																																																																																																											
2	95	86	78	92	83	76	79	73																																																																																																																																											
3	86	75	66	83	73	64	69	62																																																																																																																																											
4	79	66	56	76	64	55	61	53																																																																																																																																											
5	72	58	49	69	57	48	54	46																																																																																																																																											
6	66	52	43	64	51	42	49	41																																																																																																																																											
7	61	47	38	59	46	38	44	37																																																																																																																																											
8	57	43	34	55	42	34	40	33																																																																																																																																											
9	53	39	31	52	39	31	37	30																																																																																																																																											
10	50	36	28	48	36	28	34	27																																																																																																																																											

3' Wide strip LED, 3,000 nominal delivered lumens

Catalog No. SCD330L840-UNV Test No. 4788764693_5 S/MH 1.3 Lamp Type LED Lumens 3188 LPW 109 Input Watts 29 Comparative yearly lighting energy cost per 1000 lumens – \$2.20 based on 3000 hrs. and \$.08 pwr KWH. The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology. Photometric values based on test performed in compliance with LM-79.	Candlepower					Light Distribution			Average Luminance																																																																																																																																										
	Angle End 45 Cross Back-45 0 861 861 861 861 5 860 856 863 862 15 828 841 849 827 25 762 792 814 775 35 671 727 770 705 45 560 643 710 622 55 434 553 635 528 65 299 452 531 430 75 165 338 389 306 85 49 207 255 177 95 9 117 171 115 105 8 83 135 79 115 8 36 87 41 125 7 15 43 20 135 7 6 21 6 145 7 5 5 5 155 6 5 3 5 165 6 5 4 6 175 6 6 4 6	Degrees Lumens % Luminaire 0-30 672 22.1 0-40 1113 34.9 0-60 2056 64.5 0-90 2939 92.2 90-180 249 7.8 0-180 3188 100.0	Angle End 45° Cross 45 11068 10476 10901 55 10444 10245 10902 65 9586 10049 10690 75 8293 9776 9829 85 6166 8957 9018																																																																																																																																																
Coefficients of Utilization EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)										<table border="1"> <thead> <tr> <th rowspan="2">pcc</th> <th colspan="3">80</th> <th colspan="3">70</th> <th colspan="2">50</th> </tr> <tr> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>pw</td> <td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>RCR</td> <td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>0</td> <td>117</td><td>117</td><td>117</td> <td>114</td><td>114</td><td>114</td> <td>107</td><td>107</td> </tr> <tr> <td>1</td> <td>105</td><td>99</td><td>94</td> <td>101</td><td>96</td><td>91</td> <td>90</td><td>87</td> </tr> <tr> <td>2</td> <td>94</td><td>85</td><td>77</td> <td>91</td><td>83</td><td>76</td> <td>78</td><td>72</td> </tr> <tr> <td>3</td> <td>85</td><td>74</td><td>65</td> <td>82</td><td>72</td><td>64</td> <td>68</td><td>61</td> </tr> <tr> <td>4</td> <td>78</td><td>65</td><td>56</td> <td>75</td><td>63</td><td>54</td> <td>60</td><td>52</td> </tr> <tr> <td>5</td> <td>71</td><td>58</td><td>48</td> <td>69</td><td>56</td><td>47</td> <td>53</td><td>45</td> </tr> <tr> <td>6</td> <td>66</td><td>52</td><td>42</td> <td>63</td><td>50</td><td>42</td> <td>48</td><td>40</td> </tr> <tr> <td>7</td> <td>61</td><td>47</td><td>38</td> <td>59</td><td>46</td><td>37</td> <td>43</td><td>36</td> </tr> <tr> <td>8</td> <td>57</td><td>43</td><td>34</td> <td>55</td><td>42</td><td>33</td> <td>40</td><td>32</td> </tr> <tr> <td>9</td> <td>53</td><td>39</td><td>31</td> <td>51</td><td>38</td><td>30</td> <td>36</td><td>29</td> </tr> <tr> <td>10</td> <td>49</td><td>36</td><td>28</td> <td>48</td><td>35</td><td>27</td> <td>34</td><td>27</td> </tr> </tbody> </table>				pcc	80			70			50		70	50	30	70	50	30	50	30	pw									RCR									0	117	117	117	114	114	114	107	107	1	105	99	94	101	96	91	90	87	2	94	85	77	91	83	76	78	72	3	85	74	65	82	72	64	68	61	4	78	65	56	75	63	54	60	52	5	71	58	48	69	56	47	53	45	6	66	52	42	63	50	42	48	40	7	61	47	38	59	46	37	43	36	8	57	43	34	55	42	33	40	32	9	53	39	31	51	38	30	36	29	10	49	36	28	48	35	27	34	27
pcc	80			70			50																																																																																																																																												
	70	50	30	70	50	30	50	30																																																																																																																																											
pw																																																																																																																																																			
RCR																																																																																																																																																			
0	117	117	117	114	114	114	107	107																																																																																																																																											
1	105	99	94	101	96	91	90	87																																																																																																																																											
2	94	85	77	91	83	76	78	72																																																																																																																																											
3	85	74	65	82	72	64	68	61																																																																																																																																											
4	78	65	56	75	63	54	60	52																																																																																																																																											
5	71	58	48	69	56	47	53	45																																																																																																																																											
6	66	52	42	63	50	42	48	40																																																																																																																																											
7	61	47	38	59	46	37	43	36																																																																																																																																											
8	57	43	34	55	42	33	40	32																																																																																																																																											
9	53	39	31	51	38	30	36	29																																																																																																																																											
10	49	36	28	48	35	27	34	27																																																																																																																																											

Photometry continues on next page.

SCD Wide strip LED

2ft, 3ft & 4ft

Photometry (cont'd)

4' Wide strip LED, 2,800 nominal delivered lumens

Catalog No.	SCD428L840-UNV	Candlepower					Light Distribution			Average Luminance			
		Angle	End	45	Cross	Back-45	Degrees	Lumens	% Luminaire	Angle	End	45'	Cross
Test No.	4788764693_1	0	767	767	767	767	0-30	604	20.7	45	7212	7018	7249
S/MH	1.2	5	764	767	764	768	0-40	1002	34.4	55	6692	6830	7273
Lamp Type	LED	15	732	744	750	742	0-60	1862	63.9	65	5946	6764	7157
Lumens	2915	25	671	700	723	700	0-90	2685	92.1	75	4644	6351	6571
LPW	119	35	586	642	683	637	90-180	230	7.9	85	2501	5544	5937
Input Watts	24	45	484	572	629	563	0-180	2915	100.0				
		55	367	489	565	478							
		65	244	403	474	392							
		75	120	290	347	288							
		85	25	168	224	166							
		95	3	107	155	95							
		105	2	78	115	64							
		115	2	40	70	25							
		125	2	21	42	11							
		135	3	4	19	2							
		145	3	3	2	2							
		155	3	3	1	3							
		165	3	3	2	3							
		175	4	4	3	4							

Coefficients of Utilization									
EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)									
pcc	80			70			50		
pw	70	50	30	70	50	30	50	30	
RCR									
0	117	117	117	114	114	114	107	107	
1	105	99	94	101	96	91	90	86	
2	94	85	77	91	82	75	77	71	
3	85	74	65	82	71	63	67	60	
4	78	65	55	75	63	54	59	52	
5	71	58	48	68	56	47	53	45	
6	66	52	42	63	50	41	48	40	
7	61	47	37	58	45	37	43	35	
8	56	42	34	54	41	33	39	32	
9	53	39	30	51	38	30	36	29	
10	49	36	28	48	35	27	33	26	

Comparative yearly lighting energy cost per 1000 lumens – **\$2.00** based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Photometric values based on test performed in compliance with LM-79.

4' Wide strip LED, 5,000 nominal delivered lumens

Catalog No.	SCD450L840-UNV	Candlepower					Light Distribution			Average Luminance			
		Angle	End	45	Cross	Back-45	Degrees	Lumens	% Luminaire	Angle	End	45'	Cross
Test No.	4788764693_3	0	1470	1470	1470	1470	0-30	1154	22.0	45	13288	12447	13111
S/MH	1.2	5	1461	1456	1458	1471	0-40	1911	34.8	55	12156	11859	12862
Lamp Type	LED	15	1386	1393	1414	1426	0-60	3533	64.3	65	10484	11363	12203
Lumens	5498	25	1261	1297	1341	1334	0-90	5075	92.3	75	7829	10120	10803
LPW	107	35	1093	1161	1249	1210	90-180	423	7.7	85	2983	8020	9343
Input Watts	51	45	891	1015	1138	1064	0-180	5498	100.0				
		55	667	850	1000	898							
		65	430	677	809	726							
		75	203	462	571	523							
		85	30	244	353	290							
		95	5	173	269	174							
		105	4	121	197	118							
		115	4	56	136	43							
		125	4	23	62	17							
		135	4	4	24	4							
		145	5	4	2	5							
		155	6	5	3	5							
		165	6	6	4	6							
		175	7	7	5	7							

Coefficients of Utilization									
EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)									
pcc	80			70			50		
pw	70	50	30	70	50	30	50	30	
RCR									
0	117	117	117	114	114	114	107	107	
1	105	99	94	101	96	91	90	86	
2	94	85	77	91	82	75	77	71	
3	85	74	65	82	72	63	67	61	
4	78	65	56	75	63	54	60	52	
5	71	58	48	69	56	47	53	45	
6	66	52	42	63	50	42	48	40	
7	61	47	38	59	46	37	43	36	
8	57	43	34	54	41	33	39	32	
9	53	39	30	51	38	30	36	29	
10	49	36	28	48	35	27	33	26	

Comparative yearly lighting energy cost per 1000 lumens – **\$2.12** based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Photometric values based on test performed in compliance with LM-79.

