



DL2PA

Standard Series American

Slim-line panel in white with blue LED indicators


The Philips Dynalite Standard series has a minimalist design with full functionality. Built with the full Philips Dynalite feature set, these simple yet elegant interfaces bring the full power of the automation system to the touch of a button. The DL2PA range features a slimline finish and is suitable for, but not limited to, North American, South American, Australian and New Zealand markets.

DL2PA

Slim-line panel in white with blue LED indicators

- **Slimline finish** – Ultra-thin profile provides a less intrusive alternative, where aesthetics are a key issue.
- **Aesthetically pleasing** – Provides an elegant point for integrated automation in commercial buildings and homes.
- **Available in two configurations** – Single column, for up to five buttons and a dual column design for up to ten buttons, where more complex control is required.
- **Incorporates a miniature DyNet control network socket** – Discreetly located under the snap-on cover, the network socket enables system adjustments and programming from any user interface on the network.
- **Smooth action buttons with blue LED indicators** – Provide tactile and visual feedback and are easily removed for engraving.
- **Décor matching capability** – Available in a range of fascia, bezel and button cap colors and finishes.

Dimensions



Specifications

Due to continuous improvements and innovations, specifications may change without notice.



DL2PA
Standard Series American

Electrical

Supply Type	DyNet (SELV / Class 2)
Supply Voltage	12-24 VDC
Supply Current	20 mA

Control

Serial Ports	1 x RS-485
Supported Protocols	DyNet
User Inputs	1-10 x software-configurable buttons
Indicators	Blue indicator LED on each button

Physical

Dimensions (H x W x D)	116 x 74 x 35 mm (4.57 x 2.91 x 1.38 in)
Packed Weight	0.15 kg (0.33 lb)
Construction	ABS plastic Silicone switch membrane
Serial Ports	1 x 5-way pluggable screw terminal +V, D-, D+, GND, SHLD
Serial Port Conductor Size	2.5 mm² (#12 AWG) (max)

Environment*

Operating Temperature	0° to 45°C ambient (32° to 113°F)
Storage/Transport Temperature	-25° to 70°C ambient (-13° to 158°F)
Humidity	0 to 90% non-condensing
IEC Pollution Degree	II

Compliance

Certification	CE, RCM, UL, FCC, ICES, RoHS
---------------	------------------------------

* For indoor installation only



Ordering Code

All Standard Series interfaces are supplied with blue LED indicators, blank white buttons, and white covers and button bezels.

Standard User Interfaces

1-button	913703388409
2-button	913703388509
3-button	913703389009
5-button	913703388209
6-button	913703388609
7-button	913703388709
10-button	913703388309

Covers & Bezels

1-button cover	913703017409
2-button cover	913703017509
3-button cover	913703017609
5-button cover	913703017709
6-button cover	913703017809
7-button cover	913703017909
10-button cover	913703018009
Button bezel - white	913703018909

Wiring Adaptors

RJ12D-ADAPTOR (pack of 5) Dual RJ12 connector, downward-facing socket Suitable for DL2PA960, DL2PA970, DL2PA9100	913703069609
RJ12U-ADAPTOR (pack of 5) Dual RJ12 connector, upward-facing socket Suitable for DL2PA910, DL2PA920	913703069709

Standard Engraving Options

The button shape offers a generous area for text or symbols, ensuring that the function of the button is clearly discernible from normal viewing distances. The following stock options are available:

[blank]	913703042909
1	913703043009
2	913703043209
3	913703043309
4	913703043409
5	913703043509
6	913703043609
7	913703043709
8	913703043809
9	913703043909
10	913703043109
▲	913703044809
▼	913703044009
PROGRAM	913703044709
ON	913703044509
OFF	913703044409
ON/OFF	913703044609
HIGH	913703044109
MED	913703044309
LOW	913703044209

Custom Engraved Button Caps

Contact your local Philips representative for details on custom engraving.

Standard Layouts



DL2PA910

DL2PA920

DL2PA950

DL2PA960

DL2PA970

DL2PA9100



© 2021 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.