



# **Energy savings,** compact size

# PL-L Energy Advantage

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum effciency and sleek design solutions are required.

## **Benefits**

- 20% energy savings when compared to PL-L 40W
- · Sustainable lighting solution only 1.4mg of mercury per lamp
- Direct replacement for PL-L 40W lamp no new ballast required
- · Instant Start ballast\*
- \* On Instant Start ballast a Standard PL-L 40W only draws 32 Watts, so the actual savings is 7 Watts (32W 25W = 7W)

#### **Features**

- $\cdot$  Save energy without changing a ballast
- · Broad range of color temperatures
- · High light output in a compact size
- · Excellent color rendering

## **Application**

· Ideal for applications requiring maximum energy savings

## **Warnings and Safety**

- · Lamp contains mercury.
- · Manage in Accord with Disposal Laws.
- · See: www.lamprecycle.org or 1-800-555-0050


# **PL-L Energy Advantage**

## Versions



40W, 2G11, 4P

# Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-L 40W/830/XEW/4P/IS 25W 1CT25	1-9/16 in	3/4 in	21-1/4 in	22-1/4 in	22-1/2 in
PL-L 40W/835/XEW/4P/IS 25W 1CT/25	1-9/16 in	3/4 in	21-1/4 in	22-1/4 in	22-1/2 in
PL-L 40W/841/XEW/4P/IS 25W 1CT/25	1-9/16 in	3/4 in	21-1/4 in	22-1/4 in	22-1/2 in

Approval and application	
Mercury (Hg) Content (Nom)	1.4 mg
Controls and dimming	
Dimmable	Yes
Operating and electrical	
Lamp Current (Nom)	0.285 A
General information	
Cap-Base	2G11
Life To 50% Failures Preheat (Nom)	20000 h
Light technical	
Lumen Maintenance 10000 h (Nom)	92 %
Lumen Maintenance 2000 h (Nom)	96 %
Lumen Maintenance 5000 h (Nom)	95 %
Luminous Flux (Nom)	2600 lm

# Operating and electrical

Order Code	Full Product Name	Power (Nom)
209130	PL-L 40W/830/XEW/4P/IS 25W 1CT25	29.0 W
209148	PL-L 40W/835/XEW/4P/IS 25W 1CT/25	29.0 W
209155	PL-L 40W/841/XEW/4P/IS 25W 1CT/25	29 W

# Light technical

# **PL-L Energy Advantage**

Order		Color	Color	Correlated Color Temperature	Color Rendering
Code	Full Product Name	Code	Designation	(Nom)	Index (Nom)
209130	PL-L 40W/830/XEW/4P /IS 25W 1CT25	830	Warm White (WW)	3000 K	>80
209148	PL-L 40W/835/XEW/4P /IS 25W 1CT/25	835	White (WH)	3500 K	82

				Correlated	
				Color	Color
Order		Color	Color	Temperature	Rendering
Code	Full Product Name	Code	Designation	(Nom)	Index (Nom)
209155	PL-L	841	Cool White	4100 K	80
	40W/841/XEW/4P		(CW)		
	/IS 25W 1CT/25				

