



# The alternative!

# PL-Q 2 Pin

PL-Q is an efficient, square-shaped compact fluorescent lamp, typically used in decorative-lighting luminaires. While offering the advantage of energy-efficient operation, it also provides design freedom for flat ceiling or wall fixtures in particular, due to its low built-in height and uniform spread of light. The 2-pin version is designed for operation on electromagnetic gear.

#### **Benefits**

- · Low built-in height
- · Multiple light color choice
- · Good color rendering (CRI <gt/>80)

#### **Features**

- $\cdot$  2-pin base with a housing incorporating the special instant starter and capacitor
- Fluorescent tri-phosphor technology

## **Application**

· Ideal for applications such as corridors, toilets, stairwells and reception areas

#### Warnings and Safety

- · Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- · Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## PL-Q 2 Pin

#### Versions



LPPR PLQ2P

## Dimensional drawing

Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 16W/827/2P	40 mm	13.7 mm	27.0 mm	138 mm	49 mm	40.5 mm	135 mm
1CT/10BOX							

