



# Simply irresistible. Superior light quality from start to finish

## MasterColor CDM-TC T4

MasterColor CDM lamp gives a unique combination of unbeatable light quality and consistent performance over lifetime while keeping running costs low. The Philips MasterColor Tubular Single-Ended T4 lamp is a compact, energy efficient, ceramic metal halide lamp that provides crisp, sparkling light.

### Benefits

- Energy-efficient alternative to incandescent/halogen.
- Improved lumen maintenance over standard metal halide.
- Lamp to lamp color consistency over life.

### Features

- 90 CRI (color rendering index)
- High lamp efficacy (up to 104LPW)
- Vertical position  $\pm 60^\circ$  (39W); Universal operating position (70W)
- Dimensions, base and light center length are same as MasterColor.
- Features FadeBlock™—an integrated UV blocking medium for reduced fading of fabrics and paintings.
- 39W and 70 Watt versions.

### Application

- Ideal for retail display lighting, and accent lighting.

# MasterColor CDM-TC T4

## Warnings and Safety


- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

## Versions




G8.5 T 14 mm Clear CCT of 3000K

## Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MasterColor CDM-TC	15 mm	0.5 in	7 mm	51 mm	53 mm	52 mm	85 mm
70W/830 G8.5 T4 CL							

## Colour Rendering Diagrams



210°

180°

150°

