



Superior Color Performance in Metal Halide Technology

MasterColor CDM-TD

The MasterColor CDM metal halide lamps deliver consistent white light and higher color rendering than any standard metal halide source for architectural lighting. Tubular double-ended TD style for enclosed luminaires are ideal for accent lighting in indoor applications.

Benefits

- Energy-efficient alternative to incandescent/halogen.
- Improved lumen maintenance over standard metal halide.

Features

- Lifetime color stability within +/- 200k.
- Exceptional color rendering.
- Features FadeBlock™—an integrated UV blocking medium for reduced fading of fabrics and paintings.
- Available in 70W TD6 and 150W TD7.

Application

- Ideal for display and accent lighting in retail, architectural applications.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

MasterColor CDM-TD

Versions



CDM-TD, 150W

Dimensional drawing



Product	D (max)	D O	C (max)
MASTERColour CDM-TD 150W/830 RX7s 1CT	22 mm	10 mm	137.43 mm
MASTERColour CDM-TD 150W/942 RX7s 1CT	22 mm	10 mm	137.43 mm

MasterColor CDM-TD

Approval and Application

Energy Efficiency Label (EEL) A+

Controls and Dimming

Dimmable No

Operating and Electrical

Lamp Current (EM) (Nom) 1.8 A

Re-Ignition Time (Min) (Max) 15 min

General Information

Cap-Base RX7S

Life To 10% Failures (Nom) 13000 h

Life To 20% Failures (Nom) 15000 h

Life To 50% Failures (Nom) 16000 h

Life To 5% Failures (Nom) 9000 h

Operating Position P45

Luminaire Design Requirements

Bulb Temperature (Max) 650 °C

Light Technical

Lumen Maintenance 2000 h (Min) 80 %

Lumen Maintenance 2000 h (Nom) 90 %

Lumen Maintenance 5000 h (Min) 75 %

Lumen Maintenance 5000 h (Nom) 85 %

Mechanical and Housing

Bulb Finish Clear

Bulb Shape T6

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/	Mercury (Hg)
		1000 h	Content (Nom)
928083605133	MASTERColour CDM-TD 150W/830 RX7s 1CT	160 kWh	10.23 mg
928084805133	MASTERColour CDM-TD 150W/942 RX7s 1CT	165 kWh	8.29 mg

Operating and Electrical

Order Code	Full Product Name	Voltage	Voltage	Voltage	Power
		(Max)	(Min)	(Nom)	(Rated)
928083605133	MASTERColour CDM-TD 150W/830 RX7s 1CT	106 V	90 V	98 V	145.0 W

Order Code	Full Product Name	Voltage	Voltage	Voltage	Power
		(Max)	(Min)	(Nom)	(Rated)
928084805133	MASTERColour CDM-TD 150W/942 RX7s 1CT	110 V	96 V	103 V	150.0 W

Light Technical (1/2)

Order Code	Full Product Name	Chromaticity		Chromaticity	
		Coordinate X (Nom)	Coordinate Y (Nom)	Color Code	Color Designation
928083605133	MASTERColour CDM-TD 150W/830 RX7s 1CT	0.437	0.399	830	Warm White (WW)


Order Code	Full Product Name	Chromaticity		Chromaticity	
		Coordinate X (Nom)	Coordinate Y (Nom)	Color Code	Color Designation
928084805133	MASTERColour CDM-TD 150W/942 RX7s 1CT	0.380	0.375	942	Cool White (CW)

Light Technical (2/2)

MasterColor CDM-TD

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Lumen Maintenance 10000 h (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
928083605133	MASTERColour CDM-TD 150W/830 RX7s 1CT	3000 K	88	75 %	88 lm/W	13250 lm	12700 lm
928084805133	MASTERColour CDM-TD 150W/942 RX7s 1CT	4200 K	96	70 %	91 lm/W	13750 lm	13650 lm

Colour Rendering Diagrams



LDCR_CDM-TD_150W-Colour rendering diagram

