



We're thinking small, so you can think big

MasterColor CDM-TM

Introducing the smallest 20W ceramic metal halide lamp together with the unique e-Vision® electronic ballast. It's visually pleasing and financially rewarding, so the focus can be on your merchandise and not the ceiling clutter.

Benefits

- Miniaturization means smaller fixtures, less ceiling clutter and more focus on the merchandise.
- Positioning accuracy within the reflector for optimal reflector performance.
- Lamp, electronic ballast and twist & lock lamp base are developed as a system, and designed for easy installation and relamping.

Features

- Energy efficient system operation reduces operating costs.
- Excellent color quality of up to 90 CRI, 3000K.
- Lamp is up to 40% smaller than industry standard.
- Lamp, electronic ballast and twist & lock lamp base are developed as a system.
- Available in 20 and 35 Watt.


Application

- Ideal for accent and display lighting, in specialty retail and architectural outdoor applications.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
CDM20/TM/830 12PK	9/16 in	0.44 in	1/8 in	7/8 in	15/16 in	15/16 in	2-1/16 in
CDM 35/TM/930	9/16 in	0.44 in	3/16 in	7/8 in	15/16 in	15/16 in	2-1/16 in

Controls and dimming	
Dimmable	No
Operating and electrical	
Re-Ignition Time (Min) (Max)	15 min
General information	
Cap-Base	PGJ5
Life To 10% Failures (Nom)	10000 h
Life To 20% Failures (Nom)	11000 h
Life To 50% Failures (Nom)	12000 h
Life To 5% Failures (Nom)	9000 h
Operating Position	Universal
Light technical	
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Lumen Maintenance 10000 h (Nom)	60 %
Mechanical and housing	
Bulb Finish	Clear
Bulb Shape	T13.3

Approval and application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
140400	CDM20/TM/830 12PK	24 kWh	2.4 mg
211391	CDM 35/TM/930	43 kWh	2.74 mg

Operating and electrical

Order Code	Full Product Name	Voltage (Max)	Voltage (Min)	Voltage (Nom)	Power (Nom)
140400	CDM20/TM/830 12PK	108 V	95 V	100 V	22.1 W

Order Code	Full Product Name	Voltage (Max)	Voltage (Min)	Voltage (Nom)	Power (Nom)
211391	CDM 35/TM/930	104 V	88 V	96 V	39.1 W

Luminaire design requirements

Order Code	Full Product Name	Bulb Temperature (Max)
140400	CDM20/TM/830 12PK	716 °F

Order Code	Full Product Name	Bulb Temperature (Max)
211391	CDM 35/TM/930	896 °F

Light technical (1/2)

		Chromaticity	Chromaticity		Color
Order	Full Product	Coordinate X	Coordinate Y	Color	Rendering
Code	Name	(Nom)	(Nom)	Code	Index (Min)
140400	CDM20/TM/83 0 12PK	0.433	0.392	830	84

		Chromaticity	Chromaticity		Color
Order	Full Product	Coordinate X	Coordinate Y	Color	Rendering
Code	Name	(Nom)	(Nom)	Code	Index (Min)
211391	CDM 35/TM/930	0.436	0.396	930	88

Light technical (2/2)

Order Code	Full Product Name	Color Rendering	Lumen Maintenance	Lumen Maintenance	Lumen Maintenance	Luminous Efficacy	Luminous Flux
		Index (Nom)	1000 h (Nom)	2000 h (Nom)	5000 h (Nom)	(rated) (Nom)	(Rated) (Nom)
140400	CDM20/TM/830 12PK	87	80 %	75 %	65 %	72 lm/W	1600 lm
211391	CDM 35/TM/930	91	85 %	80 %	70 %	77 lm/W	3000 lm

