



Perfect sparkle, easy application

MASTERColour CDM-Rm Elite Mini

Mini, very high-efficiency Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high color rendering

Benefits

- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- Easy to install and replace, reducing installation and relamping costs
- Fits in small luminaires which are less visible

Features

- Crisp white sparkling light
- Excellent color rendering, with extra red
- High efficacy with unparalleled lumen maintenance
- Mini design fitting in open luminaires
- UV-blocking front glass

Application


- Accent and display lighting in retail
- General and decorative indoor lighting

Warnings and Safety

- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035).
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTERColour CDM-Rm Elite Mini

Dimensional drawing





Product	D (max)	D	C (max)	C	C1 (max)	A (max)
CDM-Rm Elite Mini 35W/930 GX10 MR16 10D	51 mm	50 mm	65.4 mm	62.75 mm	60.9 mm	59 mm
CDM-Rm Elite Mini 35W/930 GX10 MR16 25D	51 mm	50 mm	65.4 mm	62.75 mm	60.9 mm	59 mm
CDM-Rm Elite Mini 35W/930 GX10 MR16 40D	51 mm	50 mm	65.4 mm	62.75 mm	60.9 mm	59 mm


General Information	
Cap-Base	GX10
Switching Cycle	1,350
Operating Position	UNIVERSAL
Light Technical	
Chromaticity Coordinate X (Nom)	0.434
Chromaticity Coordinate Y (Nom)	0.398
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	80 %
Operating and Electrical	
Warm-up time to 60% light	120 s
Voltage (Nom)	87 V
Power Consumption	39.1 W
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	MR16
Approval and Application	
Energy Consumption kWh/1000 h	40 kWh
Mercury (Hg) Content (Max)	4.7 mg
Mercury (Hg) Content (Nom)	4.7 mg

Light Technical


Order Code	Full Product Name	Beam Angle (Nom)	Luminous Efficacy (rated)	Luminous Intensity	
			(Nom)	Luminous Flux	(Nom)
928194605330	CDM-Rm Elite Mini 35W/930 GX10 MR16 10D	10 degree(s)	60 lm/W	2,100 lm	17,500 cd
928194705330	CDM-Rm Elite Mini 35W/930 GX10 MR16 25D	25 degree(s)	60 lm/W	2,150 lm	7,600 cd
928194805330	CDM-Rm Elite Mini 35W/930 GX10 MR16 40D	40 degree(s)	61 lm/W	2,150 lm	3,600 cd




MASTERColour CDM-Rm Elite Mini




Accent Diagrams



Accent Diagram - CDM-Rm Elite Mini 35W/930
GX10 MR16 10D




Accent Diagram - CDM-Rm Elite Mini 35W/930
GX10 MR16 25D




Accent Diagram - CDM-Rm Elite Mini 35W/930
GX10 MR16 40D


Beam Diagrams



Beam diagram - CDM-Rm Elite Mini 35W/930
GX10 MR16 10D



Beam diagram - CDM-Rm Elite Mini 35W/930
GX10 MR16 25D



Beam diagram - CDM-Rm Elite Mini 35W/930
GX10 MR16 40D

