



Product Description

MASTERColour CDM-T

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

Benefits

- Stable color impression over lifetime
- Stable colour impression over lifetime
- High lamp efficacy results in low operating costs and low heat generation
- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps
- Long lamp life compared with incandescent and halogen lamps
- Relatively low heat output enhances comfort for shoppers and staff
- Relatively low heat output enhances comfort for shoppers and staff
- All types are UV-Block for reduced fading risks
- All types are UV-Block for reduced fading risks

Features

- Crisp white light
- Warm or cool white colour impression
- Superior color quality
- Colour rendering good to excellent
- Allows small-size luminaires designs that give high beam intensities
- Allows small-size luminaires designs that give high beam intensities

Application

- Shops and shop windows, offices and public buildings
- Shops and shop windows, offices and public buildings
- Decorative outdoor: floodlighting and pedestrian areas
- Decorative outdoor: floodlighting and pedestrian areas

MASTERCoulour CDM-T

Warnings and Safety


- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR CDM-T 0005

Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T	20 mm	0.75 inch	9 mm	55 mm	57 mm	56 mm	110 mm
150W/830 G12 1CT							

