

Product Description

Gear for SDW-T lamps

CSLS electronic control unit with impregnated (HID "BASIC") or encapsulated (HID "Heavy Duty") electromagnetic ballasts

Benefits

- Electronic control unit ensures reliable starting and stabilizes lamp power for optimum performance (minimum color deviation)
- Simple installation and cabling

Features

- Ballasts and electronic control units equipped with screw terminal blocks; other contact possibilities for
- Earthing-while-mounting facility (HID 'BASIC' ballasts), separate earth terminal (HID 'Heavy Duty')

Application


- Similar to those of the related lamps
- Climatic suitability:
- CSLS + HID "BASIC": restricted to built-in situations under normal conditions
- CSLS + HID "Heavy Duty": use in luminaires under humid conditions (not drip-proof)

Warnings and Safety

- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)

Gear for SDW-T lamps



Versions



BSL 100 K202-A2-TS 230V

GPPR CSLS PHL 0001

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
CSLS 100 SDW-T 220-240V 50/60Hz	4.5 mm	39.5 mm	98.0 mm	70.0 mm	58.5 mm	46.0 mm

Product	A1	A2	B1	C1	D1
BSL 100 K202-A2-TS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm



Gear for SDW-T lamps

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Input Voltage	Line
				Frequency
74076700	BSL 100 K202-A2-TS 230V 50Hz	50 Hz	230 V	50 Hz

Order Code	Full Product Name	Input Frequency	Input Voltage	Line
				Frequency
90870430	CSLS 100 SDW-T 220-240V 50/60Hz	50 to 60 Hz	220 to 240 V	-

