



Product Description

Gear for SDW-T lamps

CSLS electronic control unit with impregnated (HID "BASIC") or encapsulated (HID "Heavy Duty") electromagnetic ballasts

Benefits

- Electronic control unit ensures reliable starting and stabilizes lamp power for optimum performance (minimum colour deviation)
- Simple installation and cabling

Features

- Ballasts and electronic control units equipped with screw terminal blocks; other contact possibilities for
- Earthing-while-mounting facility (HID 'BASIC' ballasts), separate earth terminal (HID 'Heavy Duty')

Application

- Similar to those of the related lamps
- Climatic suitability:
- CSLS + HID "BASIC": restricted to built-in situations under normal conditions
- CSLS + HID "Heavy Duty": use in luminaires under humid conditions (not drip-proof)

Warnings and Safety


- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)

Gear for SDW-T lamps

Versions



Dimensional drawing



Product

CSLS 50 SDW-T 220-240V 50/60Hz

CSLS 100 SDW-T 220-240V 50/60Hz

Operating and Electrical

| | |
|-----------------|--------------|
| Input Frequency | 50 to 60 Hz |
| Input Voltage | 220 to 240 V |

General Information

| | |
|-----------------|--------------|
| Number Of Lamps | 1 piece/unit |
| Lamp Type | SDW-T |

System characteristics

| Order Code | Full Product Name | Rated Ballast-Lamp Power |
|--------------|--------------------------------|--------------------------|
| 913619179966 | CSLS 50 SDW-T 220-240V 50/60Hz | 50 W |



Gear for SDW-T lamps

| Order Code | Full Product Name | Rated Ballast-Lamp Power |
|--------------|---------------------------------|--------------------------|
| 913619189966 | CSLS 100 SDW-T 220-240V 50/60Hz | 100 W |

