



Product Description

MASTER HPI-T Plus

Quartz metal halide lamps with clear outer bulb

Benefits

- High safety and comfort level, maintained over life
- Minimal maintenance cost
- Initial investment saving options with "Plus"-concept

Features

- Clear tubular outer bulb
- Unique 3-band technology resulting in high luminous efficacy, both initially and over long lifetime
- Renders a natural white colour appearance and good colour stability

Application


- Sports lighting, floodlighting of buildings and monuments, area lighting e.g. harbours and building sites, canopy lighting e.g. petrol stations, horticultural lighting

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER HPI-T Plus

Dimensional drawing



Product	D (max)	O	L	C (max)
MASTER HPI-T Plus 250W/645 E40 1SL/12	47 mm	29 mm	155 mm	255 mm
MASTER HPI-T Plus 400W/645 E40 1SL/12	47 mm	30.5 mm	168 mm	286 mm

General Information

Cap-Base	E40
Operating Position	P20

Light Technical

Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4500 K
Color rendering index (CRI)	65

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T46

Light Technical

Order Code	Full Product Name	Chromaticity		Luminous Efficacy (rated) (Nom)
		Coordinate X (Nom)	Coordinate Y (Nom)	
928481300098	MASTER HPI-T Plus 250W/645 E40 1SL/12	365	377	79 lm/W
928481600096	MASTER HPI-T Plus 400W/645 E40 1SL/12	361	372	83 lm/W

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power	
			Consumption	
928481300098	MASTER HPI-T Plus 250W/645 E40 1SL/12	128 V	247 W	

Order Code	Full Product Name	Voltage (Nom)	Power	
			Consumption	
928481600096	MASTER HPI-T Plus 400W/645 E40 1SL/12	125 V	385 W	

Approval and Application

Order Code	Full Product Name	Energy Consumption	Mercury (Hg)
		kWh/1000 h	Content (Nom)
928481300098	MASTER HPI-T Plus 250W/645 E40 1SL/12	272 kWh	36 mg
928481600096	MASTER HPI-T Plus 400W/645 E40 1SL/12	424 kWh	29.5 mg

