



# Product Description

## HPL-N

Standard High Pressure Mercury lamp

### Benefits

### Features

### Application

### Warnings and Safety

### Versions



## Dimensional drawing

D

Product	D (max)	C (max)
HPL-N 125W/542 E27 1CT/24	76 mm	173 mm
HPL-N 250W/542 E40 1SL/12	91 mm	226 mm
HPL-N 400W/542 E40 HG 1SL/6	122 mm	290 mm
HPL-N 80W/542 E27 1CT/24	71 mm	155 mm

### Approval and Application

Energy Efficiency Label (EEL) B

### Controls and Dimming

Dimmable No

### General Information

LSF 2000 h Rated 99 %

Operating Position UNIVERSAL

### Luminaire Design Requirements

Bulb Temperature (Max) 350 °C

### Light Technical

Colour Code 542

Colour Designation Cool White (CW)

### Mechanical and Housing

Bulb Finish Coated glass

### Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h (Nom)	Mercury (Hg) Content
27777100	HPL-N 80W/542 E27 1CT/24	88 kWh	14.0 mg
27779500	HPL-N 125W/542 E27 1CT/24	137 kWh	19.0 mg
27781800	HPL-N 250W/542 E40 1SL/12	275 kWh	38 mg
18045299	HPL-N 400W/542 E40 HG 1SL/6	440 kWh	72 mg

## Operating and Electrical (1/2)

Order Code	Full Product Name	Lamp			
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
27777100	HPL-N 80W/542 E27 1CT/24	0.8 A	125 V	105 V	115 V
27779500	HPL-N 125W/542 E27 1CT/24	1.15 A	135 V	115 V	125 V

Order Code	Full Product Name	Lamp			
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
27781800	HPL-N 250W/542 E40 1SL/12	2.1 A	145 V	125 V	135 V
18045299	HPL-N 400W/542 E40 HG 1SL/6	3.25 A	150 V	130 V	140 V

## Operating and Electrical (2/2)

Order Code	Full Product Name	Power (Rated) (Nom)
27777100	HPL-N 80W/542 E27 1CT/24	80.0 W
27779500	HPL-N 125W/542 E27 1CT/24	125.0 W

Order Code	Full Product Name	Power (Rated) (Nom)
27781800	HPL-N 250W/542 E40 1SL/12	250.0 W
18045299	HPL-N 400W/542 E40 HG 1SL/6	400.0 W

## General Information (1/2)

Order Code	Full Product Name	Cap-Base	Life To 20%	Life To 50%	Life To 5%
			Failures (Nom)	Failures (Nom)	Failures (Nom)
27777100	HPL-N 80W/542 E27 1CT/24	E27	12000 h	20000 h	6000 h
27779500	HPL-N 125W/542 E27 1CT/24	E27	12000 h	20000 h	6000 h

Order Code	Full Product Name	Cap-Base	Life To 20%	Life To 50%	Life To 5%
			Failures (Nom)	Failures (Nom)	Failures (Nom)
27781800	HPL-N 250W/542 E40 1SL/12	E40	10000 h	15000 h	5000 h
18045299	HPL-N 400W/542 E40 HG 1SL/6	E40	12000 h	16000 h	6000 h

## General Information (2/2)

Order Code	Full Product Name	LSF 12000 h Rated	LSF 16000 h Rated	LSF 20000 h Rated	LSF 4000 h Rated	LSF 6000 h Rated	LSF 8000 h Rated
27777100	HPL-N 80W/542 E27 1CT/24	80 %	68 %	50 %	98 %	95 %	92 %
27779500	HPL-N 125W/542 E27 1CT/24	80 %	68 %	50 %	98 %	95 %	92 %
27781800	HPL-N 250W/542 E40 1SL/12	65 %	45 %	28 %	97 %	92 %	83 %
18045299	HPL-N 400W/542 E40 HG 1SL/6	65 %	45 %	28 %	97 %	92 %	83 %

## Light Technical (1/3)

Order Code	Full Product Name	Chromaticity		Correlated Colour	Colour Rendering
		Coordinate X (Nom)	Coordinate Y (Nom)	Temperature (Nom)	Index (Nom)
27777100	HPL-N 80W/542 E27 1CT/24	370	366	4300 K	45
27779500	HPL-N 125W/542 E27 1CT/24	374	373	4100 K	46
27781800	HPL-N 250W/542 E40 1SL/12	381	383	4100 K	40

Order Code	Full Product Name	Chromaticity		Correlated Colour	Colour Rendering
		Coordinate X (Nom)	Coordinate Y (Nom)	Temperature (Nom)	Index (Nom)
18045299	HPL-N 400W/542 E40 HG 1SL/6	384	384	4200 K	50

## Light Technical (2/3)

Order Code	Full Product Name	LLMF 12000	LLMF 16000	LLMF 2000	LLMF 20000	LLMF 4000	LLMF 6000	LLMF 8000	Lumen Maintenance 2000	Lumen Maintenance 2000
		h Rated	h Rated	h Rated	h Rated	h Rated	h Rated	h Rated	h (Min)	h (Nom)
27777100	HPL-N 80W/542 E27 1CT/24	85 %	80 %	92 %	76 %	91 %	89 %	88 %	82 %	92 %
27779500	HPL-N 125W/542 E27 1CT/24	85 %	80 %	92 %	76 %	91 %	89 %	88 %	82 %	92 %
27781800	HPL-N 250W/542 E40 1SL/12	78 %	75 %	88 %	72 %	86 %	84 %	82 %	78 %	88 %
18045299	HPL-N 400W/542 E40 HG 1SL/6	78 %	75 %	88 %	72 %	86 %	84 %	82 %	78 %	88 %

## Light Technical (3/3)

# HPL-N

Order Code	Full Product Name	Lumen Maintenance 5000 h (Min)	Lumen Maintenance 5000 h (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Rated) (Nom)
27777100	HPL-N 80W/542 E27 1CT/24	80 %	90 %	44.5 lm/W	3600 lm
27779500	HPL-N 125W/542 E27 1CT/24	80 %	90 %	50 lm/W	6200 lm
27781800	HPL-N 250W/542 E40 1SL/12	75 %	85 %	51 lm/W	12700 lm



Order Code	Full Product Name	Lumen Maintenance 5000 h (Min)	Lumen Maintenance 5000 h (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Rated) (Nom)
18045299	HPL-N 400W/542 E40 HG 1SL/6	75 %	85 %	55 lm/W	22000 lm

## Mechanical and Housing

Order Code	Full Product Name	Bulb Material	Bulb Shape
27777100	HPL-N 80W/542 E27 1CT/24	Soft Glass	BF70
27779500	HPL-N 125W/542 E27 1CT/24	Soft Glass	E75

Order Code	Full Product Name	Bulb Material	Bulb Shape
27781800	HPL-N 250W/542 E40 1SL/12	Hard Glass	ED90
18045299	HPL-N 400W/542 E40 HG 1SL/6	Hard Glass	ED120

## Colour Rendering Diagrams



LDCR\_HPL\_0002-Colour rendering diagram



# HPL-N

