



Product Description

HPL-N

Standard High Pressure Mercury lamp

Benefits

- Good budget alternative

Features

- Equipped with 1 or 2 auxiliary electrodes to ensure quick and reliable ignition
- Single-ended gas-filled glass bulb (HG-SG) with a quartz mercury vapour discharge tube
- Internally coated ovoid outer bulb, providing a cool, bluish white light with reasonable colour qualities


Application

- All outdoor applications, factories, transport sector and industrial area lighting

Versions



Dimensional drawing



Product	D (max)	C (max)
HPL-N 250W/542 E40 1SL/12	91 mm	226 mm
HPL-N 80W/542 E27 1CT/24	71 mm	155 mm
HPL-N 400W/542 E40 HG 1SL/6	122 mm	290 mm
HPL-N 125W/542 E27 1CT/24	76 mm	173 mm

Approval and Application

Energy Efficiency Label (EEL)	B
-------------------------------	---

Controls and Dimming

Dimmable	no
----------	----

General Information

LSF 2000 h Rated	99 %
------------------	------

Operating Position	UNIVERSAL
--------------------	-----------

Luminaire Design Requirements

Bulb Temperature (Max)	350 °C
------------------------	--------

Light Technical

Colour Code	542
Colour Designation	Cool White (CW)

Mechanical and Housing

Bulb Finish	Coated
-------------	--------

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
928051007391	HPL-N 80W/542 E27 1CT/24	88 kWh	14.0 mg
928052007391	HPL-N 125W/542 E27 1CT/24	137 kWh	19.0 mg
928053007492	HPL-N 250W/542 E40 1SL/12	275 kWh	38 mg
928053507496	HPL-N 400W/542 E40 HG 1SL/6	440 kWh	72 mg

Operating and Electrical (1/2)

Order Code	Full Product Name	Lamp			
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
928051007391	HPL-N 80W/542 E27 1CT/24	0.8 A	125 V	105 V	115 V
928052007391	HPL-N 125W/542 E27 1CT/24	1.15 A	135 V	115 V	125 V

Order Code	Full Product Name	Lamp			
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
928053007492	HPL-N 250W/542 E40 1SL/12	2.1 A	145 V	125 V	135 V
928053507496	HPL-N 400W/542 E40 HG 1SL/6	3.25 A	150 V	130 V	140 V

Operating and Electrical (2/2)

Order Code	Full Product Name	Power (Rated) (Nom)
928051007391	HPL-N 80W/542 E27 1CT/24	80.0 W
928052007391	HPL-N 125W/542 E27 1CT/24	125.0 W

Order Code	Full Product Name	Power (Rated) (Nom)
928053007492	HPL-N 250W/542 E40 1SL/12	250.0 W
928053507496	HPL-N 400W/542 E40 HG 1SL/6	400.0 W

General Information (1/2)

Order Code	Full Product Name	Cap-Base	Life To 20%	Life To 50%	Life To 5%
			Failures (Nom)	Failures (Nom)	Failures (Nom)
928051007391	HPL-N 80W/542 E27 1CT/24	E27	12000 h	20000 h	6000 h
928052007391	HPL-N 125W/542 E27 1CT/24	E27	12000 h	20000 h	6000 h

Order Code	Full Product Name	Cap-Base	Life To 20%	Life To 50%	Life To 5%
			Failures (Nom)	Failures (Nom)	Failures (Nom)
928053007492	HPL-N 250W/542 E40 1SL/12	E40	10000 h	15000 h	5000 h
928053507496	HPL-N 400W/542 E40 HG 1SL/6	E40	12000 h	16000 h	6000 h

General Information (2/2)

Order Code	Full Product Name	LSF 12000 h Rated	LSF 16000 h Rated	LSF 20000 h Rated	LSF 4000 h Rated	LSF 6000 h Rated	LSF 8000 h Rated
928051007391	HPL-N 80W/542 E27 1CT/24	80 %	68 %	50 %	98 %	95 %	92 %
928052007391	HPL-N 125W/542 E27 1CT/24	80 %	68 %	50 %	98 %	95 %	92 %
928053007492	HPL-N 250W/542 E40 1SL/12	65 %	45 %	28 %	97 %	92 %	83 %
928053507496	HPL-N 400W/542 E40 HG 1SL/6	65 %	45 %	28 %	97 %	92 %	83 %

Light Technical (1/3)

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Correlated Colour	Colour Rendering
				Temperature (Nom)	Index (Nom)
928051007391	HPL-N 80W/542 E27 1CT/24	370	366	4300 K	45
928052007391	HPL-N 125W/542 E27 1CT/24	374	373	4100 K	46
928053007492	HPL-N 250W/542 E40 1SL/12	381	383	4100 K	40

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Correlated Colour	Colour Rendering
				Temperature (Nom)	Index (Nom)
928053507496	HPL-N 400W/542 E40 HG 1SL/6	384	384	4200 K	50

Light Technical (2/3)

Order Code	Full Product Name	LLMF 12000 h	LLMF 16000 h	LLMF 2000 h	LLMF 20000 h	LLMF 4000 h	LLMF 6000 h	LLMF 8000 h	Lumen Maintenance 2000 h (Min)	Lumen Maintenance 2000 h (Nom)
		Rated	Rated	h Rated	Rated	h Rated	h Rated	h Rated		
928051007391	HPL-N 80W/542 E27 1CT/24	85 %	80 %	92 %	76 %	91 %	89 %	88 %	82 %	92 %
928052007391	HPL-N 125W/542 E27 1CT/24	85 %	80 %	92 %	76 %	91 %	89 %	88 %	82 %	92 %
928053007492	HPL-N 250W/542 E40 1SL/12	78 %	75 %	88 %	72 %	86 %	84 %	82 %	78 %	88 %
928053507496	HPL-N 400W/542 E40 HG 1SL/6	78 %	75 %	88 %	72 %	86 %	84 %	82 %	78 %	88 %

Light Technical (3/3)

HPL-N

Order Code	Full Product Name	Lumen Maintenance 5000 h (Min)	Lumen Maintenance 5000 h (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Rated) (Nom)
928051007391	HPL-N 80W/542 E27 1CT/24	80 %	90 %	44.5 lm/W	3600 lm
928052007391	HPL-N 125W/542 E27 1CT/24	80 %	90 %	50 lm/W	6200 lm
928053007492	HPL-N 250W/542 E40 1SL/12	75 %	85 %	51 lm/W	12700 lm



Order Code	Full Product Name	Lumen Maintenance 5000 h (Min)	Lumen Maintenance 5000 h (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Rated) (Nom)
928053507496	HPL-N 400W/542 E40 HG 1SL/6	75 %	85 %	55 lm/W	22000 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Material	Bulb Shape
928051007391	HPL-N 80W/542 E27 1CT/24	Soft Glass	BF70
928052007391	HPL-N 125W/542 E27 1CT/24	Soft Glass	E75

Order Code	Full Product Name	Bulb Material	Bulb Shape
928053007492	HPL-N 250W/542 E40 1SL/12	Hard Glass	ED90
928053507496	HPL-N 400W/542 E40 HG 1SL/6	Hard Glass	ED120

Colour Rendering Diagrams



HPL-N

