



Product description

MH-NaSc

Sodium Scandium Metal Halide Lamps consisting of a gasfilled glass bulb, which alternatively are clear or internal coated, and a quartz discharge tube (DT).

Benefits

- Energy saving solution with better color appearance and rendering property for conventional version.

Features

- Quartz discharge tube containing high-pressure mercury and a mixture of Sodium and Scandium halides, which contribute to multi-lines spectra; with Ar to aid ignition.
- Better colour rendering index around 60
- Luminous efficacy up to 90 lm/W
- Low wattage lamps with extra quartz tube around DT to prevent the risk of outer bulb shattering when abnormal operated or to the end of life.
- Universal operation position permitted

Application



- Stadium and sports facilities lighting
- Industrial and commercial lighting—factory
- supermarket and exhibition hall etc.
- Public lighting—square, station, port, airport etc.
- Decorative flood lighting—monument, buildings e.g.
- hotel

MH-NaSc

Versions



Dimensional drawing



Product	D (max)	L (min)	C (max)
MH 70W/640 E27 CL 1SL/24	56 mm	83 mm	141 mm
MH 400W/640 E40 CL U 1SL/6	121 mm	184 mm	290 mm
MH Quartz 400W/637 E40 CO U 1SL/6	121 mm	184 mm	290 mm
MH 150W/640 E27 CL 1SL/24	56 mm	83 mm	141 mm

Product	D (max)	L (min)	C (max)
MH 250W/637 E40 CO U 1SL/12	91 mm	149 mm	226 mm
MH - 250W/640 E40 CL U 1SL/12	91 mm	149 mm	226 mm

Controls and Dimming	
Dimmable	no
Operating and Electrical	
Power (Rated) (Max)	- W
Power (Rated) (Min)	- W
General Information	
Cap-Base	E27
Life To 20% Failures (Nom)	5000 h
Life To 50% Failures (Nom)	10000 h
Life To 5% Failures (Nom)	2000 h
Operating Position	H
System Description	na
Luminaire Design Requirements	
Bulb Temperature (Max)	450 °C
Light Technical	
Colour Code	640
Colour Designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Lumen Maintenance 2000 h (Nom)	75 %
Lumen Maintenance 5000 h (Nom)	60 %
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	ED55

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000	Mercury (Hg) Content
		h	(Nom)
928484400092	MH 70W/640 E27 CL 1SL/24	-	12 mg
928484600092	MH 150W/640 E27 CL 1SL/24	165 kWh	11 mg

Operating and Electrical (1/2)

Order Code	Full Product Name	Lamp			
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
928484400092	MH 70W/640 E27 CL 1SL/24	0.98 A	100 V	75 V	85 V

Order Code	Full Product Name	Lamp			
		Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
928484600092	MH 150W/640 E27 CL 1SL/24	1.8 A	105 V	85 V	95 V

Operating and Electrical (2/2)

Order Code	Full Product Name	Power (Rated) (Nom)
928484400092	MH 70W/640 E27 CL 1SL/24	70.0 W

Order Code	Full Product Name	Power (Rated) (Nom)
928484600092	MH 150W/640 E27 CL 1SL/24	150.0 W

Light Technical (1/2)

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Colour Rendering	Luminous Efficacy
				(Nom)	(rated)
928484400092	MH 70W/640 E27 CL 1SL/24	390	380	60	80 lm/W
928484600092	MH 150W/640	385	390	65	90 lm/W

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Colour Rendering	Luminous Efficacy
				(Nom)	(rated)
	E27 CL 1SL/24				

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)
928484400092	MH 70W/640 E27 CL 1SL/24	4200 lm	5600 lm
928484600092	MH 150W/640 E27 CL 1SL/24	12150 lm	13500 lm

