



Product Description

MASTER MHN-SA

Compact quartz metal halide lamps with double-pinch

Benefits

- Allows compact and very efficient luminaire systems with high precision optics for good beam control and minimal spill light
- Very good colour rendering creates a pleasant ambience with high visual comfort for players and spectators
- Continuous spectral distribution offers a superior solution for (semi-) professional stadiums with regular TV coverage

Features

- Very compact source (Short Arc) with high luminous efficacy and superior colour rendering
- Double-pinch concept results in long lifetime
- Natural white colour appearance, high colour rendering and good colour stability
- Daylight colour temperature eases transition from daylight to artificial lighting

Application

- Professional sports lighting and floodlighting

Warnings and Safety


- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER MHN-SA

Versions




Dimensional drawing



Product

MASTER MHN-SA 2000W/956 400V XW HO UNP/1



Product

MASTER MHN-SA 1800W/956 (P)SFC 400V

MASTER MHN-SA

Approval and Application	
Energy Efficiency Label (EEL)	A+
Controls and Dimming	
Dimmable	no
Operating and Electrical	
Voltage (Max)	220 V
Voltage (Min)	185 V
Voltage (Nom)	205 V
General Information	
Life To 5% Failures (Nom)	1700 h
Operating Position	P15
Light Technical	
Chromaticity Coordinate X (Nom)	330
Colour Code	956
Colour Designation	Daylight
Correlated Colour Temperature (Nom)	5600 K
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	TD40

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h	Mercury (Hg) Content (Nom)
20076100	MASTER MHN-SA 1800W/956 (P)SFC 400V	2035 kWh	250 mg
24183600	MASTER MHN-SA 2000W/956 400V XW HO UNP/1	2305 kWh	215 mg

Operating and Electrical

Order Code	Full Product Name	Lamp Current (EM) (Nom)	Power (Rated) (Nom)
20076100	MASTER MHN-SA 1800W/956 (P)SFC 400V	10.5 A	1850.0 W

Order Code	Full Product Name	Lamp Current (EM) (Nom)	Power (Rated) (Nom)
24183600	MASTER MHN-SA 2000W/956 400V XW HO UNP/1	11.8 A	2095.0 W

General Information

Order Code	Full Product Name	Cap- Base	Life To 10% Failures (Nom)	Life To 20% Failures (Nom)	Life To 50% Failures (Nom)
20076100	MASTER MHN-SA 1800W/956 (P)SFC 400V	(P)SFC	2400 h	3600 h	6100 h

Order Code	Full Product Name	Cap- Base	Life To 10% Failures (Nom)	Life To 20% Failures (Nom)	Life To 50% Failures (Nom)
24183600	MASTER MHN-SA 2000W/956 400V XW HO UNP/1	X830R	2300 h	3000 h	5000 h

Luminaire Design Requirements

Order Code	Full Product Name	Bulb Temperature (Max)
20076100	MASTER MHN-SA 1800W/956 (P)SFC 400V	980 °C
24183600	MASTER MHN-SA 2000W/956 400V XW HO UNP/1	1015 °C

Light Technical (1/2)

MASTER MHN-SA

Order Code	Full Product Name	Chromaticity Coordinate Y (Nom)	Colour		
			Rendering Index (Nom)	Lumen Maintenance 1000 h (Nom)	Lumen Maintenance 2000 h (Nom)
20076100	MASTER MHN-SA 1800W/956 (P)SFC 400V	339	86	90 %	81 %
24183600	MASTER MHN-SA	366	81	96.5 %	92.5 %

Order Code	Full Product Name	Chromaticity Coordinate Y (Nom)	Colour		
			Rendering Index (Nom)	Lumen Maintenance 1000 h (Nom)	Lumen Maintenance 2000 h (Nom)
	2000W/956 400V XW HO UNP/1				

Light Technical (2/2)

Order Code	Full Product Name	Lumen Maintenance	Luminous Efficacy (rated)	Luminous Flux (Rated) (Nom)
		5000 h (Nom)	(Nom)	(Nom)
20076100	MASTER MHN-SA 1800W/956 (P)SFC 400V	71 %	86 lm/W	160000 lm

Order Code	Full Product Name	Lumen Maintenance	Luminous Efficacy (rated)	Luminous Flux (Rated) (Nom)
		5000 h (Nom)	(Nom)	(Nom)
24183600	MASTER MHN-SA 2000W/956 400V XW HO UNP/1	78 %	108 lm/W	226000 lm

