



# Energy savings, reformulated blend

## Energy Advantage T8 Value Line

Philips Energy Advantage T8 Value Line offers high energy savings in an environmentally responsible lamp without sacrificing performance.

### Benefits

### Features

### Application

### Warnings and Safety


### Versions



G13, T8

# Energy Advantage T8 Value Line

## Dimensional drawing



### Product

F32T8/VEA841/XEW ALTO 25W

F32T8/VEA841/EW/ALTO 28W

### Approval and Application

Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg

### General Information

Cap-Base	G13
Life 12-Hr Instant Start [Hrs]	38000 h
Life 12-Hr Programstart [Hrs]	44000 h
Life 3-Hr Instant Start [Hrs]	32000 h
Life 3-Hr Program Start [Hrs]	38000 h

### Light Technical

Color Code	Advantage 841
Color Designation	Value Energy Advantage 841
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	85

### Mechanical and Housing

Bulb Shape	T8
------------	----

### Approval and Application

Order Code	Full Product Name	Picogram Per Lumen Hour
424200	F32T8/VEA841/XEW ALTO 25W	29 pg/lm.h
424192	F32T8/VEA841/EW/ALTO 28W	27 pg/lm.h

## Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
424200	F32T8/VEA841/XEW ALTO 25W	25 W

Order Code	Full Product Name	Power (Rated) (Nom)
424192	F32T8/VEA841/EW/ALTO 28W	28 W

## Light Technical

Order Code	Full Product Name	Design Mean	
		Lumens	Luminous Flux (Nom)
424200	F32T8/VEA841/XEW ALTO 25W	2230 lm	2300 lm

Order Code	Full Product Name	Design Mean	
		Lumens	Luminous Flux (Nom)
424192	F32T8/VEA841/EW/ALTO 28W	2520 lm	2600 lm

## Energy Advantage T8 Value Line

