



Philips Twistline GU10

Twistline GU10

Bright, white accent light with superior energy savings. Philips Twistline GU10 Philips Halogen Twistline MR16 with GU10 base provide bright white accent light. The twist and lock base enables easy installation and a secure fit. Suited for track and recessed lighting applications.

Benefits

- Easy to install and maintain a secure fit.
- Highlight art and featured objects for decorative accent.

Features

- Bright, white light.
- Easy to use twist and lock base.
- Available in a variety of wattages operating on 120 volts.
- Available in 25,35 and 50 Watts.

Application

- Ideal for indoor recessed and track fixtures, floor and desk lamps.


Versions



GU10 2inch/50mm Clear

Twistline GU10

Dimensional drawing



Product	D (max)	C (max)
BC35 TWISTLINE GU10/FL25 TP	2 in	2-1/8 in
BC25 TWISTLINE GU10 / FL25	2 in	2-1/8 in


Controls and dimming	
Dimmable	Yes
Operating and electrical	
Voltage (Nom)	120 V
Starting Time (Nom)	0.0 s
General information	
Cap-Base	GU10
Nominal Lifetime (Nom)	2000 h
Operating Position	Universal
Rated Lifetime (Hours)	2000 h
Rated Lifetime (Years)	2 a
Light technical	
Correlated Color Temperature (Nom)	2800 K
Color Rendering Index (Nom)	100
Mechanical and housing	
Bulb Finish	Clear
Bulb Shape	MR16

Operating and electrical

Order Code	Full Product Name	Power (Nom)
415737	BC35 TWISTLINE GU10/FL25 TP	35 W
416933	BC25 TWISTLINE GU10 / FL25	25 W


Light technical

Order Code	Full Product Name	Beam Angle (Nom)	Luminous Intensity (Max)	Rated Beam Angle
415737	BC35 TWISTLINE GU10/FL25 TP	20 °	800 cd	-
416933	BC25 TWISTLINE GU10 / FL25	25 °	400 cd	25 °




Twistline GU10

Accent Diagrams



LDAC_HTWIST_Dichr_25D-Accent diagram

Beam Diagrams



LDBE_HTWIST_Dichr_25D-Beam diagram

