



# Spot of crisp white light

#### Accentline

Low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.

#### **Benefits**

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement costs due to longer burning hours

#### **Features**

- Superior quality of light with excellent color rendering (Ra=100)
- $\boldsymbol{\cdot}$  Low-pressure technology with UV-block glass allows use in luminaires without front glass
- · Dichroic coating
- · Universal burning position
- · Instant start

### **Application**


• Spot accent lighting to create the right ambiance in hotels, restaurants and shops

## **Accentline**

#### Versions



# Dimensional drawing



Product	D (max)	C (max)
Accent 35W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm
Accent 50W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

General Information	
Cap-Base	GU5.3
Rated Lifetime (Hours)	4,000 hour(s)
Switching Cycle	16,000
Nominal lifetime	4,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Beam Angle (Nom)	36 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Operating and Electrical	
Warm-up time to 60% light	Instant full light s
Voltage (Nom)	12 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16

#### **Light Technical**

Order Code	Full Product Name	Luminous Flux
926000850062	Accent 35W 4000h GU5.3 12V 36D 1CT/10X5F	430 lm
926000850063	Accent 50W 4000h GU5.3 12V 36D 1CT/10X5F	680 lm

## Operating and Electrical

#### **Accentline**

Order Code	Full Product Name	Power Consumption
926000850062	Accort 35W 4000h GUE 3 13V 36D 1CT/10V5E	3E ///

Order Code	Full Product Name	Power Consumption
926000850063	Accent 50W 4000h GU5.3 12V 36D 1CT/10X5F	50 W

#### **Approval and Application**

Order Code Full Product Name 1000 h   926000850062 Accent 35W 4000h GU5.3 12V 36D 1CT/ 37 kWh			Energy Consumption kWh/
926000850062 Accent 35W 4000h GU5.3 12V 36D 1CT/ 37 kWh	Order Code	Full Product Name	1000 h
	926000850062	Accent 35W 4000h GU5.3 12V 36D 1CT/	37 kWh
10X5F		10X5F	

		Energy Consumption kWh/
Order Code	Full Product Name	1000 h
926000850063	Accent 50W 4000h GU5.3 12V 36D 1CT/	53 kWh
	10X5F	

