



Spot of crisp white light

Accentline


Low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.

Benefits

Features

Application

Dimensional drawing



Product	D (max)	C (max)
Accentline 20W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm
Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm
Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

Approval and Application	
Energy Efficiency Label (EEL)	B
Controls and Dimming	
Dimmable	Yes
Operating and Electrical	
Voltage (Nom)	12 V
Starting Time (Nom)	0.0 s
Warm Up Time To 60% Light (Nom)	instant full light s
General Information	
Cap-Base	GU5.3
Nominal Lifetime (Nom)	4000 h
Life To 50% Failures (Nom)	4000 h
Operating Position	UNIVERSAL
Rated Lifetime (Hours)	4000 h
Switching Cycle	16000X
Light Technical	
Beam Angle (Nom)	36 °
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	100
Rated Beam Angle	36 °
Mechanical and Housing	
Bulb Shape	MR16

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
926000850061	Accentline 20W 4000h GU5.3 12V 36D 1CT/10X5F	21 kWh
926000850062	Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F	37 kWh
926000850063	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	53 kWh

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
926000850061	Accentline 20W 4000h GU5.3 12V 36D 1CT/10X5F	20 W
926000850062	Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F	35 W

Order Code	Full Product Name	Power (Rated) (Nom)
926000850063	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	50 W

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Intensity (Max)
926000850061	Accentline 20W 4000h GU5.3 12V 36D 1CT/10X5F	205 lm	500 cd
926000850062	Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F	430 lm	1000 cd

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Intensity (Max)
926000850063	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	680 lm	1500 cd

