



# Product Description

## Brilliantline Dichroic

Low-voltage, xenon gas-filled halogen burner with axial filament optically positioned in a glass reflector

### Benefits

- Cool beam as a large part of the heat generated is transmitted backwards through the back glass

### Features

- High-intensity beam with a clearly defined beam spread
- Reflector has a light-reflecting, light-transmitting hard dichroic coating
- Constant high quality and aesthetics maintained over lifetime
- Wide range of 35mm and 50 mm types
- UV-Block front glass
- Excellent colour rendering
- GU5.3 or GU4 base for extra retention in luminaire

### Application


- Ideally suited for accent, task and decorative lighting in shops, stores, hotels, restaurants etc.

Brilliantline Dichroic


Versions




Dimensional drawing



Product
Brilliantline Dichroic 50W GU5.3 12V 60D 1CT/10X5F



Accent Diagrams



## Beam Diagrams

$1/\lambda_{\text{max}}$	$= 2 \times 28$	h	E <sub>h</sub>	d(m)
--------------------------	-----------------	---	----------------	------

LDBE\_HDICHRO\_50W\_60D-Beam diagram

