



An energy-efficient solution

HF-Performer II for PL-T/C/R/L/TL5C lamps

HF-Performer EII PL-T/C/R/T5c is a sustainable, slim and high-frequency electronic ballast for a wide range of CFL- ni applications. It is ideal for applications where high energy efficiency is required. The HF-Performer EII range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2).The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.

Benefits

Features

Application

Versions



HF-P 122-42 PL-T/C/L/TL5C EII
220-240V

HF-Performer II for PL-T/C/R/L/TL5C lamps

Dimensional drawing

Product	D1	C1	A1	A2	B1	B2
HF-P 1 22-42 PL-T/C/L/	4.5	30.0	103.0	93.5	67.0	57.5
TL5C EII 220-240V	mm	mm	mm	mm	mm	mm
HF-P 2 22-42 PL-T/C/L/	4.5	30.0	103.0	93.5	67.0	57.5
TL5C EII 220-240V	mm	mm	mm	mm	mm	mm

Approval and Application	
Energy Efficiency Index	A2
Operating and Electrical	
Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V
General Information	
Lamp Type	PL-T/C/L/TL5C
System characteristics	
Rated Ballast-Lamp Power	22-42 W

General Information

Order Code	Full Product Name	Number Of Products On MCB (16A Type B) (Nom)	Number Of Lamps
913700630766	HF-P 1 22-42 PL-T/C/L/TL5C EII 220-240V	28	1 piece/unit

Order Code	Full Product Name	Number Of Products On MCB (16A Type B) (Nom)	Number Of Lamps
913700630866	HF-P 2 22-42 PL-T/C/L/TL5C EII 220-240V	12	2 piece/unit

