



# Dimming – a next step in energy saving

## HF-Regulator Intelligent Touch DALI for PL-T/C and TL5C

Intelligent high-frequency electronic dimming ballast, using DALI (Digital Addressable Lighting Interface according to IEC62386) or Touch and Dim push-button protocol for fluorescent lamps. Features Corridor Mode, programmable with Philips MultiOne. High-frequency operation improves light quality and lamp lifetime. Pre-empting upcoming legislation as it meets A1BAT requirements. The ballast is primarily designed for indoor application. For outdoor application, the luminaire should be minimum Class II need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.

### Benefits

- Programmed start: flicker-free ignition in 0.5 seconds and striation-free operation, no stroboscopic effects. Preheating the lamp electrodes enables the lamps to be switched on and off without reducing life
- Smart power ensures constant light, independent of mains fluctuations, and dimming from 3 to 100%
- Protected against excessive mains voltages, incorrect connections and incorrect lamp use

### Features


- Extremely low stand-by losses, controlled cut-off for dimming levels above 80%
- Combined with controls, additional energy savings can be achieved
- Stop circuit is activated within 5 seconds of lamp failure (safety stop), and ballast resets automatically after lamp replacement
- HF operation improves light quality and lamp lifetime
- Programmable Corridor Mode
- Compliant with European and Asian norms and suitable for emergency lighting systems

# HF-Regulator Intelligent Touch DALI for PL-T/C and TL5C

## Application

- Indoor general and task lighting applications in combination with lighting control systems (personal control, daylight linking and/or movement detection)

## Dimensional drawing



Product						
HF-Ri TD 1 26-42 PL-T/C E+	4.5	33.0	123.0	111.0	79.0	67.0
	mm	mm	mm	mm	mm	mm
HF-Ri TD 160 TL5C E+ 195-240V 50/60Hz						
HF-Ri TD 2 26-42 PL-T/C E+	4.5	33.0	123.0	111.0	79.0	67.0
	mm	mm	mm	mm	mm	mm

Product	A1	B1	C1	A2	B2	D1
HF-Ri TD 160 TL5C E+ 195-240V 50/60Hz	123.0 mm	79.0 mm	33.0 mm	111.0 mm	67.0 mm	4.5 mm



# HF-Regulator Intelligent Touch DALI for PL-T/C and TL5C

Operating and Electrical	
Input Frequency	50 to 60 Hz
Input Voltage	195-240 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Housing	L 123x79x33
Approval and Application	
Energy Efficiency Index	A1 BAT

## Operating and Electrical

Order Code	Full Product Name	Number of Products on MCB (16A Type B) (Nom)
913700684766	HF-Ri TD 1 26-42 PL-T/C E+	28
913700684866	HF-Ri TD 2 26-42 PL-T/C E+	12

Order Code	Full Product Name	Number of Products on MCB (16A Type B) (Nom)
913700761966	HF-Ri TD 160 TL5C E+ 195-240V 50/60Hz	12

