## **PHILIPS** Lighting



# Affordable, robust solution

#### HF-Selectalume II for PL-T/C Strain Relief

HF-Selectalume II independent version is the most cost-effective, reliable, slim and affordable fluorescent solution, with highly disruptive technology for energy saving, system flexibility and unsurpassed performance. The cost-saving HF-Selectalume II PLTC SR has a robust design which meets all relevant international safety and performance standards. The HF-S II strain relief is optimized mainly for PL-T/C lamps.HF-Selectalume II is intended for use with indoor lighting fixtures such as spotlights, downlights and recessed luminaries, which are largely used in office, retail, industry, hotel, restaurant and other applications.

#### Benefits

- The HF-SII 2x18/26W PL-T/C/T5c range has a robust design and meets internal safety, EMC and temperature protection requirements
- Automatic restart (after voltage dip or lamp replacement) ensures easy operation and hassle-free re-lamping (only for 2-lamp ballasts)
- DC emergency operation in line with IEC/EN 60598-2-22 luminaire norms (only for 2-lamp ballasts)
- Integrated terminal cover and strain relief

#### Features

- Complies with CE and ENEC (only for 2-lamp ballasts)
- Robust design over 70,000 hours lifetime at Ta=50 °C and over 50,000 on/off switching operations on one lamp (only for 2-lamp ballasts)
- Energy efficiency class: A2
- Active power factor correction to ensure constant light, irrespective of mainsvoltage fluctuations (only for 2-lamp ballasts)

#### HF-Selectalume II for PL-T/C Strain Relief

#### Application


- Commercial indoor lighting applications such as retail stores, office buildings, supermarkets, hotels, convenience stores and industrial premises with long operating hours (e.g. in corridors)
- In luminaires of protection class I and II such as spotlights, downlights and recessed
- Suitable for operation with movement-detection control systems like Philips OccuSwitch or in applications with frequentswitching activity (on/off) (only for 2lamp ballasts)

#### Versions



**GPPR HFSIISR 0001** 

#### Dimensional drawing



### Product D1 C1 A1 A2 B1 B2 HF-S 1/226 PL-T/C II SR 4.0 mm 32.0 mm 125.5 mm 93.5 mm 67.8 mm 57.5 mm 220-240V 50/60Hz

#### **Product details**



HF-Selectalume II for PL-T/C Strain Relief



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2023, August 2 - data subject to change