



Product Description

HalogenA IDE

Mains-voltage high-wattage double-envelope giving a white halogen light

Benefits

- Bright, sparkling halogen light
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Low replacement costs due to long lifetime

Features

- Quartz burner with a linear tungsten filament in a single-ended thermal-shock-resistant clear glass tubular envelope
- High luminous efficacy
- Excellent colour rendering

Application


- Typical application: outdoor floodlighting such as sport grounds, car parks, building sites, harbours and airport aprons
- Also used in Indoor applications: public halls, factories, sport halls etc.

Versions



HalogenA IDE

Dimensional drawing



Product	D (max)	C (max)
HalogenA IDE 500W E40 230V CL 1CT/6	38.5 mm	216 mm
HalogenA IDE 1000W E40 230V CL 1CT/6	38.5 mm	256 mm

