



Incandescent Infrared Reflector Flood

Reflector Infrared BR40,PAR38

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators that produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.

Benefits

- No warm-up time required.
- Decreased heat loss.

Features

- Instantaneous heat
- Radiated heat only warms object to be heated
- Build-in reflector for radiant energy control

Application

- Ideal for bathroom recessed fixtures and commercial and industrial applications.

Reflector Infrared BR40,PAR38

Versions



E26/E27, PAR38




PAR 38 IR E27 Red




Single Contact Medium Screw
BR40 Clear

Dimensional drawing



Product	D	C (max)	C1 (max)
Par38 115-125V E26 1CT/12	121 mm	135 mm	123 mm
IR175R/PAR 120V 12/1	121 mm	135 mm	123 mm



Product
250BR40 IR/1 120V 4/1

General information

Rated Lifetime (Hours)	5000 h
------------------------	--------

Reflector Infrared BR40,PAR38

Controls and dimming

Order Code	Full Product Name	Dimmable
405183	Par38 115-125V E26 1CT/12	Yes
232306	IR175R/PAR 120V 12/1	Yes

Order Code	Full Product Name	Dimmable
203836	250BR40 IR/1 120V 4/1	-

Operating and electrical

Order Code	Full Product Name	Voltage (Nom)	Power (Nom)
405183	Par38 115-125V E26 1CT/12	115-125 V	175 W
232306	IR175R/PAR 120V 12/1	115-125 V	175 W

Order Code	Full Product Name	Voltage (Nom)	Power (Nom)
203836	250BR40 IR/1 120V 4/1	120 V	250 W

General information

Order Code	Full Product Name	Nominal			
		Cap-Base	Lifetime (Nom)	Main Application	Operating Position
405183	Par38 115-125V E26 1CT/12	E26/50X39	5000 h	Infrared Industrial	Universal
232306	IR175R/PAR 120V 12/1	E26	5000 h	Infrared Industrial	H45

Order Code	Full Product Name	Nominal			
		Cap-Base	Lifetime (Nom)	Main Application	Operating Position
203836	250BR40 IR/1 120V 4/1	E26	-	Infrared	Universal

Light technical

Order Code	Full Product Name	Beam Description	Color Designation
405183	Par38 115-125V E26 1CT/12	-	C
232306	IR175R/PAR 120V 12/1	-	R

Order Code	Full Product Name	Beam Description	Color Designation
203836	250BR40 IR/1 120V 4/1	Spot	-

Mechanical and housing

Order Code	Full Product Name	Bulb Finish	Bulb Material	Bulb Shape
405183	Par38 115-125V E26 1CT/12	Clear	Hard Glass	PAR38
232306	IR175R/PAR 120V 12/1	Red	Hard Glass	PAR38

Order Code	Full Product Name	Bulb Finish	Bulb Material	Bulb Shape
203836	250BR40 IR/1 120V 4/1	Clear	-	BR40

