



# Rough Service Incandescent Lamps

## Rough / Vibration Service

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

### Benefits

- An exceptionally strong filament resists shocks, bumps and vibrations.

### Features

- Rugged design resists vibration.
- Incandescent, vacuum or gas-filled lamp with clear or inside-frosted bulb.
- Single coil filament.
- Medium or mogul screw base.
- Available in 60W and 75W versions in clear and frosted. Also available in 100W TuffGuard version.

### Application

- Ideal for use in worklights and other fixtures subject to rough handling. Suited for Ships, engine rooms, mines, elevators public transport buses and trains and other industrial applications.

## Rough / Vibration Service

### Versions



E26, A21, Frosted

### Dimensional drawing



Product	D	C (max)
100A/RS 250V 60PK	2.625 in	5.312 in

