



EB-E electronic ballasts for TL-D lamps

EB-E Electronic ballasts for TL-D lamps (India)

Compact, lightweight, high-frequency electronic ballast for TL-D lamps

Benefits

- More than 25% reduction in energy consumption compared with conventional gear at equal luminous flux
- Suitable for modern low-height battens thanks to slim construction and 21 mm height

Features


- Flicker-free instant start
- High power factor
- Minimum ignition voltage of 90 V

Application

- Home
- Retail
- Areas with low-voltage problems

EB-E Electronic ballasts for TL-D lamps (India)

Versions



EBE 136 TLD 240 OEM

EB-B Slim136 TLD 220

Dimensional drawing

A2

Product	D1	C1	A1	A2	B1
EBE (Slim) 136 TLD 240V	4.0 mm	21.0 mm	265.0 mm	253.3 mm	30.0 mm

A2

Product	D1	C1	A1	A2	B1
EBE 236 TLD 240	4.0 mm	30.0 mm	211.0 mm	200.0 mm	40.0 mm

Approval and Application

Energy Efficiency Index Not specified

Operating and Electrical

Input Frequency 50 to 60 Hz

General Information

Lamp Type TL-D

System characteristics

Rated Ballast-Lamp Power 36 W

EB-E Electronic ballasts for TL-D lamps (India)

Operating and Electrical

Order Code	Full Product Name	Input Voltage
913702242021	EBE (Slim) 136 TLD 240V	240 V

Order Code	Full Product Name	Input Voltage
913702242112	EBE 236 TLD 240	220 to 240 V

General Information

Order Code	Full Product Name	Number Of Lamps
913702242021	EBE (Slim) 136 TLD 240V	1 piece/unit

Order Code	Full Product Name	Number Of Lamps
913702242112	EBE 236 TLD 240	2 piece/unit

