



PowerBalance – sustainable performance

PowerBalance RC600B

When it comes to lighting an office space with LED luminaires, people are willing to invest in sustainability, but only at reasonable cost. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. PowerBalance is an attractively priced LED luminaire specially developed to meet all office requirements. It consumes significantly less energy while offering longer life of the light source, resulting in lower operational cost compared to traditional luminaires.

Benefits

- · Operational cost saving
- · Energy-efficient
- · Office norm-compliant

Features

- · Advanced LED technology
- Smart Pyramid Optics (SPO)
- Dedicated lumen package for office application

Application

- · General lighting in offices
- · Circulation areas

Specifications

| Туре | RC600B | Ceiling type | Exposed T-bar ceiling |
|------|--------|--------------|-----------------------|
| | | | Bandraster ceiling |

PowerBalance RC600B

| Light source | Philips Fortimo LEDline 3R | |
|-----------------------|----------------------------|--|
| Power | LED31S: 40 W (4000 K) | |
| | LED40S: 52 W (4000 K) | |
| Beam angle | 85º | |
| Correlated Color | 3000 or 4000 K | |
| Temperature | | |
| Color Rendering Index | 80 | |
| Maintenance of lumen | 30,000 hours at 25°C | |
| output - L90 | | |
| Maintenance of lumen | 50,000 hours at 25°C | |
| output - L70 | | |
| Operating temperature | +10°C < T | |
| range | | |

| Driver | Built-in |
|--|---|
| Mains voltage | 230 or 240 V / 50 Hz |
| Dimming | Compatible with DALI controllers |
| Controls system input | DALI |
| Options | Lighting controls: Actilume (ACL) |
| | Airhandling |
| Material | Housing: zinc-coated steel |
| | Rim: post lacquered |
| | Optics: plastic |
| Color | White (WH) |
| Maintenance | Optical module sealed for life; no internal cleaning required |
| nstallation Exposed ceilings: in lay, no brackets needed | |

Versions



RC600B W30XL120

RC600B W30XL120

PowerBalance RC600B

| Application Conditions | |
|--------------------------------|--------------------|
| Maximum dimming level | 1% |
| Suitable for random switching | Yes |
| | |
| Approval and Application | |
| Mech. impact protection code | IK03 |
| Ingress protection code | IP20 |
| | |
| Controls and Dimming | |
| Dimmable | Yes |
| Operating and Electrical | |
| Input Voltage | 220/240 V |
| input voltage | 220/240 V |
| General Information | |
| Beam angle of light source | _ ° |
| CE mark | CE mark |
| Protection class IEC | Safety class I (I) |
| Optical cover/lens type | 0 |
| Driver included | Yes |
| ENEC mark | ENEC mark |
| Flammability mark | NO |
| Glow-wire test | 650/30 |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Optic type | 100 |
| | |
| Initial Performance (IEC Compl | iant) |
| Initial chromaticity | SDCM<4 |
| Init. Corr. Colour Temperature | 4000 K |
| Init. Colour rendering index | >80 |
| Luminous flux tolerance | +/-10% |
| | |
| Mechanical and Housing | |
| Colour | White |

Application Conditions

| Order Code | Full Product Name | Ambient temperature range |
|--------------|---------------------------------------|---------------------------|
| 911401800397 | RC600B LED30S/840 PSD W30L120 CAU | -20 to +40 °C |
| 911401800697 | RC600B LED40S/840 PSD W30L120 CAU | -20 to +40 °C |
| 911401801297 | RC600B LED40S/840 PSD ACW W30L120 CAU | 0 to +40 °C |
| 911401801097 | RC600B LED40S/840 PSD ACW W60L60 CAU | 0 to +40 °C |
| 911401899999 | RC600B LED30S/840 PSD W60L60 CAU | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | | Initial LED | | |
|--------------|-------------------|-------------|---------------|---------------|
| | | luminaire | Initial | Initial input |
| Order Code | Full Product Name | efficacy | luminous flux | power |
| 911401800397 | RC600B LED30S/840 | 129.17 lm/W | 3100 lm | 24 W |
| | PSD W30L120 CAU | | | |
| 911401800697 | RC600B LED40S/840 | 125 lm/W | 4000 lm | 32 W |
| | PSD W30L120 CAU | | | |
| 911401801297 | RC600B LED40S/840 | 160 lm/W | 4000 lm | 25 W |
| | PSD ACW W30L120 | | | |
| | CAU | | | |
| | | | | |

| | | Initial LED | | |
|--------------|-------------------|-------------|---------------|---------------|
| | | luminaire | Initial | Initial input |
| Order Code | Full Product Name | efficacy | luminous flux | power |
| 911401801097 | RC600B LED40S/840 | 160 lm/W | 4000 lm | 25 W |
| | PSD ACW W60L60 | | | |
| | CAU | | | |
| 911401899999 | RC600B LED30S/840 | 129.17 lm/W | 3100 lm | 24 W |
| | PSD W60L60 CAU | | | |
| | | | | |

PowerBalance RC600B



© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.