



PowerBalance – sustainable performance

PowerBalance RC600B

When it comes to lighting an office space with LED luminaires, people are willing to invest in sustainability, but only at reasonable cost. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. PowerBalance is an attractively priced LED luminaire specially developed to meet all office requirements. It consumes significantly less energy while offering longer life of the light source, resulting in lower operational cost compared to traditional luminaires.

Benefits

- Operational cost saving
- Energy-efficient
- Office norm-compliant

Features

- Advanced LED technology
- Smart Pyramid Optics (SPO)
- Dedicated lumen package for office application

Application

- General lighting in offices
- Circulation areas

Specifications


Type	RC600B	Ceiling type	Exposed T-bar ceiling Bandrastrer ceiling
------	--------	--------------	--

PowerBalance RC600B

Light source	Philips Fortimo LEDline 3R
Power	LED31S: 40 W (4000 K) LED40S: 52 W (4000 K)
Beam angle	85°
Correlated Color Temperature	3000 or 4000 K
Color Rendering Index	80
Maintenance of lumen output - L90	30,000 hours at 25°C
Maintenance of lumen output - L70	50,000 hours at 25°C
Operating temperature range	+10°C < T

Driver	Built-in
Mains voltage	230 or 240 V / 50 Hz
Dimming	Compatible with DALI controllers
Controls system input	DALI
Options	Lighting controls: Actilume (ACL) Airhandling
Material	Housing: zinc-coated steel Rim: post lacquered Optics: plastic
Color	White (WH)
Maintenance	Optical module sealed for life; no internal cleaning required
Installation	Exposed ceilings: in lay, no brackets needed

Versions



RC600B W30XL120

RC600B W30XL120

PowerBalance RC600B

Application Conditions

Maximum dim level	1%
Suitable for random switching	Yes

Approval and Application

Mech. impact protection code	IK03
Ingress protection code	IP20

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Input Voltage	220/240 V
---------------	-----------

General Information

Beam angle of light source	- °
CE mark	CE mark
Protection class IEC	Safety class I (I)
Optical cover/lens type	O
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	NO
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Optic type	100

Initial Performance (IEC Compliant)

Initial chromaticity	SDCM<4
Init. Corr. Colour Temperature	4000 K
Init. Colour Rendering Index	>80
Luminous flux tolerance	+/-10%

Mechanical and Housing

Colour	White
--------	-------

Application Conditions

Order Code	Full Product Name	Ambient temperature range
911401800297	RC600B LED40S/840 PSD W60L60 CAU	-20 to +40 °C
911401801097	RC600B LED40S/840 PSD ACW W60L60 CAU	0 to +40 °C
911401899999	RC600B LED30S/840 PSD W60L60 CAU	-20 to +40 °C
911401800397	RC600B LED30S/840 PSD W30L120 CAU	-20 to +40 °C
911401800697	RC600B LED40S/840 PSD W30L120 CAU	-20 to +40 °C
911401801297	RC600B LED40S/840 PSD ACW W30L120 CAU	0 to +40 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401800297	RC600B LED40S/840 PSD W60L60 CAU	125 lm/W	4000 lm	32 W
911401801097	RC600B LED40S/840 PSD ACW W60L60 CAU	160 lm/W	4000 lm	25 W
911401899999	RC600B LED30S/840 PSD W60L60 CAU	129.17 lm/W	3100 lm	24 W
911401800397	RC600B LED30S/840 PSD W30L120 CAU	129.17 lm/W	3100 lm	24 W

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401800697	RC600B LED40S/840 PSD W30L120 CAU	125 lm/W	4000 lm	32 W
911401801297	RC600B LED40S/840 PSD ACW W30L120 CAU	160 lm/W	4000 lm	25 W

PowerBalance RC600B

