



A smooth design solution for a seamless look

PAR30S LED Single Optic Lamps with AirFlux Technology

Philips PAR30S LED Single Optic Lamps with AirFlux Technology provide superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

Avantages

- Will not fade colors, avoids inventory spoilage
- Lowers maintenance costs by reducing re-lamp frequency
- 5-year limited warranty**
- ** For details see: http://www.usa.lighting.philips.com/connect/tools_literature/warranties.wpd.

Fonctions

- Retail Optic reduces glare to improve shopper experience
- 25,000-hour rated average life*
- 12W PAR30S saves 63 watts when compared to a 75W halogen PAR30S
- 83 CRI for excellent color rendering
- Virtually UV/IR free in the beam
- Contains no mercury

Application

- Ideal for general and accent lighting in retail, hospitality and office spaces.

PAR30S LED Single Optic Lamps with AirFlux Technology

Mises en garde et sécurité

- Suitable for use in damp locations.
- Not for use in totally enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.
- CAUTION: Risk of electric shock— do not use where directly exposed to water
- NOTES: This device complies with Part 18 of the FCC rule. This product may cause interference with other devices. If interference occurs, change the location of the products involved. This RFLD device complies with Canadian ICES-005.

Versions








Schéma dimensionnel



Product	D	C
12PAR30S/EXPERTCOLOR/F40/940/DIM	120,7 mm	134,6 mm
12PAR30S/EXPERTCOLOR/S10/927/DIM	94,8 mm	93,1 mm
12PAR30S/EXPERTCOLOR RETAIL/F25/930/DIMB	94,8 mm	93,1 mm
12PAR30S/EXPERTCOLOR RETAIL/F40/930/DIM	94,8 mm	93,1 mm
12PAR30S/EXPERTCOLOR RETAIL/S10/930/DIM	94,8 mm	93,1 mm
12PAR30S/EXPERTCOLOR RETAIL/F25/930/DIM	94,8 mm	93,1 mm
12PAR30S/EXPERTCOLOR/F25/927/DIM	94,8 mm	93,1 mm
12PAR30S/EXPERTCOLOR/F25/940/DIM	120,7 mm	134,6 mm
12PAR30S/EXPERTCOLOR/S10/940/DIM/120V	94,8 mm	93,1 mm
12PAR30S/EXPERTCOLOR/F40/927/DIM	94,8 mm	116,1 mm

PAR30S LED Single Optic Lamps with AirFlux Technology

Schéma dimensionnel



Product	D	C
12PAR30L/EXPERTCOLOR/F40/927/DIM	94,8 mm	93,1 mm
12PAR30L/EXPERTCOLOR/F25/927/DIM	94,8 mm	93,1 mm
12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM	94,8 mm	116,1 mm
12PAR30L/EXPERTCOLOR RETAIL/F25/930/DIM	94,8 mm	116,1 mm
12PAR30L/EXPERTCOLOR RETAIL/S10/930/DIM	94,8 mm	116,1 mm
12PAR30L/EXPERTCOLOR/F40/940/DIM	94,8 mm	116,1 mm
12PAR30L/EXPERTCOLOR/F25/940/DIM	94,8 mm	116,1 mm

Product	D	C
10PAR30L/LED/830/F25/DIM/ULW/120V 6/1FB	94 mm	118 mm
10PAR30L/LED/840/F40/DIM/ULW/120V 6/1FB	94 mm	118 mm
10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB	94 mm	118 mm
10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB	94 mm	118 mm
10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB	94 mm	118 mm
10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB	94 mm	118 mm

Product	D	C
10PAR30S/LED/830/F40/DIM/ULW/120V 6/1FB	94 mm	93 mm
10PAR30S/LED/840/F40/DIM/ULW/120V 6/1FB	94 mm	93 mm
10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB	94 mm	93 mm
10PAR30S/LED/827/F40/DIM/ULW/120V 6/1FB	94 mm	93 mm
10PAR30S/LED/827/F25/DIM/ULW/120V 6/1FB	94 mm	93 mm
10PAR30S/LED/830/F25/DIM/ULW/120V 6/1FB	94 mm	93 mm

Commandes et gradation

Intensité réglable Yes

Fonctionnement et électricité

Tension (nom.) 120 V

Équivalent de puissance 75 W

Temps d'allumage (nom.) 0,5 s

Renseignements généraux

Culot E26

Données techniques sur l'éclairage

Llmf à la fin de la durée nominale (nom.) 70 %

Fonctionnement et électricité

PAR30S LED Single Optic Lamps with AirFlux Technology

Order Code	Full Product Name	Fréquence d'entrée	Puissance (nominale) (nom.)
471037	12PAR30L/EC RETAIL/S10/930/DIM 6/1	60 Hz	12 W
471045	12PAR30L/EC RETAIL/F25/930/DIM 6/1	60 Hz	12 W
471052	12PAR30L/EC RETAIL/F40/930/DIM 6/1	60 Hz	12 W
471060	12PAR30S/EC RETAIL/S10/930/DIM 6/1	60 Hz	12 W
470914	12PAR30S/EC/F40/927/DIM/120V 6/1	60 Hz	12 W
470970	12PAR30L/EC/F25/940/DIM/120V 6/1	60 Hz	12 W
470988	12PAR30L/EC/F40/940/DIM/120V 6/1	60 Hz	12 W
471078	12PAR30S/EC RETAIL/F25/930/DIM 6/1	60 Hz	12 W
471086	12PAR30S/EC RETAIL/F40/930/DIM 6/1	60 Hz	12 W
470898	12PAR30S/EC/S10/927/DIM/120V 6/1	60 Hz	12 W
470954	12PAR30L/EC/F25/927/DIM/120V 6/1	60 Hz	12 W
470962	12PAR30L/EC/F40/927/DIM/120V 6/1	60 Hz	12 W
471789	12PAR30S/EXPERTCOLOR/S10/940/DIM/120V	60 Hz	12 W
471094	12PAR30S/EC RETAIL/F25/930/DIM 6/1	60 Hz	12 W
529768	10PAR30S/LED/827/F25/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W

Order Code	Full Product Name	Fréquence d'entrée	Puissance (nominale) (nom.)
529776	10PAR30S/LED/830/F25/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W
529784	10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W
529792	10PAR30S/LED/827/F40/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W
529800	10PAR30S/LED/830/F40/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W
529818	10PAR30S/LED/840/F40/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W
529701	10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W
529719	10PAR30L/LED/830/F25/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W
529727	10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W
529735	10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W
529743	10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W
529750	10PAR30L/LED/840/F40/DIM/ULW/120V 6/1FB	50 à 60 Hz	10 W
470906	12PAR30S/EC/F25/927/DIM/120V 6/1	60 Hz	12 W
470930	12PAR30S/EC/F25/940/DIM/120V 6/1	60 Hz	12 W
470948	12PAR30S/EC/F40/940/DIM/120V 6/1	60 Hz	12 W

Renseignements généraux

Order Code	Full Product Name	Durée de vie (nom.)	Durée de vie (en heures)	Cycle de commutation
471037	12PAR30L/EC RETAIL/S10/930/DIM 6/1	25000 h	25000 h	50 000 x
471045	12PAR30L/EC RETAIL/F25/930/DIM 6/1	25000 h	25000 h	50 000 x
471052	12PAR30L/EC RETAIL/F40/930/DIM 6/1	25000 h	25000 h	50 000 x
471060	12PAR30S/EC RETAIL/S10/930/DIM 6/1	25000 h	25000 h	50 000 x
470914	12PAR30S/EC/F40/927/DIM/120V 6/1	40000 h	40000 h	50 000 x
470970	12PAR30L/EC/F25/940/DIM/120V 6/1	40000 h	40000 h	50 000 x
470988	12PAR30L/EC/F40/940/DIM/120V 6/1	40000 h	40000 h	50 000 x

Order Code	Full Product Name	Durée de vie (nom.)	Durée de vie (en heures)	Cycle de commutation
471078	12PAR30S/EC RETAIL/F25/930/DIM 6/1	25000 h	25000 h	50 000 x
471086	12PAR30S/EC RETAIL/F40/930/DIM 6/1	25000 h	25000 h	50 000 x
470898	12PAR30S/EC/S10/927/DIM/120V 6/1	40000 h	40000 h	50 000 x
470954	12PAR30L/EC/F25/927/DIM/120V 6/1	40000 h	40000 h	50 000 x
470962	12PAR30L/EC/F40/927/DIM/120V 6/1	40000 h	40000 h	50 000 x
471789	12PAR30S/EXPERTCOLOR/S10/940/DIM/120V	40000 h	40000 h	50 000 x
471094	12PAR30S/EC RETAIL/F25/930/DIM 6/1	25000 h	25000 h	50 000 x

PAR30S LED Single Optic Lamps with AirFlux Technology

Order Code	Full Product Name	Durée de vie (nom.)	Durée de vie (en heures)	Cycle de commutation	Order Code	Full Product Name	Durée de vie (nom.)	Durée de vie (en heures)	Cycle de commutation
529768	10PAR30S/LED/827/F25/DIM/ULW/120V 6/1FB	25000 h	25000 h	-	529727	10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB	25000 h	25000 h	-
529776	10PAR30S/LED/830/F25/DIM/ULW/120V 6/1FB	25000 h	25000 h	-	529735	10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB	25000 h	25000 h	-
529784	10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB	25000 h	25000 h	-	529743	10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB	25000 h	25000 h	-
529792	10PAR30S/LED/827/F40/DIM/ULW/120V 6/1FB	25000 h	25000 h	-	529750	10PAR30L/LED/840/F40/DIM/ULW/120V 6/1FB	25000 h	25000 h	-
529800	10PAR30S/LED/830/F40/DIM/ULW/120V 6/1FB	25000 h	25000 h	-	470906	12PAR30S/EC/F25/927/DIM/120V 6/1	40000 h	40000 h	50 000 x
529818	10PAR30S/LED/840/F40/DIM/ULW/120V 6/1FB	25000 h	25000 h	-	470930	12PAR30S/EC/F25/940/DIM/120V 6/1	40000 h	40000 h	50 000 x
529701	10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB	25000 h	25000 h	-	470948	12PAR30S/EC/F40/940/DIM/120V 6/1	40000 h	40000 h	50 000 x
529719	10PAR30L/LED/830/F25/DIM/ULW/120V 6/1FB	25000 h	25000 h	-					

Données techniques sur l'éclairage (1/2)

Order Code	Full Product Name	Angle du faisceau (nom.)	Code de couleur	Indice de rendu des couleurs		Flux lumineux (nom.)	Flux lumineux (nominal)	Intensité lumineuse (nom.)
				Température selon la couleur corrélée (nom.)	Flux lumineux (nom.)			
471037	12PAR30L/EC RETAIL/S10/930/DIM 6/1	10°	930	3000 K	90	880 lm	880 lm	10000 cd
471045	12PAR30L/EC RETAIL/F25/930/DIM 6/1	25°	930	3000 K	90	880 lm	880 lm	4500 cd
471052	12PAR30L/EC RETAIL/F40/930/DIM 6/1	40°	930	3000 K	90	880 lm	880 lm	2000 cd
471060	12PAR30S/EC RETAIL/S10/930/DIM 6/1	10°	930	3000 K	90	880 lm	880 lm	10000 cd
470914	12PAR30S/EC/F40/927/DIM/120V 6/1	40°	927	2700 K	95	850 lm	850 lm	1800 cd
470970	12PAR30L/EC/F25/940/DIM/120V 6/1	25°	940	4000 K	95	950 lm	950 lm	4800 cd
470988	12PAR30L/EC/F40/940/DIM/120V 6/1	40°	940	4000 K	95	950 lm	950 lm	2100 cd
471078	12PAR30S/EC RETAIL/F25/930/DIM 6/1	25°	930	3000 K	90	880 lm	880 lm	4500 cd
471086	12PAR30S/EC RETAIL/F40/930/DIM 6/1	40°	930	3000 K	90	880 lm	880 lm	2000 cd
470898	12PAR30S/EC/S10/927/DIM/120V 6/1	10°	927	2700 K	95	850 lm	850 lm	10000 cd
470954	12PAR30L/EC/F25/927/DIM/120V 6/1	25°	927	2700 K	95	850 lm	850 lm	4200 cd
470962	12PAR30L/EC/F40/927/DIM/120V 6/1	40°	927	2700 K	95	850 lm	850 lm	1800 cd
471789	12PAR30S/EXPERTCOLOR/S10/940/DIM/120V	10°	940	4000 K	95	950 lm	950 lm	10500 cd
471094	12PAR30S/EC RETAIL/F25/930/DIM 6/1	25°	930	3000 K	90	880 lm	880 lm	4500 cd
529768	10PAR30S/LED/827/F25/DIM/ULW/120V 6/1FB	25°	827	2700 K	80	800 lm	800 lm	3300 cd
529776	10PAR30S/LED/830/F25/DIM/ULW/120V 6/1FB	25°	830	3000 K	80	850 lm	850 lm	3300 cd
529784	10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB	25°	840	4000 K	80	850 lm	850 lm	3300 cd
529792	10PAR30S/LED/827/F40/DIM/ULW/120V 6/1FB	40°	827	2700 K	80	800 lm	800 lm	1600 cd
529800	10PAR30S/LED/830/F40/DIM/ULW/120V 6/1FB	40°	830	3000 K	80	850 lm	850 lm	1600 cd
529818	10PAR30S/LED/840/F40/DIM/ULW/120V 6/1FB	40°	840	4000 K	80	850 lm	850 lm	1600 cd

PAR30S LED Single Optic Lamps with AirFlux Technology

Order Code	Full Product Name	Angle du faisceau (nom.)	Code de couleur	Température selon la couleur corrélée (nom.)	Indice de rendu des couleurs (nom.)	Flux lumineux (nom.)	Flux lumineux (nominal)	Intensité lumineuse (nom.)
529701	10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB	25 °	827	2700 K	80	800 lm	800 lm	3300 cd
529719	10PAR30L/LED/830/F25/DIM/ULW/120V 6/1FB	25 °	830	3000 K	80	850 lm	850 lm	3300 cd
529727	10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB	25 °	840	4000 K	80	850 lm	850 lm	3300 cd
529735	10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB	40 °	827	2700 K	80	800 lm	800 lm	1600 cd
529743	10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB	40 °	830	3000 K	80	850 lm	850 lm	1600 cd
529750	10PAR30L/LED/840/F40/DIM/ULW/120V 6/1FB	40 °	840	4000 K	80	850 lm	850 lm	1600 cd
470906	12PAR30S/EC/F25/927/DIM/120V 6/1	25 °	927	2700 K	95	850 lm	850 lm	4200 cd
470930	12PAR30S/EC/F25/940/DIM/120V 6/1	25 °	940	4000 K	95	950 lm	950 lm	4800 cd
470948	12PAR30S/EC/F40/940/DIM/120V 6/1	40 °	940	4000 K	95	950 lm	950 lm	2100 cd

Données techniques sur l'éclairage (2/2)

Order Code	Full Product Name	Angle de faisceau nominal	Order Code	Full Product Name	Angle de faisceau nominal
471037	12PAR30L/EC RETAIL/S10/930/DIM 6/1	10 °	529776	10PAR30S/LED/830/F25/DIM/ULW/120V 6/1FB	25 °
471045	12PAR30L/EC RETAIL/F25/930/DIM 6/1	25 °	529784	10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB	25 °
471052	12PAR30L/EC RETAIL/F40/930/DIM 6/1	40 °	529792	10PAR30S/LED/827/F40/DIM/ULW/120V 6/1FB	40 °
471060	12PAR30S/EC RETAIL/S10/930/DIM 6/1	10 °	529800	10PAR30S/LED/830/F40/DIM/ULW/120V 6/1FB	40 °
470914	12PAR30S/EC/F40/927/DIM/120V 6/1	40 °	529818	10PAR30S/LED/840/F40/DIM/ULW/120V 6/1FB	40 °
470970	12PAR30L/EC/F25/940/DIM/120V 6/1	25 °	529701	10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB	25 °
470988	12PAR30L/EC/F40/940/DIM/120V 6/1	40 °	529719	10PAR30L/LED/830/F25/DIM/ULW/120V 6/1FB	25 °
471078	12PAR30S/EC RETAIL/F25/930/DIM 6/1	25 °	529727	10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB	25 °
471086	12PAR30S/EC RETAIL/F40/930/DIM 6/1	40 °	529735	10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB	40 °
470898	12PAR30S/EC/S10/927/DIM/120V 6/1	10 °	529743	10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB	40 °
470954	12PAR30L/EC/F25/927/DIM/120V 6/1	25 °	529750	10PAR30L/LED/840/F40/DIM/ULW/120V 6/1FB	40 °
470962	12PAR30L/EC/F40/927/DIM/120V 6/1	40 °	470906	12PAR30S/EC/F25/927/DIM/120V 6/1	25 °
471789	12PAR30S/EXPERTCOLOR/S10/940/DIM/120V	10 °	470930	12PAR30S/EC/F25/940/DIM/120V 6/1	25 °
471094	12PAR30S/EC RETAIL/F25/930/DIM 6/1	25 °	470948	12PAR30S/EC/F40/940/DIM/120V 6/1	40 °
529768	10PAR30S/LED/827/F25/DIM/ULW/120V 6/1FB	25 °			

Mécanique et boîtier

Order Code	Full Product Name	Forme de l'ampoule	Order Code	Full Product Name	Forme de l'ampoule
471037	12PAR30L/EC RETAIL/S10/930/DIM 6/1	PAR30L	470898	12PAR30S/EC/S10/927/DIM/120V 6/1	PAR30S
471045	12PAR30L/EC RETAIL/F25/930/DIM 6/1	PAR30L	470954	12PAR30L/EC/F25/927/DIM/120V 6/1	PAR30L
471052	12PAR30L/EC RETAIL/F40/930/DIM 6/1	PAR30L	470962	12PAR30L/EC/F40/927/DIM/120V 6/1	PAR30L
471060	12PAR30S/EC RETAIL/S10/930/DIM 6/1	PAR30S	471789	12PAR30S/EXPERTCOLOR/S10/940/DIM/120V	PAR30S
470914	12PAR30S/EC/F40/927/DIM/120V 6/1	PAR30S	471094	12PAR30S/EC RETAIL/F25/930/DIM 6/1	PAR30S
470970	12PAR30L/EC/F25/940/DIM/120V 6/1	PAR30L	529768	10PAR30S/LED/827/F25/DIM/ULW/120V 6/1FB	PAR30S
470988	12PAR30L/EC/F40/940/DIM/120V 6/1	PAR30L	529776	10PAR30S/LED/830/F25/DIM/ULW/120V 6/1FB	PAR30S
471078	12PAR30S/EC RETAIL/F25/930/DIM 6/1	PAR30S	529784	10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB	PAR30S
471086	12PAR30S/EC RETAIL/F40/930/DIM 6/1	PAR30S	529792	10PAR30S/LED/827/F40/DIM/ULW/120V 6/1FB	PAR30S



PAR30S LED Single Optic Lamps with AirFlux Technology

Order Code	Full Product Name	Forme de l'ampoule
529800	10PAR30S/LED/830/F40/DIM/ULW/120V 6/1FB	PAR30S
529818	10PAR30S/LED/840/F40/DIM/ULW/120V 6/1FB	PAR30S
529701	10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB	PAR30L
529719	10PAR30L/LED/830/F25/DIM/ULW/120V 6/1FB	PAR30L
529727	10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB	PAR30L
529735	10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB	PAR30L



Order Code	Full Product Name	Forme de l'ampoule
529743	10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB	PAR30L
529750	10PAR30L/LED/840/F40/DIM/ULW/120V 6/1FB	PAR30L
470906	12PAR30S/EC/F25/927/DIM/120V 6/1	PAR30S
470930	12PAR30S/EC/F25/940/DIM/120V 6/1	PAR30S
470948	12PAR30S/EC/F40/940/DIM/120V 6/1	PAR30S

Température




Order Code	Full Product Name	T boîtier maximum (nom.)
471037	12PAR30L/EC RETAIL/S10/930/DIM 6/1	85 °C
471045	12PAR30L/EC RETAIL/F25/930/DIM 6/1	85 °C
471052	12PAR30L/EC RETAIL/F40/930/DIM 6/1	85 °C
471060	12PAR30S/EC RETAIL/S10/930/DIM 6/1	90 °C
470914	12PAR30S/EC/F40/927/DIM/120V 6/1	90 °C
470970	12PAR30L/EC/F25/940/DIM/120V 6/1	85 °C
470988	12PAR30L/EC/F40/940/DIM/120V 6/1	85 °C
471078	12PAR30S/EC RETAIL/F25/930/DIM 6/1	90 °C
471086	12PAR30S/EC RETAIL/F40/930/DIM 6/1	90 °C
470898	12PAR30S/EC/S10/927/DIM/120V 6/1	90 °C
470954	12PAR30L/EC/F25/927/DIM/120V 6/1	85 °C
470962	12PAR30L/EC/F40/927/DIM/120V 6/1	85 °C
471789	12PAR30S/EXPERTCOLOR/S10/940/DIM/120V	90 °C
471094	12PAR30S/EC RETAIL/F25/930/DIM 6/1	90 °C
529768	10PAR30S/LED/827/F25/DIM/ULW/120V 6/1FB	70 °C
529776	10PAR30S/LED/830/F25/DIM/ULW/120V 6/1FB	70 °C
529784	10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB	70 °C
529792	10PAR30S/LED/827/F40/DIM/ULW/120V 6/1FB	70 °C
529800	10PAR30S/LED/830/F40/DIM/ULW/120V 6/1FB	70 °C
529818	10PAR30S/LED/840/F40/DIM/ULW/120V 6/1FB	70 °C
529701	10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB	67 °C
529719	10PAR30L/LED/830/F25/DIM/ULW/120V 6/1FB	67 °C
529727	10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB	67 °C
529735	10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB	67 °C
529743	10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB	67 °C
529750	10PAR30L/LED/840/F40/DIM/ULW/120V 6/1FB	67 °C
470906	12PAR30S/EC/F25/927/DIM/120V 6/1	90 °C
470930	12PAR30S/EC/F25/940/DIM/120V 6/1	90 °C
470948	12PAR30S/EC/F40/940/DIM/120V 6/1	90 °C



PAR30S LED Single Optic Lamps with AirFlux Technology



Accent Diagrams





PAR30L 120V 12-75W 900lm 10D 3000K E26 D

PAR30L 120V 12-75W 900lm 25D 3000K E26 D


PAR30L 120V 12-75W 900lm 40D 3000K E26 D

PAR30S LED Single Optic Lamps with AirFlux Technology


Accent Diagrams




PAR30S 120V 12-75W 25D 3000K E26 D WH




PAR30S 120V 12-75W 900lm 40D 3000K E26 D




PAR30S 120V 12-75W 25D 3000K E26 D BL




10-75W E26 PAR30S 25D 827 2700K




10-75W E26 PAR30S 25D 830 3000K




10-75W E26 PAR30S 25D 840 4000K




10-75W E26 PAR30S 40D 827 2700K




10-75W E26 PAR30S 40D 830 3000K



10-75W E26 PAR30S 40D 840 4000K




10-75W E26 PAR30L 25D 827 2700K




10-75W E26 PAR30L 25D 830 3000K

PAR30S LED Single Optic Lamps with AirFlux Technology


Accent Diagrams




10-75W E26 PAR30L 25D 840 4000K




10-75W E26 PAR30L 40D 827 2700K




10-75W E26 PAR30L 40D 830 3000K




10-75W E26 PAR30L 40D 840 4000K




PAR30S 12W 850lm 10D 2700K E26




PAR30S 12W 850lm 25D 2700K E26




PAR30S 12W 850lm 40D 2700K E26




PAR30S 12W 950lm 25D 2700K E26




PAR30S 12W 950lm 40D 2700K E26



PAR30L 12W 850lm 25D 2700K E26




PAR30L 12W 850lm 40D 2700K E26




PAR30L 12W 950lm 25D 4000K E26

PAR30S LED Single Optic Lamps with AirFlux Technology

Accent Diagrams




PAR30L 12W 950lm 40D 4000K E26




PAR30S 12W 950lm 10D 4000K E26


Beam Diagrams




PAR30L 120V 12-75W 900lm 10D 3000K E26 D




PAR30L 120V 12-75W 900lm 25D 3000K E26 D




PAR30L 120V 12-75W 900lm 40D 3000K E26 D




PAR30S 120V 12-75W 900lm 10D 3000K E26 D




PAR30S 120V 12-75W 25D 3000K E26 D WH




PAR30S 120V 12-75W 900lm 40D 3000K E26 D



PAR30S 120V 12-75W 25D 3000K E26 D BL




10-75W E26 PAR30S 25D 827 2700K




10-75W E26 PAR30S 25D 830 3000K

PAR30S LED Single Optic Lamps with AirFlux Technology


Beam Diagrams




10-75W E26 PAR30S 25D 840 4000K




10-75W E26 PAR30S 40D 827 2700K




10-75W E26 PAR30S 40D 830 3000K




10-75W E26 PAR30S 40D 840 4000K




10-75W E26 PAR30L 25D 827 2700K




10-75W E26 PAR30L 25D 830 3000K




10-75W E26 PAR30L 25D 840 4000K




10-75W E26 PAR30L 40D 827 2700K




10-75W E26 PAR30L 40D 830 3000K



10-75W E26 PAR30L 40D 840 4000K




PAR30S 12W 850lm 10D 2700K E26




PAR30S 12W 850lm 25D 2700K E26

PAR30S LED Single Optic Lamps with AirFlux Technology


Beam Diagrams




PAR30S 12W 850lm 40D 2700K E26




PAR30S 12W 950lm 25D 2700K E26




PAR30S 12W 950lm 40D 2700K E26




PAR30L 12W 850lm 25D 2700K E26




PAR30L 12W 850lm 40D 2700K E26



PAR30L 12W 950lm 25D 4000K E26



PAR30L 12W 950lm 40D 4000K E26



PAR30S 12W 950lm 10D 4000K E26

