



A new generation for Linear LED T8 lighting.

LED InstantFit Lamps

Philips LED T8 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Benefits

- Over 41% energy savings vs F32T8 electronic instant start systems (2)
- No mercury allowing for non-hazardous waste disposal.
- Emits virtually no UV rays or IR
- Glass-free for safer working conditions
- 5 year limited warranty (3)
- (2) Lamp F32T8 Electronic Instant Start System with 0.88 Ballast Factor= 58 SystemWatts (2) Philips LED T8 InstantFit = 34 SystemWatts $58 - 34 = 24$ SystemWatts Saved $24 / 58 = 41.4\%$ Energy Saved
- (3) See warranty for terms and conditions.

Features

- Instant on, no flicker or buzz
- Fits into existing linear fixtures
- Compatible with Instant Start ballasts (1) eliminating the need for rewiring and allows fixture to maintain original UL compliance.
- (1) Must follow guidelines for installation from Philips Quick Installation Guide included with lamp shipment.

Application


- Full light output in spaces with temperatures down to -22°F (-30°C)
- Perfect for applications with frequent "on/off" switching cycles
- Buildings that desire to be mercury free

LED InstantFit Lamps

Warnings and Safety


- Philips LED T8 InstantFit lamps will only operate properly on compatible instant-start ballasts. Please refer to the Philips LED T8 InstantFit Installation Guide, which can be obtained through your local Philips Sales Representative, or visit www.philips.com/tled

Versions



Medium Bi-Pin Fluorescent

Dimensional drawing



Product	D1	D2	A1	A2	A3
16T8/LED/48-850/IF18/G 25/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm
16T8/LED/48-840/IF18/G 25/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm

LED InstantFit Lamps

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Frequency	20K to 120K Hz
Voltage (Nom)	120-277, 347 V
Power (Rated) (Nom)	16 W
Starting Time (Nom)	0.5 s

General Information

Cap-Base	G13
Nominal Lifetime (Nom)	36000 h
Rated Lifetime (Hours)	36000 h
Switching Cycle	50000X

Light Technical

Color Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux (Nom)	1800 lm
Luminous Flux (Rated) (Nom)	1800 lm

Temperature

T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Case Maximum (Nom)	35 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C

Light Technical

Order Code	Full Product Name	Color Code	Correlated Color Temperature (Nom)
542084	16T8/LED/48-840/IF18/G 25/1	841	4000 K
542092	16T8/LED/48-850/IF18/G 25/1	850	5000 K

