



Philips tanning starters: a complete range of easy-to-install eco- friendly starters for tanning lamps operating on a conventional electromagnetic ballast

Starters for tanning lamps

Range of premium-quality starters for igniting fluorescent lamps operating on electromagnetic ballasts

Benefits

- Easy to install (click and switch)
- Safe ignition
- Eco-friendly

Features

- Narrowed starter shape and two extra notches (patented innovation)
- Flame-retardant components and UV-resistant canister
- Lead-free, and no radioactive substances

Starters for tanning lamps


Application

- Ignite fluorescent lamps (all brands) operating on a conventional electromagnetic ballast.
- Bodytone Starter 25-100W - 220-240V~, 25-100W, Single application
- Bodytone Starter 120-180W - 220-240V~, 120-180W, Single application
- S12 Bodytone Starter 115-140W - 220-240V~, 115-140W, Single application
- S16 Starter 220-240~, 70, 75, 85, 100, 125W, Single application

Versions



Dimensional drawing



Product	C (max)	E (max)
BodyTone St 120-180W 230-240V 20x25	40.3 mm	21.5 mm
BodyTone St 25-100W 220-240V 20X25	40.3 mm	21.5 mm
BodyTone St 120-180W 230-240V 1000	40.3 mm	21.5 mm

Operating and Electrical	
Non Reclosure Voltage (Min)	140 V
General Information	
System Description	Single
Mechanical and Housing	
Housing Colour	Black

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power (Rated) (Nom)
928391830303	BodyTone St 25-100W 220-240V 20X25	220-240 V	25-100 W
928391930303	BodyTone St 120-180W 230-240V 20x25	230-240 V	120-180 W

Order Code	Full Product Name	Voltage (Nom)	Power (Rated) (Nom)
928391930355	BodyTone St 120-180W 230-240V 1000	230-240 V	120-180 W

Starters for tanning lamps

