



Product Description

MASTER TL5 High Output

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Benefits

- Allows system miniaturisation and maximum luminaire design freedom
- Lamp lengths enable easy fitting into ceiling module systems
- Optimised for installations which need high luminous flux
- Virtually constant lumen level with excellent lumen maintenance
- Good colour rendering

Features

- 40% thinner than TL-D lamps
- Designed for high light output and system miniaturisation
- Highly efficient 3-band fluorescent coating in combination with precoating
- Specifically designed for operation with electronic gear and well suited for dimming
- Maximum light output reached at approx. 35 °C in free-burning position if an electronic ballast without additional electrode heating is used
- Can be ignited from -15 to +50 °C

Application

- The combination of a compact lamp and high lumen package of the MASTER TL5 HO offers exciting opportunities for architectural lighting and customised solutions
- Offers economic solutions with high-ceiling lighting in shops, industry and department stores
- The high luminous flux gives optimal results in aesthetic pendants and furniture-mounted luminaires in offices, workshops, restaurants and reception areas

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTER TL5 High Output

Versions



LPPR TL5-HO8

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 54W/865 SLV/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
MASTER TL5 HO 80W/865 SLV/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

General Information

Cap-Base G5

Light Technical

Chromaticity Coordinate X (Nom) 0.313

Chromaticity Coordinate Y (Nom) 0.337

Color Designation Cool Daylight

Correlated Color Temperature (Nom) 6500 K

Color rendering index (CRI) 82

Controls and Dimming

Dimmable Yes

Mechanical and Housing

Bulb Shape T5

Approval and Application

Mercury (Hg) Content (Nom) 1.2 mg

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
927929086555	MASTER TL5 HO 54W/865 SLV/40	78 lm/W	4,200 lm
927929586557	MASTER TL5 HO 80W/865 SLV/40	79 lm/W	6,300 lm

Operating and Electrical

MASTER TL5 High Output

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927929086555	MASTER TL5 HO 54W/865 SLV/40	0.455 A	54.4 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927929586557	MASTER TL5 HO 80W/865 SLV/40	0.530 A	79.8 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927929086555	MASTER TL5 HO 54W/865 SLV/40	55 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927929586557	MASTER TL5 HO 80W/865 SLV/40	80 kWh

