



Product Description

MASTER TL-D HF Super 80

Low-pressure mercury discharge lamps with a tubular 26 mm envelope and argon gas filling

Benefits

- Relatively high efficacy, both initially and during lamp lifetime
- Relatively high efficacy, both initially and during lamp lifetime, with high lumen maintenance
- · Smooth start
- · Good colour rendering
- · Stable behavior in dimming operation with cool environments
- · Creates atmospheres from warm white to cool daylight

Features

- \cdot Special lamp designed for High Frequency operation
- Highly efficient 3-band fluorescent coating in combination with New Generation pre-coating technology
- · Highly efficient 3-band fluorescent coating
- · High initial lumen output
- · Low mercury dose
- · Available in varying colour designations
- · Low mercury dose
- · MASTER TL-D lamps are fully recyclable
- End-cap has green bottom plate to identify lamp as recyclable

Application

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps for 'human' applications such as schools, offices, shops, factory halls etc.
- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps for 'human' applications such as schools, offices, shops, factory halls etc.

MASTER TL-D HF Super 80

Warnings and Safety


- · Special electronic gear must be used
- · Special electronic gear must be used
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR TL-D8HF Super-80 G13

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D HF Super 80	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm
50W/840 SLV/25					



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.