



# Product Description

## TL-D Standard Colours

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Benefits

- Create atmospheres from warm white to cool daylight

### Features

- Standard colours with moderate colour rendering
- Available in various colour designations


### Application

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where colour rendering is not an important factor

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/33-640 UNP/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL-D 36W/33-640 UNP/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

# TL-D Standard Colours

General Information	
Cap-Base	G13

Light Technical	
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	63

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8

Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg

## Light Technical

Order Code	Full Product Name	Luminous Flux
928048003384	TL-D 18W/33-640 UNP/25	1,200 lm

Order Code	Full Product Name	Luminous Flux
928048503384	TL-D 36W/33-640 UNP/25	2,850 lm

## Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928048003384	TL-D 18W/33-640 UNP/25	0.360 A	59 V	18.0 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928048503384	TL-D 36W/33-640 UNP/25	0.440 A	103 V	36.0 W

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
928048003384	TL-D 18W/33-640 UNP/25	22 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
928048503384	TL-D 36W/33-640 UNP/25	43 kWh

