



For every project where light really matters, a 1:1 retrofit replacement

Coreline tempo small

CoreLine tempo small is a highly efficient range of luminaires designed for 1:1 retrofit replacement of conventional floodlighting technology, while retaining the same electrical installation and poles. This urban lighting range is designed for the direct replacement of 70-W HID lamps, but uses less energy and requires less investment than conventional installations. A narrow range of options makes it easy to find the best lux-for-lux replacement for your project lighting.

Benefits

- The same light levels as your existing conventional solution while saving on energy
- High quality small tempo floodlights
- Easy to use

Features


- Symmetric and asymmetric optics for general area lighting
- Long lifetime of 75,000 hours, integrated surge protection, high impact resistance IK08, IP65
- Plug and play installation with 1m cable and IP65 connector

Application

- Warehouses
- Buildings/shop facades
- Landscape

Coreline tempo small

Dimensional drawing



Product details



Coreline_tempo_small-BVP110-DP01.tif



Coreline_tempo_small-BVP110-DP02.tif



Coreline_tempo_small-BVP110-DP03.tif



Coreline_tempo_small-BVP110-DP05.tif



Coreline_tempo_small-BVP110-DP06.tif

Coreline tempo small

General information

Driver included	Yes
Lamp family code	LED42
Light source replaceable	No
Number of gear units	Unit

Light technical

Light source colour	Neutral white
Optical cover/lens type	Flat glass
Standard tilt angle side entry	0°
Standard tilt angle post-top	0°
Upwards light output ratio	88

Controls and dimming

Dimmable	No
----------	----

Approval and application

CE mark	CE mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Mech. impact protection code	IK08
Surge Protection (Common/Differential)	Luminaire surge protection level up to 10 kV differential mode and 10 kV common mode

Light technical

Order Code	Full Product Name	Luminaire light beam spread	Optic type outdoor
30635300	BVP110 LED42/NW A	39° x 96°	Asymmetrical
30636000	BVP110 LED42/NW S	92° x 91°	Symmetrical

