



CoreLine Waterproof – the clear choice for LED

CoreLine Waterproof

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it’s a simple switch.

Benefits

Features

Application

Specifications

Ambient Temperature	-20 to +35 °C
	-20 to +40 °C
	0 to +25 °C
Dimming	No, wireless Dim, yes
Driver	Power supply unit (Power supply unit)
	Power supply unit with DALI interface (Power supply unit with DALI interface)
Initial correlated color temperature	3000 K, 4000 K, 6500 K

Initial input power	15, 16, 20.5, 21, 22, 24.3, 24.5, 25.5, 26, 27, 28.5, 28.6, 30, 30.5,
	34.5, 35, 42.9, 43, 45, 45.5, 50, 51, 57.1, 61, 66 W
Initial luminous flux	1800, 1900, 2500, 2700, 3100, 3400, 3700, 4000, 5500, 5700, 6000, 7500, 8000 lm
Material	Bracket:
Material	Housing: polycarbonate

CoreLine Waterproof

Versions



Coreline Waterproof G2 LSC - LED Module, system flux 2700 lm - 840 neutral white - Power supply unit



840 neutral white - Power supply unit

Product details



CoreLine Waterproof WT120C G2 PCU-7DPP



CoreLine Waterproof WT120C G2 PCU-3DPP




CoreLine Waterproof WT120C G2 PCU-10DPP



CoreLine Waterproof WT120C G2 PCU-9DPP



CoreLine Waterproof WT120C G2 PCU-12DPP



CoreLine Waterproof WT120C G2 PCU-2DPP

CoreLine Waterproof

Product details

CoreLine Waterproof WT120C G2
PCU-13DPP



CoreLine Waterproof WT120C G2
PCU-8DPP



CoreLine Waterproof WT120C G2
PCU-11DPP



Application Conditions	
Suitable for random switching	Not applicable
Approval and Application	
Mech. impact protection code	IK08
Ingress protection code	IP65
Operating and Electrical	
Input Voltage	220 to 240 V
General Information	
CE mark	CE mark
Protection class IEC	Safety class I (I)
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	D
Glow-wire test	850/30
Light source replaceable	No
Number of gear units	1 unit
Optic type	110
Initial Performance (IEC Compliant)	
Init. Color Rendering Index	>80
Luminous flux tolerance	+/-10%
Mechanical and Housing	
Color	Gray

Application Conditions

Order Code	Full Product Name	Ambient temperature range	Maximum dim level
88306800	WT120C G2 LED19S/840 PSD L600	-20 to +35 °C	1%
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-20 to +35 °C	Not applicable
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	0 to +25 °C	Not applicable
88307500	WT120C G2 LED27S/840 PSD L1200	-20 to +35 °C	1%
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	0 to +25 °C	1%
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-20 to +35 °C	Not applicable
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-20 to +35 °C	Not applicable
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-20 to +35 °C	Not applicable
88309900	WT120C G2 LED40S/840 PSD L1200	-20 to +35 °C	1%
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	0 to +25 °C	Not applicable
39980100	WT120C G2 LED40S/840 IA1 ELB3 L1200	0 to +25 °C	10%
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	0 to +25 °C	1%
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-20 to +35 °C	Not applicable
88308200	WT120C G2 LED34S/840 PSD L1500	-20 to +35 °C	1%
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	0 to +25 °C	Not applicable
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	0 to +25 °C	1%
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-20 to +35 °C	Not applicable
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-20 to +35 °C	Not applicable
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-20 to +35 °C	Not applicable
88310500	WT120C G2 LED60S/840 PSD L1500	-20 to +35 °C	1%
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	0 to +25 °C	Not applicable
39981800	WT120C G2 LED60S/840 IA1 ELB3 L1500	0 to +25 °C	10%
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	0 to +25 °C	1%
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-20 to +35 °C	Not applicable
40929600	WT120C G2 LED80S/840 PSD L1500	-20 to +35 °C	1%

CoreLine Waterproof

Order Code	Full Product Name	Ambient temperature range	Maximum dim level
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	0 to +25 °C	Not applicable
84045900	WT120C G2 LED19S/840 PSU L600	-20 to +40 °C	Not applicable
84046600	WT120C G2 LED27S/840 PSU L1200	-20 to +40 °C	Not applicable
84047300	WT120C G2 LED34S/840 PSU L1500	-20 to +40 °C	Not applicable
84048000	WT120C G2 LED40S/840 PSU L1200	-20 to +40 °C	Not applicable
84049700	WT120C G2 LED60S/840 PSU L1500	-20 to +40 °C	Not applicable
40928900	WT120C G2 LED80S/840 PSU L1500	-20 to +40 °C	Not applicable
36934199	WT120C G2 LED34S/865 PSU L1500	-20 to +40 °C	Not applicable
36935899	WT120C G2 LED60S/865 PSU L1500	-20 to +40 °C	Not applicable
34976399	WT120C G2 LED18S/840 PSU PCO L600	-20 to +40 °C	Not applicable
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-20 to +40 °C	Not applicable
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-20 to +40 °C	Not applicable
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-20 to +40 °C	Not applicable
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-20 to +40 °C	Not applicable
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-20 to +40 °C	Not applicable

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
88306800	WT120C G2 LED19S/840 PSD L600	Yes	85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	No
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	No	39981800	WT120C G2 LED60S/840 IA1 ELB3 L1500	Wireless Dim
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	No	88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	Yes
88307500	WT120C G2 LED27S/840 PSD L1200	Yes	40930200	WT120C G2 LED80S/840 PSU TW3 L1500	No
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	Yes	40929600	WT120C G2 LED80S/840 PSD L1500	Yes
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	No	40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	No
16316700	WT120C G2 LED40S/840 PSU WEC L1200	No	84045900	WT120C G2 LED19S/840 PSU L600	No
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	No	84046600	WT120C G2 LED27S/840 PSU L1200	No
88309900	WT120C G2 LED40S/840 PSD L1200	Yes	84047300	WT120C G2 LED34S/840 PSU L1500	No
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	No	84048000	WT120C G2 LED40S/840 PSU L1200	No
39980100	WT120C G2 LED40S/840 IA1 ELB3 L1200	Wireless Dim	84049700	WT120C G2 LED60S/840 PSU L1500	No
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	Yes	40928900	WT120C G2 LED80S/840 PSU L1500	No
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	No	36934199	WT120C G2 LED34S/865 PSU L1500	No
88308200	WT120C G2 LED34S/840 PSD L1500	Yes	36935899	WT120C G2 LED60S/865 PSU L1500	No
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	No	34976399	WT120C G2 LED18S/840 PSU PCO L600	No
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	Yes	34977099	WT120C G2 LED25S/840 PSU PCO L1200	No
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	No	34978799	WT120C G2 LED31S/840 PSU PCO L1500	No
16318100	WT120C G2 LED60S/840 PSU WEC L1500	No	34979499	WT120C G2 LED37S/840 PSU PCO L1200	No
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	No	34980099	WT120C G2 LED57S/840 PSU PCO L1500	No
88310500	WT120C G2 LED60S/840 PSD L1500	Yes	34981799	WT120C G2 LED75S/840 PSU PCO L1500	No

General Information (1/2)

Order Code	Full Product Name	Beam			Lamp family code	Order Code	Full Product Name	Beam			Lamp family code
		angle of light source	Optical cover/ lens type	Emergency lighting				angle of light source	Optical cover/ lens type	Emergency lighting	
88306800	WT120C G2 LED19S/840 PSD L600	-	MLO	-	LED19S	85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	-	MLO	EL3	LED27S
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-	MLO	-	LED27S	88307500	WT120C G2 LED27S/840 PSD L1200	-	MLO	-	LED27S

CoreLine Waterproof

Order Code	Full Product Name	Beam angle of light source	Optical cover/ lens type	Emergency lighting	Lamp family code
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	-	MLO	EL3	LED27S
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-	MLO	-	LED40S
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-	MLO	-	LED40S
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	MLO	-	LED40S
88309900	WT120C G2 LED40S/840 PSD L1200	-	MLO	-	LED40S
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	-	MLO	EL3	LED40S
39980100	WT120C G2 LED40S/840 IA1 ELB3 L1200	-	MLO	EL3	LED40S
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	-	MLO	EL3	LED40S
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-	MLO	-	LED34S
88308200	WT120C G2 LED34S/840 PSD L1500	-	MLO	-	LED34S
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	-	MLO	EL3	LED34S
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	-	MLO	EL3	LED34S
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-	MLO	-	LED60S
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-	MLO	-	LED60S
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	MLO	-	LED60S
88310500	WT120C G2 LED60S/840 PSD L1500	-	MLO	-	LED60S
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	-	MLO	EL3	LED60S

Order Code	Full Product Name	Beam angle of light source	Optical cover/ lens type	Emergency lighting	Lamp family code
39981800	WT120C G2 LED60S/840 IA1 ELB3 L1500	-	MLO	EL3	LED60S
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	-	MLO	EL3	LED60S
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-	MLO	-	LED80S
40929600	WT120C G2 LED80S/840 PSD L1500	-	MLO	-	LED80S
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	-	MLO	EL3	LED80S
84045900	WT120C G2 LED19S/840 PSU L600	-°	MLO	-	-
84046600	WT120C G2 LED27S/840 PSU L1200	-°	MLO	-	-
84047300	WT120C G2 LED34S/840 PSU L1500	-°	MLO	-	-
84048000	WT120C G2 LED40S/840 PSU L1200	-°	MLO	-	-
84049700	WT120C G2 LED60S/840 PSU L1500	-°	MLO	-	-
40928900	WT120C G2 LED80S/840 PSU L1500	-°	MLO	-	-
36934199	WT120C G2 LED34S/865 PSU L1500	-°	-	-	-
36935899	WT120C G2 LED60S/865 PSU L1500	-°	-	-	-
34976399	WT120C G2 LED18S/840 PSU PCO L600	-°	MLO	-	-
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-°	MLO	-	-
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-°	MLO	-	-
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-°	MLO	-	-
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-°	MLO	-	-
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-°	MLO	-	-

General Information (2/2)

CoreLine Waterproof

Order Code	Full Product Name	Product	
		Family Code	Service tag
88306800	WT120C G2 LED19S/840 PSD L600	WT130C	Yes
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	WT130C	Yes
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	WT130C	Yes
88307500	WT120C G2 LED27S/840 PSD L1200	WT130C	Yes
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	WT130C	Yes
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	WT130C	Yes
16316700	WT120C G2 LED40S/840 PSU WEC L1200	WT130C	Yes
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	WT130C	Yes
88309900	WT120C G2 LED40S/840 PSD L1200	WT130C	Yes
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	WT130C	Yes
39980100	WT120C G2 LED40S/840 IA1 ELB3 L1200	WT130C	Yes
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	WT130C	Yes
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	WT130C	Yes
88308200	WT120C G2 LED34S/840 PSD L1500	WT130C	Yes
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	WT130C	Yes
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	WT130C	Yes
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	WT130C	Yes
16318100	WT120C G2 LED60S/840 PSU WEC L1500	WT130C	Yes
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	WT130C	Yes
88310500	WT120C G2 LED60S/840 PSD L1500	WT130C	Yes

Order Code	Full Product Name	Product	
		Family Code	Service tag
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	WT130C	Yes
39981800	WT120C G2 LED60S/840 IA1 ELB3 L1500	WT130C	Yes
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	WT130C	Yes
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	WT130C	Yes
40929600	WT120C G2 LED80S/840 PSD L1500	WT130C	Yes
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	WT130C	Yes
84045900	WT120C G2 LED19S/840 PSU L600	-	Yes
84046600	WT120C G2 LED27S/840 PSU L1200	-	Yes
84047300	WT120C G2 LED34S/840 PSU L1500	-	Yes
84048000	WT120C G2 LED40S/840 PSU L1200	-	Yes
84049700	WT120C G2 LED60S/840 PSU L1500	-	Yes
40928900	WT120C G2 LED80S/840 PSU L1500	-	Yes
36934199	WT120C G2 LED34S/865 PSU L1500	-	-
36935899	WT120C G2 LED60S/865 PSU L1500	-	-
34976399	WT120C G2 LED18S/840 PSU PCO L600	-	Yes
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-	Yes
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-	Yes
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-	Yes
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-	Yes
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-	Yes

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr.	Initial LED	Initial
			Color Temperature	luminaire efficacy	luminous flux
88306800	WT120C G2 LED19S/840 PSD L600	(0.38,0.38)SDCM<=3	4000 K	119 lm/W	1900 lm
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3	4000 K	129 lm/W	2700 lm
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	104 lm/W	2700 lm
88307500	WT120C G2 LED27S/840 PSD L1200	(0.38,0.38)SDCM<=3	4000 K	123 lm/W	2700 lm
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	100 lm/W	2700 lm
91687200	WT120C G2 LED40S/840 O PSU TW3 L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm
16316700	WT120C G2 LED40S/840	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr.	Initial LED	Initial
			Color Temperature	luminaire efficacy	luminous flux
	O PSU WEC L1200				
16317400	WT120C G2 LED40S/840 O PSU TW1 WEC L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm
88309900	WT120C G2 LED40S/840 O PSD L1200	(0.38,0.38)SDCM<=3	4000 K	133 lm/W	4000 lm
85419700	WT120C G2 LED40S/840 O PSU ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	114 lm/W	4000 lm
39980100	WT120C G2 LED40S/840 O IA1 ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	116 lm/W	4000 lm
88312900	WT120C G2 LED40S/840 O PSD ELB3 L1200	(0.38,0.38)SDCM<=3	4000 K	114 lm/W	4000 lm
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3	4000 K	136 lm/W	3400 lm

CoreLine Waterproof

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
88308200	WT120C G2 LED34S/840 PSD L1500	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	3400 lm
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	(0.38,0.38)	SDCM<=3 4000 K	113 lm/W	3400 lm
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	(0.38,0.38)	SDCM<=3 4000 K	111 lm/W	3400 lm
91688900	WT120C G2 LED60S/84 0 PSU TW3 L1500	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	6000 lm
16318100	WT120C G2 LED60S/84 0 PSU WEC L1500	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	6000 lm
16319800	WT120C G2 LED60S/84 0 PSU TW1 WEC L1500	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	6000 lm
88310500	WT120C G2 LED60S/84 0 PSD L1500	(0.38,0.38)	SDCM<=3 4000 K	133 lm/W	6000 lm
85421000	WT120C G2 LED60S/84 0 PSU ELB3 L1500	(0.38,0.38)	SDCM<=3 4000 K	120 lm/W	6000 lm
39981800	WT120C G2 LED60S/84 0 IA1 ELB3 L1500	(0.38,0.38)	SDCM<=3 4000 K	120 lm/W	6000 lm
88314300	WT120C G2 LED60S/84 0 PSD ELB3 L1500	(0.38,0.38)	SDCM<=3 4000 K	118 lm/W	6000 lm
40930200	WT120C G2 LED80S/84 0 PSU TW3 L1500	(0.38,0.38)	SDCM<=3 4000 K	131 lm/W	8000 lm
40929600	WT120C G2 LED80S/84 0 PSD L1500	(0.38,0.38)	SDCM<=3 4000 K	131 lm/W	8000 lm
40931900	WT120C G2 LED80S/84	(0.38,0.38)	SDCM<=3 4000 K	121 lm/W	8000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	0 PSU L1500 ELB3				
84045900	WT120C G2 LED19S/840 PSU L600	(0.38,0.38)	SDCM<=3 4000 K	127 lm/W	1900 lm
84046600	WT120C G2 LED27S/840 PSU L1200	(0.38,0.38)	SDCM<=3 4000 K	135 lm/W	2700 lm
84047300	WT120C G2 LED34S/840 PSU L1500	(0.38,0.38)	SDCM<=3 4000 K	142 lm/W	3400 lm
84048000	WT120C G2 LED40S/84 0 PSU L1200	(0.38,0.38)	SDCM<=3 4000 K	143 lm/W	4000 lm
84049700	WT120C G2 LED60S/84 0 PSU L1500	(0.38,0.38)	SDCM<=3 4000 K	143 lm/W	6000 lm
40928900	WT120C G2 LED80S/84 0 PSU L1500	(0.38,0.38)	SDCM<=3 4000 K	140 lm/W	8000 lm
36934199	WT120C G2 LED34S/865 PSU L1500	(0.31,0.32)	SDCM<=3 6500 K	139 lm/W	3400 lm
36935899	WT120C G2 LED60S/86 5 PSU L1500	(0.31,0.32)	SDCM<=3 6500 K	140 lm/W	6000 lm
34976399	WT120C G2 LED18S/840 PSU PCO L600	(0.38,0.38)	SDCM<=3 4000 K	120 lm/W	1800 lm
34977099	WT120C G2 LED25S/840 PSU PCO L1200	(0.38,0.38)	SDCM<=3 4000 K	125 lm/W	2500 lm
34978799	WT120C G2 LED31S/840 PSU PCO L1500	(0.38,0.38)	SDCM<=3 4000 K	129 lm/W	3100 lm
34979499	WT120C G2 LED37S/840 PSU PCO L1200	(0.38,0.38)	SDCM<=3 4000 K	132 lm/W	3700 lm
34980099	WT120C G2 LED57S/840 PSU PCO L1500	(0.38,0.38)	SDCM<=3 4000 K	136 lm/W	5700 lm
34981799	WT120C G2 LED75S/840 PSU PCO L1500	(0.38,0.38)	SDCM<=3 4000 K	132 lm/W	7500 lm

CoreLine Waterproof

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power	Order Code	Full Product Name	Initial input power
88306800	WT120C G2 LED19S/840 PSD L600	16 W	85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	50 W
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	21 W	39981800	WT120C G2 LED60S/840 IA1 ELB3 L1500	50 W
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	26 W	88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	51 W
88307500	WT120C G2 LED27S/840 PSD L1200	22 W	40930200	WT120C G2 LED80S/840 PSU TW3 L1500	61 W
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	27 W	40929600	WT120C G2 LED80S/840 PSD L1500	61 W
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	30 W	40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	66 W
16316700	WT120C G2 LED40S/840 PSU WEC L1200	30 W	84045900	WT120C G2 LED19S/840 PSU L600	15 W
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	30 W	84046600	WT120C G2 LED27S/840 PSU L1200	20.5 W
88309900	WT120C G2 LED40S/840 PSD L1200	30 W	84047300	WT120C G2 LED34S/840 PSU L1500	24.3 W
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	35 W	84048000	WT120C G2 LED40S/840 PSU L1200	28.6 W
39980100	WT120C G2 LED40S/840 IA1 ELB3 L1200	34.5 W	84049700	WT120C G2 LED60S/840 PSU L1500	42.9 W
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	35 W	40928900	WT120C G2 LED80S/840 PSU L1500	57.1 W
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	25.5 W	36934199	WT120C G2 LED34S/865 PSU L1500	24.5 W
88308200	WT120C G2 LED34S/840 PSD L1500	25.5 W	36935899	WT120C G2 LED60S/865 PSU L1500	43 W
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	30.5 W	34976399	WT120C G2 LED18S/840 PSU PCO L600	15 W
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	30.5 W	34977099	WT120C G2 LED25S/840 PSU PCO L1200	20.5 W
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	45 W	34978799	WT120C G2 LED31S/840 PSU PCO L1500	24.3 W
16318100	WT120C G2 LED60S/840 PSU WEC L1500	45 W	34979499	WT120C G2 LED37S/840 PSU PCO L1200	28.6 W
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	45 W	34980099	WT120C G2 LED57S/840 PSU PCO L1500	42.9 W
88310500	WT120C G2 LED60S/840 PSD L1500	45 W	34981799	WT120C G2 LED75S/840 PSU PCO L1500	57.1 W

