



MSR Gold™ SA Double Ended – for extended performance

MSR Gold™ SA Double Ended

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Benefits

- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- Pure, white light; color point close to black body line. Consistent color impression over MSR Range
- Reduces early lamp or lamp holder failures

Features

- Philips Pinch Protection
- MSR filling
- Gold plated lamp caps

Application


- Entertainment

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MSR Gold™ SA Double Ended

Dimensional drawing



Product	D (max)	O	A	C (max)		
MSR Gold 1200 SA/2 DE 1CT/4	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm
MSR Gold 1200 SA/DE 1CT/4	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm
MSR Gold 1510 SA/DE UNP/108	23.2 mm	7.0 mm	114.8 mm	136 mm		
MSR Gold 700 SA/2 DE 1CT/4	19 mm	4.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm

General Information

Cap-Base	SFC10-4
Operating Position	UNIVERSAL

Light Technical

Color Code	-
------------	---

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
22121000	MSR Gold™ 1200 SA/DE 1CT/4	6000 K	83	103,000 lm
22123400	MSR Gold™ 700 SA/2 DE 1CT/4	7500 K	73	48,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
22107400	MSR Gold™ 1200 SA/2 DE 1CT/4	7500 K	85	100,000 lm
21342629	MSR Gold™ 1510 SA/DE UNP/108	6000 K	85	140,000 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
22121000	MSR Gold™ 1200 SA/DE 1CT/4	13.6 A	1,200 W
22123400	MSR Gold™ 700 SA/2 DE 1CT/4	11.5 A	700 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
22107400	MSR Gold™ 1200 SA/2 DE 1CT/4	13.6 A	1,200 W
21342629	MSR Gold™ 1510 SA/DE UNP/108	13.5 A	1,510 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
22121000	MSR Gold™ 1200 SA/DE 1CT/4	No
22123400	MSR Gold™ 700 SA/2 DE 1CT/4	No

Order Code	Full Product Name	Dimmable
22107400	MSR Gold™ 1200 SA/2 DE 1CT/4	No
21342629	MSR Gold™ 1510 SA/DE UNP/108	Yes

MSR Gold™ SA Double Ended

