



# MSR Gold™ SA Double Ended – for extended performance

## MSR Gold™ SA Double Ended

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

### Benefits

- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- Pure, white light; color point close to black body line. Consistent color impression over MSR Range
- Reduces early lamp or lamp holder failures

### Features

- Philips Pinch Protection
- MSR filling
- Gold plated lamp caps

### Application

- Entertainment

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

# MSR Gold™ SA Double Ended


## Versions



MSR Gold™ SA/2) DE

MSR Gold™ 575 SA/2 DE

## Dimensional drawing



Product	D (max)	O	A (min)	A (max)	A	C (max)
MSR Gold™ 700 SA/2 DE 1CT/4	19 mm	4.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm
MSR Gold™ 575 SA/2 DE 1CT/40	18.5 mm	5.0 mm	69.6 mm	70.4 mm	70 mm	92 mm
MSR Gold™ 1200 SA/DE 1CT/4	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm

Controls and Dimming	
Dimmable	No
General Information	
Life To 50% Failures (Nom)	750 h
Operating Position	Universal

## Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
287144	MSR Gold™ 1200 SA/DE 1CT/4	13.6 A	1200 W
287136	MSR Gold™ 700 SA/2 DE 1CT/4	11.5 A	700 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
245019	MSR Gold™ 575 SA/2 DE 1CT/40	7 A	575 W

## General Information

Order Code	Full Product Name	Cap-Base	Main Application	System Description
287144	MSR Gold™ 1200 SA/DE 1CT/4	SFC10-4	Entertainment	SA/DE
287136	MSR Gold™ 700 SA/2 DE 1CT/4	SFC10-4	Studio/Disco	SA/2 DE


Order Code	Full Product Name	Cap-Base	Main Application	System Description
245019	MSR Gold™ 575 SA/2 DE 1CT/40	SFC-11	Entertainment	SA/2 DE

# MSR Gold™ SA Double Ended

## Light Technical

Order Code	Full Product Name	Color Code	Correlated Color	Color Rendering	Color Rendering	Luminous Flux (Min)	Luminous Flux (Nom)
			Temperature (Nom)	Index (Min)	Index (Nom)		
287144	MSR Gold™ 1200 SA/DE 1CT/4	-	6000 K	-	85	92700 lm	103000 lm
287136	MSR Gold™ 700 SA/2 DE 1CT/4	-	7500 K	62	75	43200 lm	48000 lm
245019	MSR Gold™ 575 SA/2 DE 1CT/40	2	7500 K	-	75	39000 lm	42000 lm

## Colour Rendering Diagrams



XDCR\_XDMSR\_1200W-Colour Rendering  
Vector diagram

