



# MSR – bright vivid colors, always

## MSR

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

### Benefits

- Optimal light collection
- Excellent color characteristics
- Brightness on stage

### Features

- Single ended lamp concept
- High CRI
- Daylight Color Temperatures

### Application

- Theatre stages
- Discos
- Events
- Shows

### Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions




XPPR XDMSR 0025

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 1200 1CT/3	40 mm	10.0 mm	84 mm	86 mm	85 mm	175 mm	53 mm
MSR 1200/2.1CT/3	40 mm	10.0 mm	84 mm	86 mm	85 mm	175 mm	53 mm
MSR 700 1CT/8	30 mm	8.0 mm	74 mm	76 mm	75 mm	152 mm	42 mm
MSR 700/2 1CT/8	30 mm	8.0 mm	74 mm	76 mm	75 mm	152 mm	42 mm



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 400	23 mm	6.0	61 mm	63 mm	62	112 mm	36 mm	35	34 mm
1CT/4		mm			mm			mm	
MSR 575/2	30 mm	7.0	64 mm	66 mm	65	125 mm	36 mm	35	34 mm
10H 1CT/4		mm			mm			mm	

General Information	
Operating Position	UNIVERSAL
Controls and Dimming	
Dimmable	No

General Information

Order Code	Full Product Name	Cap-Base
91575400	MSR 700 1CT/8	G22
91121300	MSR 1200 1CT/3	G22
91638600	MSR 700/2 1CT/8	G22

Order Code	Full Product Name	Cap-Base
91133600	MSR 1200/2 1CT/3	G22
41600600	MSR 400 1CT/4	GX9.5

Order Code	Full Product Name	Cap-Base
22127200	MSR 575/2 10H 1CT/4	GX9.5

### Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux (Min)	Luminous Flux
91575400	MSR 700 1CT/8	5900 K	75	-	-	55,000 lm
91121300	MSR 1200 1CT/3	5900 K	80	-	-	103,000 lm
91638600	MSR 700/2 1CT/8	7200 K	80	2	-	55,000 lm
91133600	MSR 1200/2 1CT/3	7200 K	85	2	-	104,000 lm
41600600	MSR 400 1CT/4	5830 K	95	-	28,440 lm	31,600 lm
22127200	MSR 575/2 10H 1CT/4	6990 K	73	2	-	47,000 lm

### Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
91575400	MSR 700 1CT/8	12 A	700 W
91121300	MSR 1200 1CT/3	13.8 A	1,200 W
91638600	MSR 700/2 1CT/8	11 A	700 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
91133600	MSR 1200/2 1CT/3	13.8 A	1,200 W
41600600	MSR 400 1CT/4	7 A	400 W
22127200	MSR 575/2 10H 1CT/4	6.75 A	575 W

